

ECONOMICAL LOW-PRESSURE/ VACUUM SWITCHES

PSW-680 Series Vacuum to 200 inH₂O

All Models
\$95



- ✓ Compound Range Covers Vacuum and Pressure in One Unit
- ✓ Low Inch-of-Water Ranges
- ✓ Silver Switch Contacts Rated for 5 A @ 250 Vac
- ✓ 1 A, Gold-Plated Contacts for TTL or Dry Contacts

SPECIFICATIONS

Process Temp: -55 to 90°C (-67 to 194°F); a setpoint change of up to 2% of sensor capacity can be anticipated when switch is used either below -25°C (-13°F) or above 50°C (122°F)

Repeatability: ±0.8 inH₂O

Cycling: Not to exceed 20 cpm

Warranty: 3 years/1 million cycles

Proof Pressure/Vacuum:
±553.6 inH₂O (±20 psi)

Wetted Parts: Buna-N, 316 SS, zinc alloy with chromate finish, loctite #271 sealing compound

Dimensions: 58.4 D x 57.2 mm H (2.3 x 2.25")

Pressure Port: 1/8-27 MNPT

Electrical Connection: 300 mm (12") pigtail leads, 20 AWG, polyvinyl insulated

Weight: 221 g (7.8 oz)

Proof Pressure/Vacuum:
15 psi, -5.4 psi or 11 inHg vac

See switch accessories on page H-48 for audible alarms and relay modules.



PSW-681, \$95, shown actual size.

Recommended Reference Book:
Newnes Engineering Science Pocket Book, EE-2663, \$37
See Section Y For Additional Books



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	ADJUSTABLE RANGE			MAX PRES*	SWITCH
		DECREASING	INCREASING	UNITS		
Compound Range (Units = inH₂O)						
PSW-681	\$95	2.75 to 200	2.75 to 200	inH ₂ O pressure	±20 psi	1 A
PSW-685	95	6.8 to 100	5.4 to 100	inH ₂ O vacuum	±20 psi	5 A

* Exceeding these values may cause a shift in the setpoint.

Comes complete with instruction sheet.

Ordering Example: PSW-685, pressure/vacuum switch with the ranges shown above and 5 A switch contact, \$95.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters