

MEDIUM TEMPERATURE HEATING TAPES

SRT Series
Starts at
\$49



- ✔ Maximum Exposure Temperature up to 230°C (450°F)
- ✔ Uniform Heat Distribution
- ✔ Moisture and Chemical Resistant
- ✔ Integrally Molded Separable Plug
- ✔ Available with Leads Same End†

SPECIFICATIONS

Heating Elements: 36-40 gage finely stranded resistance wire

Heating Elements Insulation: Double braided fiberglass yarn

Dielectric Strength: In excess of 2000V


Lead Wires: 16 AWG high temperature 600V silicone rubber insulated lead wire emerging from opposite ends of the heating tape into separate sides of integrally molded separable plug

OMEGALUX® silicone rubber extruded heating tapes are low-watt density electrical resistance heaters designed for temperature maintenance in applications requiring moisture and chemical resistance. Silicone rubber tapes are constructed of finely stranded resistance wires fully insulated with braided fiberglass and knitted into flat tape with fiberglass yarn. These tapes are encapsulated in a void-free silicone rubber sheath.


† To order heaters with power leads exiting the same end of the tape, add suffix “-LSE” to model number. Call Sales for pricing. To order 240V version change the “1” before the “-” in model number to “2”. All 240V versions are supplied without plugs. Call for sales prices.

APPLICATIONS

- ✔ Silicone rubber extruded heating tapes can be used in direct contact with a metal or conductive surface



Integrally molded separable plug shown.



SRT051-060, \$66, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

| To Order (Specify Model Number) | | | | | |
|---------------------------------|-------------------|-------|-----------------|-------------|-------|
| Watts | W/in ² | Volts | Size cm/m ("/') | Model No. | Price |
| 52 | 4.3 | 120 | 1/0.6 (1/2) | SRT051-020 | \$49 |
| 104 | 4.3 | 120 | 1/1.2 (1/4) | SRT051-040 | 55 |
| 156 | 4.3 | 120 | 1/1.8 (1/6) | SRT051-060 | 66 |
| 209 | 4.3 | 120 | 1/2.4 (1/8) | SRT051-080 | 77 |
| 261 | 4.3 | 120 | 1/3 (1/10) | SRT051-100 | 88 |
| 313 | 4.3 | 120 | 1/3.7 (1/12) | SRT051-120 | 79 |
| 104 | 4.3 | 120 | 2.5/0.6 (1/2) | SRT101-020 | 66 |
| 209 | 4.3 | 120 | 2.5/1.2 (1/4) | SRT101-040 | 82 |
| 313 | 4.3 | 120 | 2.5/1.8 (1/6) | SRT101-060 | 104 |
| 418 | 4.3 | 120 | 2.5/2.4 (1/8) | SRT101-080 | 120 |
| 522 | 4.3 | 120 | 2.5/3 (1/10) | SRT101-100 | 137 |
| 627 | 4.3 | 120 | 2.5/3.7 (1/12) | SRT101-120 | 147 |
| 731 | 4.3 | 120 | 2.5/3.7 (1/12) | SRT101-140 | 169 |
| 836 | 4.3 | 120 | 2.5/4.9 (1/16) | SRT101-160 | 180 |
| 940 | 4.3 | 120 | 2.5/5.5 (1/18) | SRT101-180 | 197 |
| 1045 | 4.3 | 120 | 2.5/6.1 (1/20) | SRT101-200 | 213 |
| 209 | 4.3 | 120 | 5/0.6 (2/2) | SRT201-020 | 88 |
| 418 | 4.3 | 120 | 5/1.2 (2/4) | SRT201-040 | 126 |
| 627 | 4.3 | 120 | 5/1.8 (2/6) | SRT201-060 | 175 |
| 836 | 4.3 | 120 | 5/2.4 (2/8) | SRT201-080 | 219 |
| 1045 | 4.3 | 120 | 5/3 (2/10) | SRT201-100 | 240 |
| 1254 | 4.3 | 120 | 5/3.7 (2/12) | SRT201-120* | 262 |
| 1463 | 4.3 | 120 | 5/4.3 (2/14) | SRT201-140* | 279 |
| 1672 | 4.3 | 120 | 5/4.9 (2/16) | SRT201-160* | 317 |
| 1881 | 4.3 | 120 | 5/5.5 (2/18) | SRT201-180* | 361 |
| 2090 | 4.3 | 120 | 5/6.1 (2/20) | SRT201-200* | 388 |

* Does not come with plug.

Comes complete with instruction sheet.

Ordering Examples: SRT051-060, 120V, 156 Watt, heating tape, \$66.

SRT051-040, 120V, 104 W heating tape, \$55.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters