

ACCELEROMETER POWER SUPPLIES/AMPLIFIERS BATTERY POWERED



ACC-PS1, \$205, shown smaller than actual size.

ACC-PS1
\$205



ACC-PS2, \$530, shown smaller than actual size.

ACC-PS2
\$530

- ✓ Amplifies Signal Up to 100x
- ✓ Rechargeable Battery Power with Charger Included
- ✓ High Performance, Single Channel

- ✓ Battery Powered
- ✓ High Performance, Single Channel
- ✓ Low Noise

OMEGA's ACC-PS1 is a battery-powered, single-channel, high-performance accelerometer power supply. Powered by two 9V batteries, it features low noise and a low-battery LED indicator.

OMEGA's ACC-PS2 is a low-noise, single-channel, high-performance accelerometer power supply/amplifier. It is powered by a rechargeable Ni-Cad battery with detachable charger (included). Features include a 3-position gain (for amplification of 1x, 10x, 100x), LED low-battery indicator, overlimit (clipping) indicator, and fault indicator. The rugged aluminum housing contains 4 easily accessible mounting holes with 121 x 44 mm (4.75 x 1.75") centers.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
MODEL NO.	PRICE	DESCRIPTION
ACC-PS1	\$205	Battery-powered, single-channel power supply
ACC-PS2	530	Rechargeable battery, single-channel power supply/amplifier
INTERFACE CABLES USED BETWEEN POWER SUPPLY AND INSTRUMENTATION		
MODEL NO.	PRICE	DESCRIPTION
ACC-CB4-15	\$65	4.6 m (15') coaxial cable (BNCM/BNCM)
ACC-CB5-2	35	0.6 m (2') coaxial cable (BNCM/banana plug)
ACC-CB6	15	178 mm (7") coaxial cable (BNCM/pigtail)

Note: See page K-18 for accessories.

Comes complete with operator's manual.

Ordering Example: ACC-PS2, with rechargeable battery and charger, single-channel power supply/amplifier, ACC-CB4-15, 4.6 m (15') coaxial interface cable, ACC102A, accelerometer, \$530 + 65 + 365 = **\$960**.

SPECIFICATIONS

	ACC-PS1	ACC-PS2
No. of Channels	1	1
Excitation Voltage (Vdc)	18	24
Excitation Current (mA)	2	2
Voltage Gain ($\pm 2\%$)	1x	1x, 10x, 100x
Output Signal FS Peak (Vdc)	10	10
Noise (mVrms) (0 to 10 kHz)	0.06	0.002
Input Power	(2) 9V battery	(3) 9V battery
Battery Life	80 hr	12 hr
Accel. Connector	BNC	BNC
Output Connector	BNC	BNC
Dimensions: mm (in)	133 x 66 x 44 (5.25 x 2.6 x 1.75)	66 x 43 x 135 (2.6 x 1.7 x 5.3)
Weight, g (oz)	31 (11)	70 (25)

ACCELEROMETER POWER SUPPLIES/AMPLIFIERS

AC POWERED, SINGLE CHANNEL, AND TRIAXIAL SUPPLY



ACC-PS3A
AC power supply,
\$475, shown smaller
than actual size.



ACC-PS4A, triaxial
supply, \$955, shown
smaller than actual size.

ACC-PS3A
\$475

ACC-PS4A
\$955

- ✓ AC Powered
- ✓ Low Cost
- ✓ High Performance, Single Channel
- ✓ Low Noise

See Section Y for a Selection of Scientific, Technical, and Reference Books Available from omega.com

OMEGA's ACC-PS3A is an AC-powered, single-channel, high-performance accelerometer power supply. This low-cost unit features low noise and a rugged aluminum housing with 4 easily accessible mounting holes on 121 x 44 mm (4.75 x 1.75") centers.

SPECIFICATIONS

	ACC-PS3A	ACC-PS4A
No. of Channels	1	3
Excitation Voltage (Vdc)	24	24
Excitation Current (mA)	2	2
Voltage Gain (±2%)	1x	1x
Output Signal FS Peak (Vdc)	10	10
Noise (mV rms) (0 to 10 kHz)	0.2	0.2
Input Power	115 Vac or 230 Vac	115 Vac or 230 Vac
Accel. Connector	BNC	4-pin female
Output Connector	BNC	BNC
Dimensions, mm (in)	102 x 51 x 76 (4 x 2 x 3)	135 x 43 x 66 (5.3 x 1.7 x 2.6)
Weight, g (oz)	624 (22)	624 (22)

- ✓ Powers All 3 Axes on Triaxial Accelerometer ACC301
- ✓ AC Powered

OMEGA's ACC-PS4A is an AC-powered, triaxial, high-performance power supply for use with the ACC301 triaxial accelerometer. It outputs the signal from all 3 axes. Along with low noise, this line-powered supply features a rugged aluminum housing with 4 easily accessible mounting holes on 121 x 44 mm (4.75 x 1.75") centers.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
ACC-PS3A	\$475	Single-channel power supply, 115 Vac power
ACC-PS4A*	955	Triaxial power supply, 115 Vac power

INTERFACE CABLES USED BETWEEN POWER SUPPLY AND INSTRUMENTATION		
MODEL NO.	PRICE	DESCRIPTION
ACC-CB4-15	\$65	4.6 m (15') coaxial cable (BNCM/BNCM)
ACC-CB5-2	35	0.6 m (2') coaxial cable (BNCM/banana plug)
ACC-CB6	15	178 mm (7") coaxial cable (BNCM/pigtail)

* For use with triaxial accelerometers only.

Note: See page K-18 for details on the above cable accessories. Comes complete with operator's manual.

Ordering Example: ACC-PS3A, 115 Vac powered single-channel power supply, \$475.

To order with 230 Vac power, add suffix "-230V" to model number, no additional charge.

To order without mounting feet, add suffix "-NMF" to model number, no additional charge.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters