

# INDUSTRIAL ACCELEROMETERS FOR HARSH ENVIRONMENTS

## 100 mV/g OUTPUT

### ACC102A

ACC102A  
**\$365**



- ✓ Ideal for Harsh Environments
- ✓ Hermetically Sealed
- ✓ Superior Low-Noise Floor for High Resolution
- ✓ Rugged Strain Relief on Integral Cable
- ✓ Fast Turn-On Time (1 s)
- ✓ High EMI Noise Rejection

The ACC102A accelerometer uses a shear mode design for high performance. It has a rugged, stainless steel inner structure covered by a molded polymer. This construction makes the ACC102 impervious to harsh environments, such as alkaline coolants, hot oil, and water sprays, resulting in long, reliable service. Additional features include high shock protection (to protect from dropping or mishandling), cross wire protection (protects against miswiring), and up to 1000-volt static discharge protection. The ACC102 has a high 100 mV/g output and measures across wide frequency and acceleration ranges. A low-impedance cable allows for runs up to 1000'. The ACC102 exhibits the low-noise floor and high-amplitude linearity one would expect in more expensive units.

#### SPECIFICATIONS

**Excitation:** 2 mA @ 24 to 30 Vdc, constant current (18 V supply can be used but will limit amplitude range)

**Rated Output:** 100 mV/g nominal at 100 Hz

**Frequency Range:** 3 Hz to 5 kHz (up to ±5% rated output shift)

**Amplitude Range:** ±40 g peak w/ACC-PS1, ±75 g peak w/ACC-PS2, ACC-PS3




ACC-PS1 power supply, \$205, shown smaller than actual size. See page K-16.

DP2000-F meter, \$310, shown smaller than actual size. See section D.

ACC102A, \$365, shown smaller than actual size.

- Amplitude Linearity:** 1% up to 65 g peak
- Temperature Range:** -40 to 82°C (-40 to 180°F)
- Temperature Sensitivity Effect:** -54 to 38°C (-65 to 100°F) ≤5% FS; 38 to 121°C (100 to 250°F) ≤8% FS
- Thermal Shock:** 1.2 g/°C
- Transverse Sensitivity:** 7% of axial max
- Maximum g Without Damage:** 5000 g peak
- Maximum g Without Clipping:** 75 g peak
- Mounted Resonance Frequency:** >23 kHz nominal
- Output Impedance:** 200 Ω nominal
- Bias Voltage:** 13 V nominal
- Base Strain:** 0.04 g/microstrain nominal
- Noise Floor (Wideband):** 0.0003 g (rms)
- Weight:** 50 g (1.8 oz) nominal (without cable)



- Material:**
  - Inner Housing:** 303 SS
  - Outer Jacket:** Non-conductive composite polymer
- Dimensions:** 2.16 H x 2.54 cm D (0.85 x 1.00")
- Connector:** 2.5 m (10') integral coaxial cable to BNCM
- Mounting:** 10-32 removable stud
- Mounting Torque Max:** 22 cm·kg (20 in·lb)

**MOST POPULAR MODELS HIGHLIGHTED!**

#### To Order (Specify Model Number)

MODEL NO.	PRICE	DESCRIPTION
ACC102A	\$365	Harsh-environment accelerometer

**Ordering Example:** ACC102A, accelerometer, ACC-CB16, coaxial cable, ACC-PS1, power supply, ACC-CB5-2, coaxial cable, \$365 + 50 + 205 + 35 = \$655.

**Note:** See pages K-20 through K-22 for details on the above power supplies and cables.

#### ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ME-1833	\$75	Reference Book: Vibration Fundamentals





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters