

DYNAMIC LOAD CELLS FOR HIGH-FREQUENCY TENSION/ COMPRESSION FORCE MEASUREMENTS

DLC101 Series

All Models
\$420



- ✓ Ideal for Measuring Impact or Pulsating Forces
- ✓ Frequency Range Up to 25 kHz
- ✓ Force Ranges Up to 5000 lb
- ✓ Calibration Certificate Supplied
- ✓ Stainless Steel Impact Cap and Mounting Stud Provided

OMEGA's DLC101 dynamic load cell is ideal for measuring force transients or dynamic force pulsations in impact or vibration applications. This load cell contains a thin piezoelectric crystal that generates an analog voltage signal in response to an applied dynamic force. The DLC101 has 2 threaded ends, enabling installation of threaded members such as mounting studs, impact caps, and machine elements. Its welded construction encloses and protects the crystals from the environment.


SPECIFICATIONS

Excitation: 2 mA nominal @ 18 to 30 Vdc, constant current
Rated Output: 5V nominal FS
Amplitude Linearity: ±1% FS (BSFL/0)
Resonant Frequency (@ No Load): 75 kHz
High Frequency Range: 25 kHz (approx. 1/3 of resonant frequency, no load)
Low Frequency Range (-3 dB): 0.08 Hz
Discharge Time Constant: 50 s (DLC101-10), 100 s (DLC101-50), 500 s (DLC 101-100), 2000 s (DLC101-500, -1K, -5K)
Maximum Compression: 200 lb (DLC101-10), 1000 lb (DLC101-50), 2000 lb (DLC101-100), 10,000 lb (DLC101-500), 15,000 lb (DLC101-1K), 15,000 lb (DLC101-5K)
Maximum Tension: 200 lb (DLC101-10), 500 lb (all ranges except 10 lb)
Stiffness: 11.4 lb/in


Overload Recovery: 10 m s for 2x range
Maximum Shock/Vibration: 10,000±5000 g (no load)
Temperature Range: -75 to 120°C (-100 to 250°F)
Temperature Sensitivity Effect: 0.03% FSPF
Output Impedance: 100 Ω
Bias Voltage: 10V nominal
Noise Floor (Wideband, RMS): 0.00014 lb (DLC101-10)
 0.0007 lb (DLC101-50)
 0.0014 lb (DLC101-100)
 0.007 lb (DLC101-500)
 0.014 lb (DLC101-1K)
 0.07 lb (DLC101-5K)
Weight: 43 g (1.5 oz) nominal
Material: 17-4 PH SS housing (RC 44)
Diameter of Top Force-Sensitive Surface: 13 mm (0.50")
Mounting Holes: 1/4-28 x 0.175" deep tapped hole



DLC101, cap and mounting stud, included.



DLC101, \$420.



Connector: Internal side coaxial, 10-32 male termination (cable sold separately; order ACC-CB2-10, \$55)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	COMPRESSION RANGE (lb)	TENSION
DLC101-10	\$420	0 to 10	0 to 10
DLC101-50	420	0 to 50	0 to 50
DLC101-100	420	0 to 100	0 to 100
DLC101-500	420	0 to 500	0 to 500
DLC101-1K	420	0 to 1000	0 to 500
DLC101-5K	420	0 to 5000	0 to 500
ACC-CB2-10	55	3 m (10') coaxial cable (10-32/BNCM) required	

Comes complete with impact cap, mounting stud, calibration certificate and operator's manual.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
ACC-PS1	\$205	Battery power supply/amplifier (BNC/F connections)
ACC-PS2	530	Battery power supply/amplifier (BNC/F connections)
ACC-PS3	525	AC power supply/amplifier (BNC/F connections)
INTERFACE CABLES USED BETWEEN POWER SUPPLY AND INSTRUMENTATION		
ACC-CB4-15	\$65	4.6 m (15') coaxial cable (BNCM/BNCM)
ACC-CB5-2	35	0.6 m (2') coaxial cable (BNCM/banana plug)
ACC-CB6	15	178 mm (7") coaxial cable (BNCM/pigtail)

Note: See pages K-16 through K-18 for details on the above accessories.

Ordering Example: DLC101-10, transducer, ACC-CB2-10, cable, ACC-PS1, power supply, ACC-CB6, BNCM/pigtail cable, \$420 + 55 + 205 + 15 = \$695.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters