

CURRENT TO PRESSURE (I/P) CONVERTER

IP210 Series
Control Air
3-15 to 3-120 psi

\$535
All Models



- ✓ Loop Powered
- ✓ Ideal for Pneumatic Control Systems
- ✓ IP65 Sealed Case
- ✓ Zero and Span Adjustments for Field Calibration
- ✓ Rugged Zinc-Cast Housing

A "current to pressure" converter (I/P) converts an analog signal (4 to 20 mA) to a proportional linear pneumatic output (3 to 15 psig). Its purpose is to translate the analog output from a control system into a precise, repeatable pressure value to control pneumatic actuators/operators, pneumatic valves, dampers, vanes, etc. The IP210 is a loop-powered instrument, which eliminates the need for an external power supply (except for IP210-X120).

Principle of Operation

OMEGA's IP210 converts an analog signal (4 to 20 mA) to a proportional linear pneumatic output (3 to 15 psig). Its uncomplicated design and proven electromagnetic force balance deliver consistently high performance.



IP210-X15, \$535,
shown actual size.

The IP210 provides a reliable, repeatable, accurate means of converting an electrical signal into pneumatic pressure. Its force balance principle is a coil suspended in a magnetic field on a flexible mount. At the lower end of the coil is a flapper valve that operates against a precision ground nozzle to create a backpressure on the servo diaphragm of a booster relay.


The input current flows in the coil and produces a force between the coil and the flapper valve, which controls the servo pressure and the output pressure.

Zero adjustment of the unit is made by turning a screw that regulates the distance between the flapper valve and the air nozzle. Span adjustment

is made by varying a potentiometer, which shunts input current past the coil. An integral volume flow booster provides adequate flow capacity, resulting in fast response time and accurate control.

See Section Y for a
Selection of Scientific,
Technical, and Reference
Books Available from
omega.com

LOOP-POWERED ELECTROPNEUMATIC CONTROL



SPECIFICATIONS

Accuracy: 0.5% FS
Supply Sensitivity: 0.025% span per % supply pressure change
Zero Adjustment: 5% FS
Span Adjustment: 20% FS
Operating Temp: -20 to 70°C (-5 to 160°F)
Compensated Temp: -10 to 60°C (15 to 140°F)
Thermal Effects: <0.1%/°C over operating range
Input Resistance: <300 Ω

Media: Oil-free, clean, dry air filtered to 25 μm
Recommended Supply Pressure: 25 to 30 psig (filtered air)
Max Supply Pressure: 80 psig (for IP210-X120: 135 psi)
Min Supply Pressure: 10 psi above maximum output pressure
Air Consumption (Leakage): 0.03 scfm
Flow Rate: 10 scfm ≤60 psi; 0.06 >60 psi
Response Time: <30 psi [less than 0.5 s (10 to 90% step); ≥30 psi: 2 s]

Failure Mode: Upon electrical failure, the signal pressure falls to bleed pressure
Pressure Port: ¼ FNPT
Electrical Connection: DIN 43650 with screw terminals included
Housing: IP65 rated, epoxy-painted zinc die castings
Construction: Nitrile diaphragms, stainless steel/nylon flapper, nozzle and supply valve, integral surface mounting bracket included
Weight: 1.7 kg (3 lb)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	INPUT RANGE	OUTPUT RANGE
IP210-X15	\$535	4 to 20 mA	3 to 15 psig
IP210-X30	535	4 to 20 mA	3 to 30 psig
IP210-X60	535	4 to 20 mA	3 to 60 psig
IP210-X120	535	4 to 20 mA*	3 to 120 psig

* 3-wire system. External 24 Vdc power supply required.
 Comes complete with operator's manual.

Ordering Examples: IP210-X15, I/P converter, takes a 4 to 20 mA control signal and converts it into 3 to 15 psig control air, \$535.
 IP210-X60, I/P converter, takes a 4 to 20 mA control signal and converts it into 3 to 60 psig control air, \$535.

Recommended Reference Book: Valve Handbook, GE-2317, \$135. Visit omega.com/bobi for Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters