

Large Display Meters

400B Series for Thermocouple, RTD, Thermistor, Voltage or Current Inputs



All models shown smaller than actual size.

400B Series
Starts at
\$439

- ✓ J, K, T, E, R, S or B Thermocouples
- ✓ 3- or 4-Wire Platinum RTDs
- ✓ Thermistor 700 Series
- ✓ Scalable Current and Voltage Inputs
- ✓ 1° Resolution



410B Series
Starts at
\$539

- ✓ Rugged Die-Cast Aluminum Case
- ✓ °F or °C Switchable
- ✓ 20 mm (0.8") Display (*bigger than conventional 14 mm (0.56") displays*)
- ✓ Modular Construction
- ✓ 0.1° Resolution



402B Series
Starts at
\$539

- ✓ 1° Resolution
- ✓ 5 Point Selector Switch



412B Series
Starts at
\$639

- ✓ 0.1° Resolution
- ✓ 5 Point Selector Switch



Thermocouple, RTD and Thermistor Single Input 400B and 410B Indicators

The 400B and 410B Series measure temperatures with laboratory accuracy. Signals from thermocouples, RTD's and thermistors can be displayed with 1°, 0.1° or 0.01° resolution. High instrument accuracy is achieved with a superior combination of low noise analog-to-digital conversion, multi-segment linearization conformity and isolated electronics. The standard resolution version, the 400B, has a 1° resolution. The higher resolution version, 410B, provides a 0.1° resolution. A miniature "DIP" switch, easily accessible behind the front panel, makes the °C to °F conversion a snap. You can add one option card to either the Model 400B or 410B.

Thermocouple Multi-Input 402B and 412B Indicators

The 402B and the 412B have multi-input boards that can switch between five inputs of a common input type (e.g., 5 Type K thermocouples). A row of five pushbutton switches, accessible on the front panel, permits easy switching between sensor readings. There are screw terminals located at the rear of the instrument where up to five sensors can be attached. The 402B has a standard 1° resolution. The 412B has a 0.1° resolution.

DC and Scaled DC 400B and 410B Indicators

For dc voltage single range indicators, the 400B and 410B provide exceptional accuracy and resolution for direct measurement of dc voltages. Ranges from 25 mV to 25 Vdc can be selected and measured with laboratory accuracy and repeatability. The 400B displays the voltage within -1000 to 2500 counts with 1-count accuracy. The 410B provides an additional decade of resolution from -10000 to 25000 and accuracy to 0.01% of reading. Both instruments offer exceptional 1-count repeatability.

Shown smaller than actual size.



405B
\$185

10 Point Selector
Switch for
Thermocouple
Inputs

For Additional Controllers, See Section P

Scaled dc Voltage and Current Loop Single Input 400B and 410B Indicators

The Models 400B and 410B display process parameters with laboratory accuracy. Signals from current transmitters, signal conditioners or other dc voltage sources can be scaled to display directly in engineering units.

Three types of input/display ranges are available. The I-1 range accepts 4 to 20 mA as its input and automatically scales and displays indicated results as 0.0 to 100% on the 400B (0.00 to 100.00% on the 410B). The decimal point position can be changed via programming, and various engineering unit labels are included. For user scalable, wide ranging displays from 4 to 20 mA inputs, select the I-3 range, or for 0 to 5 V, select the V5 range. Both provide the ability to scale and offset the instrument's display proportional to process engineering units.

dc Voltage Multi-Input 402B and 412B Indicators

Models 402B and 412B provide low cost measurement in applications where more than one voltage input is needed. Five front panel pushbuttons provide convenient selection between similar inputs. All channels must measure the same input range (e.g., -10 to 25 volts).

Scaled dc Voltage Multi-Input 402B and 412B Indicators

Models 402B and 412B can be specified with the V5 range to provide the ability to switch between five inputs of a commonly scaled voltage (e.g., all inputs accepting 1 to 5 Vdc inputs can be scaled to display 0 to 2500). A row of five pushbutton switches permits easy switching between input readings.

400B Series Digital Process Indicators

Specifications

Accuracy: See Range Specifications

Resolution: 400B, 402B and 403B:

1° range RTD and TC;

410B, 412B and 415B:

0.1° range RTD and TC

Repeatability:

R, S, B Ranges: ±0.2°C or °F

T Range < -130°C (-202°F):

±0.1°C (±0.2°F)

All Other Ranges: ±1 digit

Stability with Temperature:

Zero: 400B models: 1 µV/°C

410B models: 0.5 µV/°C

Span: 400B models: 0.01% rdg/°C;

410B models: 0.005% rdg/°C

Reference Junction: 0.05%

°C/°C, 10 to 40°C (50 to 104°F)

base metal types 0.05% °C/°C,

10 to 40°C (50 to 104°F) noble

metal types

Stability with Time:

No measurable drift

Noise Rejection:

NMR: >60 dB at 58 to 62 Hz,

>56 dB at 50 Hz 3 pole,

low pass filter with 6 Hz poles

CMR: >120 dB at 58 to 62 Hz,

> 110 dB at 50 Hz with 250 Ω

in balance

Operating Range:

Ambient Temperature: 0 to 50°C

(32 to 122°F); Temp rise inside

case is 5°C (9°F) typical

Ambient Humidity: 0 to 70% RH,

0 to 50°C (32 to 122°F) for rated

accuracy

Storage Temperature:

-40 to 60°C (-40 to 140°F)

Input Connections:

At rear of

indicator; four screw terminals on

3/8" centers

Power: 100 to 125 Vac or

190 to 250 Vac (switch selectable),

48 to 400 Hz, An 1.8 m (6')

detachable power cord is supplied

Display: 20.3 mm (0.8") high LEDs

Construction: Instrument case of

rugged die-cast aluminum with

textured vinyl paint

Instrument Size:

72 H x 144 W x 173 mm D

(2.84 x 5.67 x 6.82")

Panel cutout: 68 x 138 mm

(2.68 x 5.44")

Weight: Net: 1.13 kg (2.5 lb)

Shipping: 1.36 kg (3.0 lb)



ACTUAL SIZE!

Temperature Input Types and Ranges

Input Code	Designation	Add'l Price	Temperature Range	Accuracy (±)	
				400B/402B 1° Resolution	410B/412B 0.1° Resolution
J	Iron-Constantan	N/C	-328 to 1712°F	1°F	0.6°F
			-200 to 933°C	1°C	0.5°C
K	CHROMEGA® ALOMEGA®	N/C	-208 to 2552°F	1.5° below 0°, 1° above 0°F	1.2° below 0°, 0.8° above 0°F
			-133 to 1400°C	1°C	0.8° below 0°, 0.5° above 0°C
T	Copper-Constantan	N/C	-328 to 752°F	2° below 0°, 1° above 0°F	1.5° below 0°, 0.6° above 0°F
			-200 to 400°C	1°C	1.0° below 0°, 0.4° above 0°C
E	CHROMEGA®-Constantan	N/C	-328 to 1952°F	1°F	0.7°F
			-200 to 1066°C	1°C	0.4°C
R	Pt-Pt13% Rh	N/C	32 to 3252°F	3° below 350°, 2° above 350°F	2° below 200°, 1° above 200°F
			0 to 1788°C	2°C	3° below 350°, 1.5° above 350°C
S	Pt-Pt10% Rh	N/C	32 to 3252°F	3° below 600°, 2° above 600°F	2° below 315°, 1° above 315°F
			0 to 1788°C	2°C	3° below 600°, 1.5° above 600°C
B	Pt30%-Rh	N/C	912 to 3392°F	4°F	2.5°F
			489 to 1867°C	2.5°C	1°C
PT3	0.00385	N/C	-388 to 1632°F	1°F	0.7° below -328°, 0.4° above -328°F
			-233 to 888°C	1°C	0.3 below -200°, 0.2 above 200°C
PT4	0.00385	N/C	-388 to 1632°F	1° F	0.7° below -328°, 0.4° above -328°F
			-233 to 888°C	1°C	0.3 below -200°, 0.2 above -200°C

DC Voltage Input Types and Ranges

Input Code	Add'l Price	Input Range	STD Resolution (400B custom order)	High Resolution (410B)
V1	N/C	10.000 to 25.000 mV	10 μ V	1 μ V
V2	N/C	-100.0 to 250.0 mV	100 μ V	10 μ V
V3	N/C	-1.000 to 2.500V	1 mV	100 μ V
V4	N/C	-10.00 to 25.00V	10 mV	1 mV
V5	\$70	0 to 5 Vdc (display adjustable for engineering units)	Adj 2500 counts	Adj 25,000 counts

Current Input Types and Ranges

Input Code	Add'l Price	Input Type	Display Range	Accuracy (all \pm)	
				400B	410B
I-1	N/C	4 to 20 mA transducer current transmitter	Fixed scale 0 to 100%	400B Resolution 0.1% rdg 410B Resolution 0.01% rdg	1 count 0.01% of reading \pm count
I-3	\$70	4 to 20 mA transducer current transmitter	Adjustable scaling to engineering units 400B Resolution -1000 to 2500 (100 ct minimum) 410B Resolution -10000 to 25000 (1000 ct min.)		\pm 5 counts \pm 50 counts

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
400B-TC	\$439	J, K, T, E, R, S, B selectable input, 1° resolution °F/°C
400B-CV	439	4 to 20 mA or 0 to 5 V input
402B-TC	539	J, K, T, E, R, S, B selectable input, 1° resolution °F/°C, 5-channel switch
402B-CV	539	4 to 20 mA or 0 to 5V input, 5-channel switch
405B	185	10-point selector switch for thermocouple input 400B and 410B models
410B-(*)	539	0.1° resolution, °F or °C switchable
412B-(*)	639	0.1° resolution, °F or °C switchable, 5-channel selector switch

* Insert input code from one of the input and range tables.

OMEGACARESM extended warranty program is available for models shown on this page.

Ordering Example: 400B-TC, indicator for various thermocouple inputs, \$439.

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$109), \$439 + 109 = \$548.


4128B-TC, indicator for various thermocouple inputs, \$639.



OMEGACARESM covers parts, labor, and equivalent loaners. Ask your sales representative for full details when placing an order.

410B, \$539, shown smaller than actual size.

GEQSS-14G-12 low noise thermocouple probe, \$30, shown smaller than actual size, sold separately, see page A-54.



M-60





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters