

HIGH- AND VERY-HIGH-TEMPERATURE PRESSURE TRANSDUCERS

PX1004/PX1009 Series

mV/V Output

0-15 to 0-10,000 psi

0-1 to 0-700 bar

1 bar = 14.5 psi

1 kg/cm² = 14.22 psi

1 atmosphere = 14.7 psi = 29.93

inHg = 760.2 mmHg = 1.014 bar

Starts at
\$1850

- ✓ Two Versions That Operate from -54 to 232°C (-65 to 450°F) (PX1004) or -54 to 343°C (-65 to 650°F) (PX1009)
- ✓ High Performance
- ✓ Proven High Reliability
- ✓ Exceptional Calibration Stability


Applications

- ✓ Engine and Test Stands
- ✓ High-Temperature Testing
- ✓ Process Monitoring
- ✓ Ground Support Equipment
- ✓ High-Temperature Geothermal Generators

OMEGA's PX1004 and PX1009 sputtered thin-film pressure transducers are designed for high-temperature service. These instruments can operate in temperatures from -54 to 232°C or 343°C (-65 to 450°F or 650°F).

Yet even in these extreme temperatures, they provide outstanding accuracy, long-term calibration stability, and reliability. Static accuracy is ±0.25%, and thermal zero and sensitivity shifts over their compensated ranges are less than ±0.01%/°F.

PX1009L0-1KAV, \$2500, shown actual size.



PX1004L1-1KAV, \$1850, shown actual size.



Standard

OMEGA's thin-film technology makes this premium performance possible. The strain gages are sputter-deposited, forming a molecular bond with the substrate. There is virtually no shift, drift, or creep to cause the transducer's calibration to change. The all-welded stainless steel pressure cavity and double-isolated case ensure pressure integrity and reliability in adverse environments.

These high-temperature transducers are available in many standard ranges from 15 psi to 10,000 psi. A NIST-traceable calibration record is available for these units.

SPECIFICATIONS

Excitation: 10 Vdc

Full Range Output:

30 mV nominal, 26 mV minimum

Residual Unbalance:

0 mV ±5% FSO at zero pressure

Input Resistance: 400 Ω nominal

Output Resistance: 400 Ω nominal

Insulation Resistance:

PX1004: 100 MΩ or greater @ 45 Vdc

PX1009: 50 MΩ or greater @ 45 Vdc

Electrical Connections:

PX1004: PCIH0-10-6P or equivalent

PX1009: Color-coded pigtail leads, 0.8 m (30") long, minimum

Sensing Element:

4-active-arm bridge using sputter-deposited thin-film elements.

Accuracy: Combined linearity, hysteresis and repeatability: ±0.25% FSO, BSL (over the compensated temperature range)

[Note: Performance is determined at 25°C ±1°C (77°F ±2°F), open circuit, rated excitation, unless otherwise specified]

Operating Temp Range:


PX1004: -54 to 232°C (-65 to 450°F)

PX1009: -54 to 343°C (-65 to 650°F)

Compensated Temp Range:

PX1004: 24 to 204°C (75 to 400°F)

PX1009: 24 to 316°C (75 to 600°F)



HIGH AND VERY HIGH TEMPERATURE PRESSURE TRANSDUCERS



MILLIVOLT OUTPUT
PRESSURE TRANSDUCERS

B

Thermal Effects:

Span: ±0.01% FSO/°F
Zero: ±0.01% FSO/°F

Natural Frequency:

50 kHz at 5000 psi decreasing logarithmically to 5 kHz at 15 psi

Vibration Sensitivity: At 35 g peak from 10 Hz to 2000 Hz (limited to ½" D.A.), the output shall not exceed:

	PX1004	PX1009
15 psi	0.04% FSO/g	0.15% FSO/g
50 psi	0.02% FSO/g	0.07% FSO/g
100 psi	0.015% FSO/g	0.05% FSO/g
500 psi	0.006% FSO/g	0.02% FSO/g
1000 psi	0.003% FSO/g	0.02% FSO/g

Shock: 100 g, 11 ms half sine wave without calibration shift or damage

Humidity:

Per MIL-STD-810, Method 507.1
Standard ranges: 0 to 15, 25, 50, 100, 250, 500, 1000, 1500, 2000, 2500, 5000 and 10,000 psia. Sealed gage available in ranges of 100 psi and above.

Proof Pressure:

PX1004: 200% of rated pressure
PX1009: 150% of rated pressure

Burst Pressure:

PX1004: 300% of rated pressure
PX1009: 200% of rated pressure

Wetted Parts: 17-4 PH vacuum melt or 15-5 stainless steel

Pressure Fitting:


¼"-20 male per MS33656-4

Mounting Isolation: Case isolation ensures that the sensing element will not be affected by external stresses

Mating Connector (PX1004):

PCS06E-10-6S(SR) (sold separately)

Weight: 145 g (5 oz) maximum



PX1004 Mating Connector
PCS06E-10-6S(SR)
\$135

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

RANGE	MODEL NO. PX1004	PRICE	MODEL NO. PX1009	PRICE	COMPATIBLE METERS*	
ABSOLUTE PRESSURE (All Ranges Available in Sealed Gage Pressure)						
0 to 15 psi	0 to 1.0 bar	PX1004L1-015AV	\$1850	PX1009L0-015AV	\$2500	DP41-S, DP25B-S
0 to 25 psi	0 to 1.7 bar	PX1004L1-025AV	1850	PX1009L0-025AV	2500	DP41-S, DP25B-S
0 to 50 psi	0 to 3.4 bar	PX1004L1-050AV	1850	PX1009L0-050AV	2500	DP41-S, DP25B-S
0 to 100 psi	0 to 6.9 bar	PX1004L1-100AV	1850	PX1009L0-100AV	2500	DP41-S, DP25B-S
0 to 250 psi	0 to 17.2 bar	PX1004L1-250AV	1850	PX1009L0-250AV	2500	DP41-S, DP25B-S
0 to 500 psi	0 to 34.5 bar	PX1004L1-500AV	1850	PX1009L0-500AV	2500	DP41-S, DP25B-S
0 to 1000 psi	0 to 68.9 bar	PX1004L1-1KAV	1850	PX1009L0-1KAV	2500	DP41-S, DP25B-S
0 to 1500 psi	0 to 103 bar	PX1004L1-1.5KAV	1850	PX1009L0-1.5KAV	2500	DP41-S, DP25B-S
0 to 2000 psi	0 to 138 bar	PX1004L1-2KAV	1850	PX1009L0-2KAV	2500	DP41-S, DP25B-S
0 to 2500 psi	0 to 172 bar	PX1004L1-2.5KAV	1850	PX1009L0-2.5KAV	2500	DP41-S, DP25B-S
0 to 5000 psi	0 to 345 bar	PX1004L1-5KAV	1850	PX1009L0-5KAV	2500	DP41-S, DP25B-S
0 to 10,000 psi	0 to 689 bar	PX1004L1-10KAV	1850	PX1009L0-10KAV	2500	DP41-S, DP25B-S

Comes complete with 5-point calibration.

* See section D for compatible meters.

Metric ranges available – Consult Engineering.

To order sealed gage pressure, replace "A" in model number with "S" (no extra charge).

Ordering Examples: **PX1004L1-100AV**, 100 psi absolute pressure transducer with male pressure connection per MS33656-4 and PCH10-10-6P electrical connector, **\$1850**. **PCS06E-10-6S(SR)**, mating connector (sold separately), **\$135**. **PX1009L0-1KSV**, 1000 psi sealed gage pressure transducer with MS33656-4 male pressure connection and 0.8 m (30") high-temperature cable, **\$2500**.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
PCS06E-10-6S(SR)	\$135	Mating connector for PX1004 transducers

CUSTOM CONFIGURATIONS

PRESSURE PORT SERIES	ELECTRICAL CONNECTION [2]	RANGE [3]	UNITS [4]	OUTPUT [5]	OPTIONS [6]
L = MS33656-4		015 psi	A	V = mV/V Output	CAL11 = 11-point NIST-traceable calibration
		025	A	Base Price PX1004:	+ \$250
		050	A	\$1850	
		100	A, S	Base Price PX1009:	
		250	A, S	\$2500	
PX1004 only 1 = PCH10-10-6P	Connector (or equal).	500	A, S		
	Mating connector	1K	A, S		
	(sold separately), order	1.5K	A, S		
	PCS06E-10-6S(SR)	2K	A, S		
	\$135.	2.5K	A, S		
PX1009 only 0 = color-coded	cable, 0.8 m (30") min.	5K	A, S		
		10K	A, S		

Metric ranges available – Consult Engineering.

To order a custom configuration:

1. Select a pressure port
2. Select electrical connection
3. Select a pressure range
4. Select pressure units
5. Select output
6. Select options and agency approvals

Ordering Examples: **PX1004L1-100AV**, MS33656-4 male pressure port, twist-lock connector, 100 psi absolute pressure range and mV/V output, **\$1850**. **PCS06E-10-6S(SR)**, mating connector (sold separately), **\$135**. **PX1004L1-015SV**, MS33656-4 male pressure port, twist-lock connector, 15 psi sealed gage pressure range and mV/V output, **\$1850**. **PCS06E-10-6S(SR)**, mating connector (sold separately), **\$135**. **PX1009L1-1KSV-CAL11**, MS33656-4 male pressure port, 0.8 m (30") high-temperature cable, 1000 psi sealed gage pressure range, mV/V output and optional 11-point NIST-traceable calibration, **\$2500 + 250 = \$2750**.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters