

# RTD Thermometers

## High Accuracy

- ✓ Comes with NIST Traceability Certificate (No Points)
- ✓ 3- and 4-wire RTDs
- ✓ High Accuracy
- ✓ 0.1° and 1° Resolution
- ✓ Compact and Rugged
- ✓ DIN 43760 Standard

### Specifications

**Sensor:** 3- or 4-wire 100 Ω Platinum RTD  $\alpha=0.00385$

**Accuracy:** Includes DIN 43760 conformity (no points), repeatability, temperature coefficient (18 to 28°C ambient), time stability (1 year) and errors with up to 50 Ω of resistance in each lead; excluded probe errors

**Repeatability:** Less than 0.2°F typical for one week at constant ambient temperature

**Temperature Coefficient:**

18 to 28°C (64 to 82°F); included in accuracy specification; less than 18°C (64°F) or greater than 28°C (82°F) less than  $\pm(0.015^\circ\text{C})/^\circ\text{C}$

**Maximum Lead Resistance:**

4-wire: 50 Ω max; 3-wire: 10 Ω max

**Display:** 3½ digit LCD, 13 mm (0.5") height; polarity, decimal point, open sensor and overrange indication

**Reading Rate:** 1.5 per second

**Battery Life:** 500 hours typical, with 9V alkaline battery (included)

**Battery Indicator:**

Display reads "LO BAT" when less than 10% of life remains

**Linearization:** Ratiometric dual-slope A/D with continuous linearization

**Mating Connection:** OMEGA® series T instrumentation connectors (model TA4F and TA4FL), see section G

**Environmental Limits:** Operating: -10 to 50°C (14 to 122°F), less than 80% RH, up to 35°C

**Storage:** -35 to 60°C (-31 to 140°F), less than 90% RH, up to 35°C

**Maximum Common Mode Voltage:** 42V peak

**Temperature Settings**

**Model 868F**

**200°F:**

**Range:** -199.0 to -100.1°F;

-199.0 to -100.1°F

**Resolution:** 0.1°F

**Accuracy:**  $\pm 1.0^\circ\text{F}$ ;  $\pm 0.4^\circ\text{F}$

**1100°F:**

**Range:** -100 to +1100°F;

-360 to -101°F

**Resolution:** 1°F

**Accuracy:**  $\pm 2^\circ\text{F}$ ;  $\pm 4^\circ\text{F}$

868F/869C  
**\$310**

869C, \$310, shown smaller than actual size.

TA4F connector provided with each unit.

**Model 869C**

**200°C:**

**Range:** -100.0 to +199.9°C;

-199.0 to -100.1°C

**Resolution:** 0.1°C

**Accuracy:**  $\pm 0.3^\circ\text{C}$ ;  $\pm 1.5^\circ\text{C}$

**1100°C:**

**Range:** -100 to 630°C;

-220 to +101°C

**Resolution:** 1°C

**Accuracy:**  $\pm 1^\circ\text{C}$ ;  $\pm 2^\circ\text{C}$

**Dimensions:** 160 H x 69 W x 31 D mm (6.3 x 2.7 x 1.2")

**Net Weight:** 210 g (7.5 oz)

See OMEGA's Complete Line of RTD Probes and Handles in Section C



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your Sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
868F	\$310	RTD Thermometer (Fahrenheit)
869C	310	RTD Thermometer (Celsius)

Accessories		
Model No.	Price	Description
SC-800	\$10	Soft carrying case
TA4F	7	Series T 4-wire connector (1 supplied)
MN1604	3	9V alkaline battery
OT-201-1/2	5	High thermal conductivity paste for fast surface measurements, ½ oz jar
CAL-3-HH	75	NIST-traceable calibration with points

Comes complete with 9V alkaline battery, NIST traceable calibration certificate (no points), operator's manual, mating input connector (TA4F).  
**Ordering Example:** 868F, RTD thermometer, with fahrenheit readout, \$310. OCW-3, OMEGACARE<sup>SM</sup> extends standard 1-year warranty to a total of 4 years (\$77) \$310 + 77 = \$387.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters