

# 483 mm (19") Jack Panels

## Standard Connectors with Anodized Panels

19SJP Series  
Starts at  
**\$67.50**



### 483 mm (19") Plain Panel Jacks

No. of Rows	Panel Height	Max. No. of Jacks
1	89 mm (3½")	22
2	133 mm (5¼")	44
3	178 mm (7")	66
4	222 mm (8¾")	88


### 483 mm (19") Jack Panels with Switch Cutout

No. of Rows	Panel Height	Switch Size	Max. No. of Jacks
1	133 mm (5¼")	76 mm (3")	15
2	133 mm (5¼")	76 mm (3")	30
2	178 mm (7")	127 mm (5")	30
3	178 mm (7")	127 mm (5")	45
4	222 mm (8¾")	127 mm (5")	60

**Note:** When a switch is ordered with a panel, installation is included at no extra charge, add suffix "-MTG" to model number of switch or meter. Panels with switches and/or meters are not supplied wired. Wiring charge is \$5 per circuit. Consult factory for details.

**Note:** Panels with switches and/or meters are not supplied wired. Wiring charge is \$5 per circuit. Consult factory for details. Patented dust caps are, included free with each panel.

Shown smaller than actual size



OSW3, \$95, see page G-71

**Custom Panels Available! Contact Sales**

Switches and Meter Sold Separately.

OSW3, \$95, see page G-71

DPi8C, \$285, ½ DIN ultra compact meter, see page M-17

### **MOST POPULAR MODELS HIGHLIGHTED!**

Model No. ANSI Color Code	Price*	Total No. of Jacks	Switch Cutout	Meter Cutout
19SJP1-10-(*)	\$67.50	10	—	—
19SJP1-20-(*)	101.50	20	—	—
19SJP2-20-(*)	106.50	20	—	—
19SJP2-28-(*)	131.08	28	—	—
19SJP2-30-(*)	138.38	30	—	—
19SJP3-30-(*)	143.30	30	—	—
19SJP4-40-(*)	184.50	40	—	—
19SJP1-10-(*)-OSW	77.50	10	76 mm (3")	—
19SJP3-30-(*)-OSW	148.38	30	127 mm (5")	—
19SJP4-40-(*)-OSW	189.50	40	127 mm (5")	—
19SJP1-10-(*)-OSW-MTR	82.50	10	76 mm (3")	Y
19SJP3-30-(*)-OSW-MTR	158.38	30	127 mm (5")	Y
19SJP4-40-(*)-OSW-MTR	189.50	40	127 mm (5")	Y

\*Insert Calibration Code J, K, T, E, R, S, U or N calibrations; For types G, C or D, Consult Sales for pricing information. Other variations available. Dust caps included.

**Ordering Example:** 19SJP1-10-K, 483 L x 89 mm H (19 L x 3.5" H) jack panel with 1-row of 10 Type K calibration snap-in jack panels with the universal "fits all" female connector design, \$67.50.

Consult Sales for custom color-coded anodized panels

### 483 mm (19") Jack Panels with Switch and Meter Cutouts

No. of Rows	Panel Height	Switch Size	Max. No. of Jacks
1	133 (5¼")	76 (3")	10
2	133 (5¼")	76 (3")	20
2	178 (7")	127 (5")	20
3	222 (8¾")	127 (5")	40
4	222 (8¾")	127 (5")	40

**Note:** A ½ DIN (45 x 92 mm) meter cutout is supplied unless otherwise specified.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters