

Unique Surface Probes

ANSI color code shown
To order IEC color code see page A-9

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Model No. 88222(*)

\$120

Right-angle probe ideal for measuring moving or rotating surfaces. Can be used in paper, fiber, printing, iron and steel industries. Max. surface temperature of 250°C (480°F).
(Replaceable Element supplied free, for additional elements order Model No. 88222()-RE, \$25.)*

Model No. 88223(*)

\$120

Surface probe designed for measuring moving or rotating surfaces. Ideal for surfaces perpendicular to the probe handle. Max. surface temperature of 250°C (480°F).
(Replaceable Element supplied free, for additional elements order Model No. 88223()-RE, \$25.)*



PATENTED
Covered by U.S. and International patents and pending applications.

Model No. 88221(*)

\$120

Model No. 98221(*)


\$140

with Swivel Head

Ideal for measurements of moving or stationary flat, smooth surfaces. Max. surface temperature of 250°C (480°F) allows for use on both metal and plastic surfaces. Surface velocity of moving surfaces should not exceed 90 meters (300 ft.) per minute.

(Replaceable Element supplied free, for additional elements order Model No. 88221()-RE, \$25.)*

Model 98221K shown



TAS adaptor

All models supplied with molded SMP or SMPW subminiature male connector and TAS adaptor.

See Following Pages for Dimensions

Unique Swivel Head Design Available 98000 Probes

Model No. 88220(*)

\$135


Model No. 98220(*)

\$155

with Swivel Head

Ideal for measuring the temperature of rollers 100 to 152 mm (4 to 6") in diameter, with velocities to 61 meters (200') per minute. Max. surface temperature of 250°C (480°F).

(Replaceable Element supplied free, for additional elements order Model No. 88220()-RE, \$25.)*




Head Rotates 180° and Swivels

Ordering Example: 98220E, Type E (CHROMEGA®-Constantan) Surface probe with swivel head, rated to 250°C (480°F), \$155. 88222K, Type K (CHROMEGA®-ALOMEGA) Right-angle surface probe, rated to 250°C (480°F), \$120.

PATENTED

Covered by U.S and International patents and pending applications



TAS adaptor

All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.

ALL MODELS AVAILABLE FOR FAST DELIVERY!

ANSI color code shown	To order IEC color code see page A-9
-----------------------	--------------------------------------

Model No. 88226(*)
\$135

Model No. 98226(*)
\$155

with Swivel Head

Right-angle probe for rotating rollers of 152 to 300 mm (6 to 12") in diameter. 61 meters (200') per minute max. velocity, with 250°C (480°F) max. surface temperature.

(Replaceable Element supplied free, for additional elements order Model No. 88226()-RE, \$25.)*

***Specify Calibration:**
K: CHROME[®]GA[®]-ALOMEGA[®]
E: CHROME[®]GA[®]-Constantan

Model No. 98225(*)
\$155
with Swivel Head

Right-angle probe for rotating rollers of 300 to 584 mm (12 to 23") in diameter. 30 meters (100') per minute max. velocity, with 250°C (480°F) max. surface temperature.

(Replaceable Element supplied free, for additional elements order Model No. 88225()-RE, \$25.)*

Model No. 88225(*)
\$135

Model No. 88224(*)
\$120

Right-angle probe for rotating rollers from 100 to 152 mm (4 to 6") in diameter. Max. surface temperature of 250°C (480°F).

(Replaceable Element supplied free, or additional elements, order Model No. 88224()-RE, \$25.)*

Model No. 88227(*)
\$120

Model No. 98227(*)
\$140
with Swivel Head

For surface measurements with end braces to minimize flexing due to a moving surface; this also prolongs probe life. PFA sliders ensure smooth operation on both metal and plastic surfaces. 61 meters (200') per minute max. velocity, 250°C (480°F) max. surface temperature.

Ordering Example: 98227K is a model 98227 swivel head surface probe in Type K thermocouple, \$140.

(Replaceable Element supplied free, for additional elements order Model No. 88227()-RE, \$25.)*

Probes not designed for long term exposures to high temperatures.

Head Rotates 180° and Swivels



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters