

ANSI  
color  
code  
shown

To order  
IEC color  
code see  
page A-9



# Unique Surface Probes

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

**PATENTED**

*Covered by U.S and  
International patents and  
pending applications*

**Model No. 88106(\*)**

**\$190**

Right-angle probe for fast response times. Sheath length is 102 mm (4"). Max. surface temperature is 760°C (1400°F).

*Replaceable Element  
not supplied, order  
Model No. 88106(\*)-RE, \$25.*

**Model No. 88107(\*)**

**\$200**

Right-angle, long reach probe with fast response design. Sheath length is 203 mm (8"), with 760°C (1400°F) max. surface temperature.

*Replaceable Element  
not supplied, order  
Model No. 88107(\*)-RE, \$25.*

**Model No. 88108(\*)**

**\$205**

Right-angle, long 300 mm (12") reach probe with fast response design. 760°C (1400°F) max. surface temperature.

*Replaceable Element  
not supplied, order  
Model No. 88108(\*)-RE, \$25.*

**Model No.  
88010(\*)**

**\$175**

Long, 300 mm (12") reach version of the 88006. Fast response design with 760°C (1400°F) max. surface temperature for use in oven and furnaces.

*Replaceable Element not supplied,  
order Model No. 88010(\*)-RE, \$25.*



**TAS adaptor**

All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.

**\* Specify Calibration:**

**K: CHROMECA®-ALOMEGA®**

**E: CHROMECA®-Constantan**



**For Temperatures  
up to 760° C (1400°F)**

**See Following Pages  
for Dimensions**

**Ordering Example:**  
**88018K** is a Type K surface  
probe, \$205.

ANSI color code shown  
To order IEC color code see page A-9



Model No. 88007(\*)

\$110

Miniature, fast response probe. Ideal for measuring the surface temperature of small electronic parts. 250°C (480°F) max. surface temperature.

Replaceable Element supplied free, for additional elements order Model No. 88007(\*)-RE, \$25.

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

Model No. 88006(\*)


\$115

Miniature, fast response probe with 480°C (900°F) max. surface temperature. Ideal for surface temperatures of small electronic parts.

Replaceable Element not supplied, Model No. 88006(\*)-RE, \$25.

**PATENTED**

Covered by U.S and International patents and pending applications



TAS adaptor

All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.

Model No. 88016(\*)

\$160

High temperature, right-angle probe, with miniature pencil type head. Best suited to stationary surfaces, with sensing head parallel to the handle. 480°C (900°F) max. surface temperature.

Replaceable Element not supplied, order Model No. 88016(\*)-RE, \$25.



Miniature Connector




Model No. 88026(\*)

\$150

High temperature, right-angle probe, with miniature pencil type head. Best suited to stationary surfaces, with sensing head perpendicular to the handle. 480°C (900°F) max. surface temperature.

Replaceable Element not supplied, order Model No. 88026(\*)-RE, \$25.



**PATENTED**

Model No. 88007K and replaceable element, Model No. 88007K-RE.

\* Specify calibration: K - Type K Thermocouple E - Type E Thermocouple  
Ordering Example: 88007K probe with type K Thermocouple, \$110.

**Replaceable Element Design**

**Customer Replaceable Element:** probe is supplied with one additional element.

**Factory Replaceable Element:** OMEGA® can install replaceable elements and check the probe for \$50, with the first replacement free! For non-replaceable element probes, replacement probes are available with a one time trade-in discount. Please contact our Customer Service Department for details.

To order Replaceable Elements, add suffix "-RE" to model no., \$25 each.

Ordering Example: 88026K-RE for 88026K probe.

\*Insert calibration needed, e.g. K (Type K thermocouple).



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters