



Unique Surface Probes

PATENTED

Covered by U.S. and International patents and pending applications.

Model No. 88203(*)

\$165

Model No. 98203(*)

\$185

with Swivel Head

For rotating, smooth metallic surfaces of 229 to 610 mm (9 to 24") in diameter. 90 m (300') per minute max surface velocity. Max surface temperature of 205°C (400°F).

Replaceable Element supplied free, for additional elements order Model No. 88203(*)-RE, \$25.

Model No. 88201(*)

\$190

Model No. 98201(*)

\$210

with Swivel Head

A roller-surface probe, for use on moving or rotating, smooth surfaces with a velocity up to 61 m (200') per minute. Max surface temperature of 205°C (400°F).

Replaceable Element supplied free, for additional elements order Model No. 88201(*)-RE, \$25.

Model No. 88202(*)

\$160

Model No. 98202(*)


\$180

with Swivel Head

A roller-surface probe, ideal for measuring outside wall temperatures of smooth plastic or steel piping. Can be used on moving or rotating surfaces of 559 to 1524 mm (22 to 60") in diameter, with 90 m (300') per minute max. surface velocity. Max surface temperature of 205°C (400°F).

Replaceable Element supplied free, for additional elements order Model No. 88202(*)-RE, \$25.

Ordering Example: 98201K, style 98201 swivel head roller surface probe in Type K thermocouple, \$210.




TAS adaptor

All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.

See pages A-109 to A-110 for dimensions.

* Specify Calibration:
K: CHROMEGA®-ALOMEGA®
E: CHROMEGA®-Constantan





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters