


Unique Surface/Insertion Probes

88000 Series



All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.

Model No. 88008(*)

\$115

Micro-sensor probe, designed for precise measurements of small surface areas, such as transistors and integrated circuits. Small contact surface area of 1.0 x 3.0 mm (0.040 x 0.118") for fast response. 400°C (750°F) max surface temperature.

Note: element not replaceable.

PATENTED

Covered by U.S. and International patents and pending applications.

Model No. 88014(*)

\$115

Right angle version of the 88013. Fast-response spring-loaded compact tip probe, for measurements to 815°C (1500°F). Surface pad made from 400 series stainless steel. 4.75 mm dia. (0.187") surface area. Not designed for long-term exposure to high temperatures.

Note: element not replaceable.

Model No. 88104(*)

\$115

Right angle version of the 88008, with unique lateral spring design and small contact surface area. 400°C (750°F) max surface temperature.

Note: element not replaceable.

AVAILABLE FOR FAST DELIVERY!

See pages A-109 to A-110 for dimensions.

All models shown smaller than actual size.

Model No. 88013(*)

\$110

Fast-response spring-loaded compact tip probe, for measurements to 815°C (1500°F). Surface pad made from 400 series stainless steel. 4.75 mm dia. (0.187") surface area. Not designed for long-term exposure to high temperatures. *Note: element not replaceable.*

Model No. 88307(*)

\$80

Longer version of the 88306, with 300 mm (12") sheath.

Note: element not replaceable.

Model No. 88305(*)

\$70

Measure temperatures in moving air, with drilled sheath to protect the thermocouple, while exposing it to air flow. 0.5 to 20 second response time (depending on air velocity). 480°C (900°F) max service temperature.

Note: element not replaceable.

* Specify Calibration K or E.



Model No. 88306(*)

\$80

Pointed tip design, ideal for measuring soft and semi-frozen material, molten plastics and rubbers. 102 mm (4") sheath, with 6 to 20 sec. response time. 500°C (930°F) max service temperature.

Note: element not replaceable.

All models shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

PATENTED

Covered by U.S. and International patents and pending applications.

See pages A-109 to A-110 for Dimensions.

Model No. 88308(*)

\$65

Specially designed fine hypodermic needle probe, least likely to disturb the surrounding insertion area. 6 to 20 second response time, 205°C (400°F) max service temperature.

Note: element not replaceable.

Model No. 88301(*)

\$80

Suitable for measuring internal temperatures of semi-solid materials, such as rubbers, plastics, clay, etc., as well as for liquid measurements. Tapered stainless steel sheath with 480°C (900°F) max service temperature.


Note: element not replaceable.

Model No. 88009(*)

\$115

Thin-body type probe designed to measure the surface of the bottom of narrow gaps or slits, like that of a plate heater. 260°C (500°F) max service temperature.

Note: element not replaceable.



TAS adaptor

All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.



Miniature connector.

Ordering Example: 88009E, style 88009 probe in Type E thermocouple, \$115.

All 88000 series probes are supplied with retractable cable [expands to 1.5 m (5')] and male subminiature connector.

*** Specify Calibration:**
K: CHROMEGA®-ALOMEGA®
E: CHROMEGA-Constantan

* Specify Calibration K or E.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters