

Leaf Surface Probes

For Instant Measurement of Flat Surfaces



88L40K
\$75




- ✓ Measures 0 to 300°C (32 to 572°F)
- ✓ Type K Thermocouple
- ✓ Accuracy ±2°C (±4°F)
- ✓ Fast Response <5 Sec
- ✓ 40 and 75 mm (1.5 and 3") Lengths

88L40K, \$75.

Supplied with

- ✓ Protective Leaf Cover
- ✓ Ergonomic Handle
- ✓ Coiled Cord — 25 mm (1') Stretches to Over 1.5 m (5')
- ✓ SMPW Miniature Connector with Mating Connector or TAS with Clip and Clamp



These unique leaf style surface probes are designed for instant measurement of temperature on flat surfaces.

Their ultra low thermal mass and flexible construction make them ideal for rugged industrial applications. Their Type K thermocouple is compatible with all standard handheld digital thermometers.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)				
Model No.	Price	Max Temperature	A Dimension	Applications
88L40K	\$75	300°C (572°F)	40 mm (1.5")	Type K Thermocouple
88L75K	85	300°C (572°F)	75 mm (3")	For flat surfaces

Comes complete with 25 mm (1') coiled cord, protective leaf cover, ergonomic handle, SMPW miniature connector with mating connector or TAS with clip and clamp. Response time for probes is under 5 seconds. Probes come with a protective cover and a coiled cable that stretches to 1.5 m (5') and a miniature Type K connector.
Ordering Example: 88L40K, 40 mm leaf probe, \$75.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters