



Unique Surface Probes

AVAILABLE FOR FAST DELIVERY!

PATENTED

Covered by U.S. and International patents and pending applications.

Model No. 88106(*)

\$190

Right-angle probe for fast response times. Sheath length is 102 mm (4"). Max surface temperature is 760°C (1400°F).

Replaceable Element not supplied, order Model No. 88106()-RE, \$25.*

Model No. 88107(*)

\$200

Right-angle, long reach probe with fast response design. Sheath length is 203 mm (8"), with 760°C (1400°F) max surface temperature.

Replaceable Element not supplied, order Model No. 88107()-RE, \$25.*

All models shown smaller than actual size.

Model No. 88108(*)

\$205

Right-angle, long 300 mm (12") reach probe with fast response design. 760°C (1400°F) max surface temperature.


Replaceable Element not supplied, order Model No. 88108()-RE, \$25.*

Model No. 88010(*)

\$175

Long, 300 mm (12") reach version of the 88006. Fast response design with 760°C (1400°F) max surface temperature for use in oven and furnaces.

Replaceable Element not supplied, order Model No. 88010()-RE, \$25.*



TAS adaptor

All models supplied with a molded SMP or SMPW subminiature male connector and TAS adaptor.

* Specify Calibration:

K: CHROME[®]GA[®]-ALOMEGA[®]

E: CHROME[®]GA[®]-Constantan



For Temperatures up to 760° C (1400° F)

See pages A-109 to A-110 for dimensions.

Ordering Example:
88018K, Type K surface probe, \$205.



Model No. 88007(*)

\$110

Miniature, fast response probe. Ideal for measuring the surface temperature of small electronic parts. 250°C (480°F) max surface temperature.

Replaceable Element supplied free, for additional elements order Model No. 88007(*)-RE, \$25.

Model No. 88006(*)

\$115

Miniature, fast response probe with 480°C (900°F) max surface temperature. Ideal for surface temperatures of small electronic parts.


Replaceable Element not supplied, Model No. 88006(*)-RE, \$25.

AVAILABLE FOR FAST DELIVERY!

All models shown smaller than actual size.

PATENTED

Covered by U.S. and International patents and pending applications.



Model No. 88016(*)

\$160


High temperature, right-angle probe, with miniature pencil type head. Best suited to stationary surfaces, with sensing head parallel to the handle. 480°C (900°F) max surface temperature.

Replaceable Element not supplied, order Model No. 88016(*)-RE, \$25.

See pages A-109 to A-110 for dimensions.



Miniature connector.




Model No. 88026(*)

\$150

High temperature, right-angle probe, with miniature pencil type head. Best suited to stationary surfaces, with sensing head perpendicular to the handle. 480°C (900°F) max surface temperature.

Replaceable Element not supplied, order Model No. 88026(*)-RE, \$25.



PATENTED

Model No. 88007K and replaceable element, Model No. 88007K-RE.

* Specify calibration: K - Type K Thermocouple E - Type E Thermocouple
Ordering Example: 88007K probe with type K Thermocouple, \$110.

Replaceable Element Design

Customer Replaceable Element: probe is supplied with one additional element.
Factory Replaceable Element: OMEGA® can install replaceable elements and check the probe for \$50, with the first replacement free! For non-replaceable element probes, replacement probes are available with a one time trade-in discount. Please contact our Customer Service Department for details.

To order Replaceable Elements, add suffix "-RE" to model no., \$25 each.

Ordering Example: 88026K-RE for 88026K probe.

* Insert calibration needed, e.g. K (Type K thermocouple).



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters