


Thermocouples for Extruders/Molding and Packaging Machines

With Stainless Steel Armor Cable

OMEGA's rugged Spring-Loaded Bayonet and Compression Fitting Thermocouples are ideally suited for measuring plastic processing machinery temperatures at the crosshead, die, and barrel. With OMEGA's pipe clamp adaptor, the Bayonet type can be used to measure pipewall and bearing temperatures. The maximum length for armored cable is 12 m (40') [1.5 m (5') is standard]. Dual elements are available. The standard termination is Style 1 or Style 2. Style 3 is available upon special request. Probes with 45° bends are also available. Consult Sales Department for availability.

Grounded Junction Standard. Ungrounded Junction Also Available



CF-000-J-2-60-1 Starts at \$25



Price includes 4.8 mm (3/16") sheath diameter probes, brass compression fitting with 1/8" NPT, and 1.5 m (60") lead length.


Standard Extruder Probes Compression Type Allow 25 mm (1") for Compression Fitting

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)									
Dimensions*	Type	Cold End Termination	Model Number ANSI Color Code	Price	Dimensions	Type	Cold End Termination	Model Number	Price
Straight A = 50 mm (2") B = 1.5 m (60")	J	1	CF-000-J-2-60-1	\$25	90° Bend A = 50 mm (2") B = 1.5 m (60")	J	1	CF-090-J-2-60-1	\$26
	J	2	CF-000-J-2-60-2	28		J	2	CF-090-J-2-60-2	29
	K	1	CF-000-K-2-60-1	25		K	1	CF-090-K-2-60-1	26
	K	2	CF-000-K-2-60-2	28		K	2	CF-090-K-2-60-2	29
	T	1	CF-000-T-2-60-1	25		T	1	CF-090-T-2-60-1	26
	T	2	CF-000-T-2-60-2	28		T	2	CF-090-T-2-60-2	29
	E	1	CF-000-E-2-60-1	25		E	1	CF-090-E-2-60-1	26
	E	2	CF-000-E-2-60-2	28		E	2	CF-090-E-2-60-2	29
A = 100 mm (4") B = 1.5 m (60")	J	1	CF-000-J-4-60-1	\$25	A = 100 mm (4") B = 1.5 m (60")	J	1	CF-090-J-4-60-1	\$26
	J	2	CF-000-J-4-60-2	28		J	2	CF-090-J-4-60-2	29
	K	1	CF-000-K-4-60-1	25		K	1	CF-090-K-4-60-1	26
	K	2	CF-000-K-4-60-2	28		K	2	CF-090-K-4-60-2	29
	T	1	CF-000-T-4-60-1	25		T	1	CF-090-T-4-60-1	26
	T	2	CF-000-T-4-60-2	28		T	2	CF-090-T-4-60-2	29
	E	1	CF-000-E-4-60-1	25		E	1	CF-090-E-4-60-1	26
	E	2	CF-000-E-4-60-2	28		E	2	CF-090-E-4-60-2	29

Ordering Example: CF-000-J-2-60-1, \$25 Compression fitting style, Type J thermocouple with an "A" dimension of 100 mm (2") and 1.5 m (5') of leads. The cold end termination is Style 1 (spade lugs standard).

Termination Styles:




Note: Cutout for Style 1 is 21.3 mm (0.83") diameter, wall thickness < 3.2 mm (1/8"). Mating connectors (HSTW-K-F-FT for Style 2 and 3 may be found in Section G. (Add \$5 to Style 1 price for Style 3).

* "B" lengths over 1.5 m (60") are available; change the "60" to desired length in inches, and add \$2.25/ft. Longer "A" lengths are available at \$1.00/inch. Cable Dia.: 7 mm (0.28").

Thermocouple Extension Cable Assemblies

To Order (Specify Model Number)			
Specify Calibration	Termination Styles		Price
SEEX-□-48-1-1	1	1	\$17
SEEX-□-48-2-1	2	1	20
SEEX-□-48-3-1	3	1	24

Construction: 6.4 mm (1/4") Stainless Flexible Cable. Standard Length: 1.2 m (48"). Ordering Example: SEEX-J-48-3-1, Type J 3-1 style thermocouple cable assembly, \$24.



To order extension cable, insert desired calibration in first space "□" provided. Add \$2.25/ft or fraction of single element extension cable over 1.2 m (48").

For dual element extension cables, add \$3.25/ft or fraction of dual element extension cable over 1.2 m (48") and change SEEX to DEEX.

For ungrounded, add \$6 and suffix "UNGROUND" to model number.

Note: Custom A and B configurations are available. Consult Sales Department for price and availability.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters