


Magnetic Thermocouple Probes

Model 88401(*)

\$135



Model 88401, shown larger than actual size, \$135.



Model 88402, \$150, shown actual size.


Model 88401, \$135, shown actual size.

Model 88402(*)


\$150



Model 88402, shown larger than actual size, \$150.



Dimensions: mm (in)



Magnetized probes, suitable for long term contact pressure. Requires 10 minutes to reach full surface temperature. The 88401 uses PFA insulated lead wire and is rated to a max surface temperature of 250°C (480°F). The 88402 uses “GG” fiberglass insulated lead wire and is rated to a max service temperature of 400°C (752°F). Both sensors are supplied with an SMPW connector and TAS adaptor.

*** Specify Calibration:**

- K:** CHROMEGA®-ALOMEGA®
- E:** CHROMEGA®-Constantan

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
88401K	\$135	Magnetic K thermocouple, max temp 250°C (480°F)
88401E	135	Magnetic E thermocouple, max temp 250°C (480°F)
88402K	150	Magnetic K thermocouple, max temp 400°C (752°F)
88402E	150	Magnetic E thermocouple, max temp 400°C (752°F)

Accessories

Model No.	Price	Description
88401K-RE	\$25	Replacement K element or 88401K
88401E-RE	25	Replacement E element or 88401E

Comes with transition adaptor from flat pin male to round pin male, TAS.

88401 probes come with a replaceable element. Due to the design of the 88402, the element is not replaceable.

Ordering Example: 88401K, magnetic K thermocouple, \$135.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters