


Mineral-Insulated Metal Sheathed Thermocouple Probes

Bare Leads Mineral-Insulated Cable




Available as
See page A-43 to A-48.

BLMI Series Starts at
\$22

Epoxy sealed "cold end", rated to 175°C (350°F). Bare 19 mm (¾") leads.

BLMI-XL-14U-12, \$31, shown smaller than actual size.



Cold-End Option

19 mm (0.7")

Shown actual size.

BLMI probes are also available in a high-temperature version. The cold end is potted using a ceramic cement rated to 1200°C (2200°F). Add "-CC" to the end of the probe part number and \$5 to list price. (The actual temperature rating of the probe is dependent upon the calibration, sheath material, and probe diameter.)

"DUAL" Construction

Also available in a 4-wire construction (2 thermocouple junctions). Add "-DUAL" to the end of the part number and \$10 to the list price. Consult Sales for probe lengths over 12".

BLMI Probes Deliver Consistent, Superior Quality Through Automated Manufacturing


Thermocouple users demand products able to deliver accurate measurements over long lifetimes. They also want proven track records from the probes they buy. With OMEGA's automated manufacturing and testing systems, these customers can be assured of consistently high-quality products, and the ability to track the manufacturing process and retrieve the initial calibration values and material sources.

OMEGA's bare leads MI (BLMI) finished probes begin with OMEGA's own high-purity magnesium oxide thermocouple cable. This mineral-insulated, metal-sheathed cable uses SLE-class materials throughout its construction.


For some applications, such as ceramic kilns, BLMI probes combined with the accessories shown on these pages offer expedient and accurate temperature solutions to 1204°C (2200°F) with XL probes. BLMI probes meet and exceed the rigorous standards for thermocouples, including ANSI/ASTM-E-230, ASTM-E-608, and the British/European BS/EN 61515 standard. The combined BLMI probe with Super OMEGA CLAD® XL sheathing produces superior measurement results.

OMEGA's BLMI Series probes are built and quality tested on our automated manufacturing lines. OMEGA CLAD® mineral-insulated, metal-sheathed thermocouple cable is cut, stripped, beaded, closed, potted, and tested by equipment designed and built in-house exclusively for these tasks.


Programmable controller-based automation used in manufacturing BLMI probes ensures the same high quality from lot to lot—from cutting to final test. After final QA tests for insulation resistance and weld and seal leakage [nitrogen pressure test at 2.5 MPa (362 psi)], OMEGA assigns identification codes to each device, which can be used to track products through the entire manufacturing process.



To pass the IR test according to ASTM specs, OMEGA's BLMI probes must achieve at least a 1 GΩ reading. The unit under test scored 50 GΩ.



Probes are subjected to a leak test at the welded thermocouple junction (hot end) with a pressurization greater than 2.5 MPa (362 psi).



BRLK and SSLK compression fittings starting at \$6. See page A-127

Junction Types

Grounded



Exposed



Ungrounded



Super OMEGACLAD® XL "BLMI" probes used in ceramic kiln firing applications. For more information on Super OMEGACLAD® XL probes, see page A-43.




Accessories



Ceramic terminal blocks, start at \$3, see page B-10.

Compensated spade lugs, \$13 pk of 20, see page G-56.



TX93A, ultra miniature transmitters, \$74, see page N-38.

Fiberglass sleeving for insulating bare wire up to 480°C (900°F), \$0.35/ft, see page A-144.



- ✓ J, K, T, Calibrations in Stock— Also Available in E and N
- ✓ 304 SS, 310 SS, 316 SS, Inconel® 600, and Super OMEGACLAD® XL Sheaths
- ✓ Exposed, Grounded, and Ungrounded Hot Junctions
- ✓ Exposed 19 mm (0.7") Bare Conductors
- ✓ Epoxy or Ceramic Cement Cold-End Seal
- ✓ Standard Lengths, 150 or 300 mm (6 or 12")—Custom Lengths Available
- ✓ Vast Selection of Termination Accessories—See Window to the Right
- ✓ Metric Diameters and Lengths Available—Contact Sales for Details

Discount Schedule

1 to 10	Net
11 to 24	10%
25 to 49	20%
50 to 99	25%
100 and over	Consult Sales

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Calibration ANSI Color	Sheath Material	Sheath Dia. mm (in)	Upper Temperature Guidelines °C (°F) T/C Junction	Model No.	Price [50 mm and 300 mm (6 and 12")]		Price Add'l 300 mm (12") MI Cable
					G*E*	U*	
K	304 SS	1/16 (1.59)	899 (1650)	BLMI-304-K-116(*)-(**)	\$22	\$24	\$1.55
	304 SS	1/8 (3.18)	899 (1650)	BLMI-304-K-18(*)-(**)	22	24	1.85
	304 SS	3/16 (4.78)	899 (1650)	BLMI-304-K-316(*)-(**)	23	25	3.15
	304 SS	1/4 (6.35)	899 (1650)	BLMI-304-K-14(*)-(**)	26	28	5.00
K	INC 600	1/16 (1.59)	921 (1690)	BLMI-INC-K-116(*)-(**)	22	24	1.55
	INC 600	1/8 (3.18)	1071 (1960)	BLMI-INC-K-18(*)-(**)	22	24	3.15
	INC 600	3/16 (4.78)	1149 (2100)	BLMI-INC-K-316(*)-(**)	23	25	4.35
	INC 600	1/4 (6.35)	1149 (2100)	BLMI-INC-K-14(*)-(**)	26	28	7.50
K	XL	1/16 (1.59)	1038 (1900)	BLMI-XL-K-116(*)-(**)	25	27	1.70
	XL	1/8 (3.18)	1149 (2100)	BLMI-XL-K-18(*)-(**)	25	27	3.50
	XL	3/16 (4.78)	1204 (2200)	BLMI-XL-K-316(*)-(**)	26	28	4.80
	XL	1/4 (6.35)	1204 (2200)	BLMI-XL-K-14(*)-(**)	29	31	8.30
J	304 SS	1/16 (1.59)	441 (825)	BLMI-304-J-116(*)-(**)	22	24	1.55
	304 SS	1/8 (3.18)	521 (970)	BLMI-304-J-18(*)-(**)	22	24	1.85
	304 SS	3/16 (4.78)	621 (1150)	BLMI-304-J-316(*)-(**)	23	25	3.15
	304 SS	1/4 (6.35)	721 (1330)	BLMI-304-J-14(*)-(**)	26	28	5.00
T	304 SS	1/16 (1.59)	260 (500)	BLMI-304-T-116(*)-(**)	22	24	1.55
	304 SS	1/8 (3.18)	316 (600)	BLMI-304-T-18(*)-(**)	22	24	1.85
	304 SS	3/16 (4.78)	371 (700)	BLMI-304-T-316(*)-(**)	23	25	3.15
	304 SS	1/4 (6.35)	371 (700)	BLMI-304-T-14(*)-(**)	26	28	5.00

* Specify junction (G)rounded, (E)xposed, or (U)ngrounded. ** Probe length 6" (150 mm), 12" (300 mm), 18" (450 mm) are stock. Ordering Example: BLMI-XL-K-316-G-24, mineral-insulated grounded probe, 24" length, \$26 + 4.80 = \$30.80.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters