

¼ DIN High-/Low-Limit Controller

CN3101
\$510



- ✓ 1 High-/Low-Limit Control Output
- ✓ 1 Independent Alarm
- ✓ Universal Sensor Inputs
- ✓ Transmitter Power Supply
- ✓ Switching Power Supply 100 to 240 Vac

Optional

- ✓ RS232, RS422/RS485 Digital Communications with Second Alarm
- ✓ Analog Output

The CN3101 are compact, fully programmable high- or low-limit controllers that is UL listed. With user programmable inputs, outputs and high-/low-limit features, it is adaptable to almost any limit control application, and can be reconfigured easily as needed. Sophisticated limit control features include a total time over/under setpoint display and peak (maximum or minimum) process variable display. These valuable CN3101 features allow you to determine if process damage has occurred, and they can help in analyzing the cause if shutdown occurs.

The CN3200-SOFT communications package allows the CN3101 controllers to be programmed, configured and have their operations monitored remotely using a computer. Multiple controllers may be connected, or "multi-dropped," on the same communications line by using the RS485 standard for multi-point communications, or by using an RS232C through modems. The CN3251 Series controllers with 16 interval ramp/soak and fuzzy logic are also available in this section.

Specifications

Limit Output:

Automatic: Normally-energized latching relay; relay de-energizes at limit setpoint; Form "C" contacts, 5 A @ 120/230 Vac



CN3101, \$510.

Limit Control Adjustments:

High/Low Limit Setpoint:

Sensor range

Setpoint Limits:

Sensor range

Deadband: -17 to 38°C (1 to 100°F)

Display Offset: -73 to 38°C

(-100 to 100°F)

Alarm Adjustments:

Setpoints: High and low settings for each alarm output

Alarm Types: Absolute—high, low and high/low

Tracking: +Deviation, -deviation, and ±deviation

Relay Action: Latching or non-latching, energized or de-energized

Alarm Deadband: Adjustable, -17 to 38°C (1 to 100°F)

Alarm Inhibit: On power-up, enabled or disabled

Alarm Outputs:

Relay: Form "C" contacts, 5.0 A at 120/230 Vac (resistive load)

Sensor Input: Field selectable Thermocouple, RTD, current or voltage

Input Update Rate: 2 samples per second

Readout Stability

J, K, E Thermocouple: ±1°F/10°F change in ambient temperature

T Thermocouple: ±2°F/10°F change in ambient temperature for sensor temperature >-80°C (-112°F); ±5°F/10°F change in ambient temperature for sensor temperature <-80°C (-112°F)

R, S, B Thermocouple: ±2°F/10°F change in ambient temperature

RTD: ±5°F/10°F change in ambient temperature

4 to 20 mA, 1 to 5 Vdc: ±2°F/10°F change in ambient temperature

Digital Input: Accepts dry-contact closure

Transmitter Power: 24 Vdc ±20% @ 50 mA maximum

Analog Output (Optional):

Retransmit Function: Process variable

Output Signal: 4 to 20 mA into 0 to 800 Ω load, 1 to 5 Vdc into 100 KΩ, selectable via DIP switch

Range: Programmable over selected sensor span for retransmission of

Process Variables

Accuracy: ±0.2% of programmed span, ±1 LSD

Digital Communications (Optional):

RS232: Single-drop, isolated

RS422/485: Multi-drop, isolated, field-selectable by switch

Baud Rates: 1200, 2400, 4800, 9600, 19.2 K

Protocols: ASCII line

Computer Interface

Instrument Power: 100 to 240 Vac, +10%, -15%; 50 to 60 Hz; 15 VA 12 to 24 Vac/Vdc, ±20%, 15 VA (optional)

Operating Environment: 0 to 65°C (32 to 150°F) ambient temperature, relative humidity less than 95%, non-condensing

Dimensions:

Overall: 96 L x 96 W x 121 mm D (3.78 x 3.78 x 4.75")

Depth Behind Panel: 102 mm (4")

Case Material: High-impact, black ABS plastic

Influence of Line Voltage

Variation: ±0.1% of sensor span/10% change in nominal line voltage

Noise Rejection:

Common Mode Noise: 140 dB at 60 Hz

Series Mode Noise: ±0.1% of sensor span with 300 mV peak to peak, 50 or 60 Hz series mode noise

RFI: Typically <0.5% of sensor span at a distance of 1 m (3.1') from transmitter (4 W, 464 MHz)

Input Types and Ranges

Input Type		Range	Accuracy @ 25°C/77°F Ambient (All ±% of Sensor Span)
J	Iron-Constantan	-100 to 1400°F -73 to 650°C	0.2%
K	CHROMEQA®-ALOMEGA®	-300 to 2400°F -184 to 1316°C	0.2%
T	Copper-Constantan	-350 to 750°F -212 to 399°C	0.2% for PV > -112°F/-80°C 0.4% for PV < -112°F/-80°C
E	CHROMEQA®-Constantan	-100 to 1100°F -73 to 593°C	0.2%
R	Pt-13%Rh/Pt	0 to 3200°F -18 to 1760°C	0.4%
S	Pt-10%Rh/Pt	0 to 3200°F -18 to 1760°C	0.4%
B	Pt-30%Rh/ Pt-6%Rh	50 to 3300°F 10 to 1816°C	0.4% for PV > 1000°F 538°C
RTD	Pt, 385 100 Ω	-200 to 1000°F -128 to 538°C -99.9 to 899.9°F -73.3 to 482.2°C	0.2%
Current	4 to 20 mA	Scalable (-500 to 5000)	0.2%
Voltage	0 to 5 Vdc	Scalable (-500 to 5000)	0.2%
	1 to 5 Vdc	Scalable (-500 to 5000)	0.2%



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



Companion Controller: CN3251 series ramp and soak, fuzzy logic controller, see page P-71.

KTSS-316G-12, molded transition joint thermocouple probe, \$19. See page A-78.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
CN3101	\$510	High-/low-limit controller with single output mechanical relay and 1 alarm

Output, Communications and Low Voltage Power Options

Ordering Suffix	Price	Description
-PV	\$80	Recorder output, 4 to 20 mA/1 to 5 Vdc
-S2†	105	RS232 digital communications with second alarm relay
-S4†	105	RS422/485 digital communications with second alarm relay

† Only 1 communications option can be purchased per unit.

Accessories

Model No.	Price	Description
3250X-S2	\$105	RS232 digital communications board
3250X-S4	105	RS485/422 digital communications board
CN3200-SOFT-WIN2	400	Software for communications options, Windows version
3250X-CASE-COMM**	100	Housing for CN3251 and CN3101 with digital communications
3250X-CASE	90	Housing for CN3251 and CN3101 without digital communications
3250X-SBKT	40	Side mounting bracket for CN3251 and CN3101 models
CNQUENCHARC	8	Noise suppression RC snubber (2 leads), 110 to 230 Vac

Comes complete with operator's manual.

Ordering Examples: CN3101, single output limit controller, ¼ DIN bezel, programmable input, one alarm, \$510.

OCW-2, OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$91), \$510 + 91 = \$601.

CN3101-PV-S4, single output limit controller, ¼ DIN bezel, programmable input, 2 alarms, recorder output, and RS485 communications, \$510 + 80 + 105 = \$695.

OCW-2, OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$125), \$695 + 125 = \$820.

Note: In order to add communications to a CN3101, the housing must be replaced with the 3250X-CASE-COMM so that either the 3250X-S2 or 3250X-S4 communications board can be installed.

Recommended Reference Book: Systems and Control, PE-1412, \$135.
See Section Y For Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters