

1/4 DIN Ramp/Soak Temperature/Process Controller with Fuzzy Logic

CN3251
Starts at
\$470



Panel punches available, visit omega.com/panelpunches

- ✓ Dual PID + Fuzzy Logic Control
- ✓ Up to 5 Outputs—Control, Alarm or Event
- ✓ Universal Sensor Input
- ✓ Switching Power Supply 100 to 240 Vac or Optional 12 to 24 Vac/Vdc
- ✓ 16-Segment Ramp/Soak Program
- ✓ Optional RS232, RS422, RS485 Digital Communications
- ✓ Programmable Remote Setpoint Input (Standard)

The CN3251 1/4 DIN temperature and process controller is a cost effective, high-performance, single loop controller that can be used for temperature, flow, pressure and level control applications. With universal sensor inputs and front panel operator setup, one CN3251 controller can be easily field configured for a wide variety of applications, and simply reconfigured as application needs change. This makes it an exceptional choice for applications requiring multiple control needs, manufacturing facilities, testing facilities and testing applications.

Features

5 Possible Outputs for single output or heat/cool control, plus up to 3 alarms or event outputs

Universal Sensor Input accepts thermocouple, RTD or analog signals; 24 Vdc output for loop power

Self-Tuning with Fuzzy Logic optimizes PID control and minimizes overshoot

Digital Input for remote switching of 1 of the following:

- ✓ PID1/PID2
- ✓ Remote/local setpoint
- ✓ Main/auxiliary setpoint
- ✓ Ramp/soak operation
- ✓ Manual/auto control
- ✓ Alarm reset for latching alarms



CN3251, \$470, 1/4 DIN.

16-Interval Ramp/Soak Program with guaranteed soak, event outputs and looping

- ✓ Optional programmable analog
- ✓ Programmable remote setpoint input (standard on all products)

AUX Pushbutton and LED for front panel switching of:

- ✓ PID1/PID2
- ✓ Remote/local setpoint
- ✓ Main/auxiliary setpoint
- ✓ Ramp/soak operation
- ✓ Manual/suto control

Security Code

Protection prevents unauthorized access

Setpoint Ramp Rate provides soft start at power-up, or on setpoint changes, to prevent uneven heating and overshoot

Control Loop Protection provides process protection from:

- ✓ Open sensor
- ✓ Shorted sensor
- ✓ Sensor reversed
- ✓ Control output open or shorted
- ✓ Power control device open or shorted
- ✓ Load power missing and self-diagnostics

Operating Ambient up to 65°C (150°F)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Specifications

Control Modes:

Automatic: On/off, proportional, PID, PI, PD, PID + fuzzy logic, heat/cool (dual PID)

Control Adjustments:

Control Setpoint: Sensor range

Setpoint Limits: Sensor range

Deadband: 1 to 100°F

Proportional Band: Sensor range

Manual Reset: -99.9 to 99.9

Automatic Reset: 0.00 to 99.99 repeats per minute

Rate: 0 to 500 seconds

Output Cycle Time: 0.1 to 60.0 seconds

Output Limit: 0.0 to 100.0%

Open Sensor/Out of Range Output Command: 0.0 to 100.0%

Display Offset: -100 to 100°F

Heat/Cool Adjustments:

Output Offsets: 0 to 100% of proportional band

Cooling Medium: Air, water or oil

Alarm Adjustments:

Setpoints: High and low settings for each alarm output

Alarm Types:

Absolute: High, low and high/low, **Tracking:** +deviation, -deviation, and ±deviation

Relay Action: Latching or non-latching, energized or de-energized

Alarm Deadband: Adjustable, -18 to 38°C (0 to 100°F)

Alarm Inhibit: On power-up, enabled or disabled

Control/Alarm Outputs: Total of 5 control/alarm outputs possible

Relay: Form A contacts, 1.0 A at 120/230 Vac (resistive load)

Solid State Relay Drive: 24 Vdc nominal at 40 mA

Triac: 1 A continuous, 10 A in-rush @ 120 or 230 Vac

Current/Voltage: 4 to 20 mA into 0 to 800 Ω, field-changeable to 1 to 5 Vdc

Output #5 (Optional):

Relay: N.O. form "C" contact, 5 A @ 120 or 2.5 A 230 Vac

Sensor Input: Field-selectable thermocouple, RTD, current or voltage

Input Update Rate: 2 samples/s

Ramp/Soak Programming:

Intervals: 16

Loops: 1 loop, 0 to 255 times or continuous

Event Outputs: Up to 3

Guaranteed Soak Differential: Off, 1°F to sensor span


Time Units: Seconds, minutes, hours (1 s to 99.99 hours/segment)

Ramp to Setpoint: 1 to 9999°/hour on power-up

Open Sensor and Out-of-Range Condition:

Programmable control action with display indicating condition "OPEN SENS"

Front Panel



Remote Setpoint Input:

Input Signal: 4 to 20 mA, 250 Ω input impedance, 1 to 5 Vdc, 110 KΩ input impedance, voltage or current field-selectable via switch

Range: Programmable over-selected sensor span

Accuracy: ±0.3% of sensor span (initial accuracy) at 24°C (75°F) ambient temperature and rated line voltage, field calibrate to ±0.2% of sensor span

Digital Input: Accepts dry-contact closure

Analog Output Option:

Assignable Functions: Process variable, output #1 command, active setpoint, output #2 command

Output Signal: 4 to 20 mA into 0 to 800 Ω load, 1 to 5 Vdc into 100 KΩ or greater load selectable via DIP switch

Range: Programmable over selected sensor span for retransmission of process variable and active setpoint, fixed to 0 to 100% for transmission of output commands

Accuracy: ±0.2% of programmed span, ±1 LSD

Digital Communications (Optional):

RS232: Single-drop, isolated

RS422/485: Multi-drop, isolated, field selectable by switch

Baud Rates: 1200, 2400, 4800, 9600, 19.2 K

Protocols: ASCII line, computer interface

Instrument Power: 100 to 240 Vac, 10%, -15%; 12 to 24 Vac/Vdc, ±10%; 50 to 60 Hz

Operating Environment: 0 to 65°C (32 to 150°F) ambient temperature, relative humidity <95%, non-condensing

Dimensions:

Overall: 97 H x 97 W x 97 mm D (3.8 x 3.8 x 3.8")

Depth Behind Panel: 97 mm (3.8")

Front Panel Projection: 20 mm (0.8")

Panel Cutout: 91 x 91 mm (3.6 x 3.6")

Weight: 454 g (1 lb)

Case Material: High-impact, black ABS plastic

Influence of Line Voltage Variation: ±0.1% of sensor span/10% change in nominal line voltage

Noise Rejection:

Common Mode Noise:

140 dB at 60 Hz

Series Mode Noise: ±0.1% of sensor span with 300 mV peak-to-peak, 50 or 60 Hz series mode noise



RFI: Typically less than 0.5% of sensor span at a distance of 1 m (3.1') from transmitter (4 W, 464 MHz)

Input Types and Ranges

Input Type	Range	Accuracy @ 25°C (77°F) Ambient (All ±% of Sensor Span)
J Iron Constantan	-73 to 760°C -100 to 1400°F	0.2%
K CHROME [®] GA ALOME [®] GA	-184 to 1316°C -300 to 2400°F	0.2%
T Copper Constantan	-212 to 399°C -350 to 750°F	0.4% for PV <-80°C 0.2% for PV >-80°C
E CHROME [®] GA Constantan	-73 to 593°C -100 to 1100°F	0.2%
R Pt-13%Rh/Pt	-18 to 1760°C 0 to 3200°F	0.4%
S Pt-10%Rh/Pt	-18 to 1760°C 0 to 3200°F	0.4%
B Pt-30%Rh/Pt-6%Rh	10 to 1816°C 50 to 3300°F	0.4% for PV >538°C
RTD Pt, 385 100 Ω	-128 to 538°C -200 to 1000°F -73.3 to 482.2°C -99.9 to 899.9°F	0.2%
4 to 20 mA	Scalable (-500 to 5000)	0.2%
0 to 5 Vdc	Scalable (-500 to 5000)	0.2%
1 to 5 Vdc	Scalable (-500 to 5000)	0.2%



CN3101 Series companion limit controller—accepts thermocouple, RTD and process signals.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model Number	Price	Description
CN3251(*)	\$470	Ramp/soak controller with fuzzy logic

Comes complete with operator's manual.

* Specify output code from Single or Dual Output option tables below.

Ordering Examples: CN3251-R, ramp and soak controller with a relay/DC pulse heat output, \$470.

OCW-2, OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$84), \$470 + 84 = \$554.

CN3251-FR, ramp and soak controller with a 4 to 20 mA heat output, relay cool output, \$470 + 40 = \$510.

OCW-2, OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$91), \$510 + 91 = \$601.

Single Output Options (No Additional Charge)

Output Suffix	Output #1 Type
-R	Relay/DC pulse**
-T	AC SSR
-F	4 to 20 mA***

**Field selectable.

***Field selectable for 1 to 5 Vdc.

Dual Output Options (Field Installable)

Order Suffix	Add'l. Cost	Description Output #1	Output #2
-RR	\$40	Relay	Relay
-TT	40	AC SSR	AC SSR
-FF	40	4 to 20 mA***	4 to 20 mA***
-DD	40	DC pulse	DC pulse
-FR	40	4 to 20 mA***	Relay
-FT	40	4 to 20 mA***	AC SSR
-DR	40	DC pulse	Relay
-DT	40	DC pulse	AC SSR

***Field selectable for 1 to 5 Vdc.

Accessories

Model No.	Price	Description
3250X-R	\$45	Relay/DC pulse output module
3250X-T	45	AC SSR output module
3250X-FF***	85	4 to 20 mA/4 to 20 mA output module
3250X-RR	85	Relay/relay output module
3250X-TT	85	AC SSR/AC SSR output module
3250X-DD	85	DC pulse/DC pulse output module
3250X-FR***	85	4 to 20 mA/relay output module
3250X-FT***	85	4 to 20 mA/AC SSR output module
3250X-DR	85	DC pulse/relay output module
3250X-DT	85	DC pulse/AC SSR output module
3250X-S2	105	RS232 digital communications board
3250X-S4	105	RS485/422 digital communications board
3250X-CASE-COMM†	100	Housing for CN3251s with digital communications
3250X-CASE	90	Housing for CN3251s without digital communications
3250X-SBKT	40	Side mounting bracket
CN3200-SOFT-WIN2	400	Software for communications option, Windows version
CNQUENCHARC	8	Noise suppression RC snubber (2 leads), 110 to 230 Vac

***Field selectable for 1 to 5 Vdc. †Special controller case required when adding -S2 or -S4 to controllers.

Options

Ordering Code	Price	Description
-TPS	\$90	24 Vdc transmitter isolated output 65 mA ³
-LV ¹	60	12 to 24 Vdc/Vac power
-A ¹	50	Dual alarm/event relays (shared common terminal)
-S2 ²	105	RS232 digital communications, with one alarm/event relay
-S4 ²	105	RS422/485 digital communications, with one alarm/event relay
-PV ²	95	Recorder output, 4 to 20 mA/1 to 5 Vdc
-S2-PV ²	125	RS232 digital communications, one alarm/event relay and recorder output
-S4-PV ²	125	RS422/485 digital communications, one alarm/event relay and recorder output

¹ These options can be ordered with any model number.

² Only 1 of these options can be ordered at a time.

³ Cannot be ordered with option "A".

CN3251-R, \$470, shown smaller than actual size.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters