

1/16 DIN High-Limit Controller with Latching Relay

CN355 and CN375 Series

Starts at
\$139

CN375-JF, \$189, shown larger than actual size.



- ✓ **Reset Button on Front Panel**
- ✓ **Indicating and Non-Indicating Models**
- ✓ **J, K, R, S Thermocouples or RTD Input**
- ✓ **Easy-to-Use: No Programming Required**

The CN355 non-indicating and CN375 indicating 1/16 DIN high-limit controllers provide reliable high-temperature-limit shut-off control for most machine and process control applications, including environmental chambers, furnaces, ovens, and packaging machinery. These controllers have a normally energized SPDT latching output relay that becomes de-energized whenever the process variable exceeds a selected setpoint value. Reset of the latching output relay is done from a reset pushbutton on the front panel.

Specifications

Accuracy: ±1.5% FS
+ 1 digit (thermocouple input); ±1% FS + 1 digit (RTD input)
Resolution: 1°C or °F
Output Type: SPDT latching mechanical relay, 240 Vac, 2.5 A resistive load
Deadband/Hysteresis: 1.5 to 2.5% FS fixed
Power: 110/230 Vac ±10%, 50/60 Hz
Input:
3-Wire RTD (Pt100): 0.00385 excitation, 2 mA lead wire (Approx. 190' of 20-gage copper wire)
Thermocouple Types J, K, R*, S* (*Non-Indicating Models Only): Input resistance, 200 kΩ; lead wire resistance, 100 Ω max; up-scale break protection standard
Power Consumption: Approx. 3 VA
Operating Ambient Range: 5 to 45°C (41 to 113°F), 90% RH max



KTSS-316 G-12 temperature probe, \$189, sold separately. See page A-83 for more information.

Rear screw terminal connections

Companion Controllers from CN350, CN360 and CN370 Series—Available in This Section!



Insulation Resistance: 500 Vdc, 20 MΩ min between input and power supply terminals
Connections: Screw terminals
Installation: Lock-in mounting type (no mounting hardware necessary)
Dimensions: 45 mm (1.772") square (1/16 DIN) panel cutout; 90 mm (1.88") depth behind panel
Panel Thickness: 1.0 to 3.5 mm (0.04 to 0.14")
Weight: 210 g (0.463 lb)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Non-Indicating Model No.	Price	Indicating Model No.	Price	Input Type	Range
CN355-JF	\$139	CN375-JF	\$189	J	0 to 799°F
CN355-JC	139	CN375-JC	189	J	0 to 399°C
CN355-KF	139	CN375-KF	189	K	0 to 999°F
CN355-KC5	139	CN375-KC	189	K	0 to 999°C
CN355-KC6	139	—	—	K	0 to 1199°C
CN355-RF	139	—	—	R	0 to 2999°F
CN355-RC	139	—	—	R	0 to 1699°C
CN355-SC	139	—	—	S	0 to 1699°C
CN355-P1F	139	CN375-P1F	189	RTD	0 to 799°F
CN355-P1C	139	CN375-P1C	189	RTD	0 to 399°C

Ordering Example: CN375-KF, indicating high-limit controller, Type K thermocouple input, -18 to 537°C (0 to 999°F) range, \$189.

For Additional Controllers and Indicators, See Section M



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters