

Non-Reversible OMEGALABEL® Temperature Monitors

Button Series


4 temperature ratings on each label.
Temperatures are read clockwise starting at the "V" mark:

Outside Diameter: 8 mm (0.3")
Indicating Window: 1.2 mm (0.05")

To order package of 30,
add suffix "-30" to model number.
Ordering Example: BUA2-180/82-30,
button series label 82 to 99°C
(180 to 210°F), package of 30, \$55.

Specifications

Accuracy: Up to 99°C (210°F) is ±2°C (1.8°F); From 100°C (212°F) to 154°C (309°F) is ±2°C (2.7°F); From 160°C (320°F) to 280°C (536°F) is ±2% and ±2°C (1.8°F)



Price
pkg of 10 pkg of 30
\$20 \$55

MOST POPULAR MODELS HIGHLIGHTED!

Model No. (Pkg 10)	Temperature Ratings			
BUA2-120/49	°C 49	54	60	66
	°F 120	130	140	150
BUA2-140/60	°C 60	66	71	77
	°F 140	150	160	170
BUA2-180/82	°C 82	88	93	99
	°F 180	190	220	210
BUA2-175/79	°C 79	93	107	121
	°F 175	200	225	250


Series 6M

6 temperature ratings
on each label:

6MA: 5.6°C (10°F) between each rating
6MB: 13.9°C (25°F) between each rating

Actual Size: 32 x 10 mm (1.3 x 0.4")
Indicating Window: 0.4 x 3 mm (0.02 x 0.13")

To order package of 30,
add suffix "-30" to model number.
Ordering Example: 6MA-130/54-30,
6 temperature rating 54 to 82°C
(130 to 180°F), package of 30, \$54.



6MA-130/54,
shown actual size.
Price
pkg of 10 pkg of 30
\$18 \$54

Model No. (Pkg 10)	Temperature Ratings			
6MA-100/38	°C 38	43	49	54
	°F 100	110	120	130
6MA-130/54	°C 54	60	66	71
	°F 130	140	150	160
6MA-160/71	°C 71	77	82	88
	°F 160	170	180	190
6MA-190/88	°C 88	93	99	104
	°F 190	200	210	220
6MA-220/104	°C 104	110	116	121
	°F 220	230	240	250
6MA-250/21	°C 121	127	132	138
	°F 250	260	270	280
6MB-100/38	°C 38	52	66	79
	°F 100	125	150	175
6MB-175/79	°C 79	93	107	121
	°F 175	200	225	250


Series 8M

8 temperature ratings
on each label:

8MA: 5.6°C (10°F) between each rating
8MB: 13.9°C (25°F) between each rating

Actual Size: 42 x 10 mm (1.6 x 0.4")
Indicating Window: 0.4 x 3 mm (0.02 x 0.13")

To order package of 30, add suffix
"-30" to Model No.
Ordering Example: 8MA-180/82-30, 8 temperature rating,
82 to 121°C (180 to 250°F), package of 30, \$83.




8MA-180/82,
shown actual size.
Price
pkg of 10 pkg of 30
\$28 \$83

Model No. (Pkg 10)	Temperature Ratings			
8MA-100/38	°C 38	43	49	54
	°F 100	110	120	130
8MA-140/60	°C 60	66	71	77
	°F 140	150	160	170
8MA-180/82	°C 82	88	93	99
	°F 180	190	200	210
8MA-230/110	°C 110	116	121	127
	°F 230	240	250	260
8MB-100/38	°C 38	52	66	79
	°F 100	125	150	175

ML4C Series, Mini Labels

4 temperature ratings per label:
Actual Size: 12 x 5 mm (0.5 x 0.2")
Indicating Circle: 1.5 mm (0.06")

To order package of 30, add suffix
"-30" to model number.
Ordering Example: ML4C-40-30,
mini label, 4 temperature rating
(40 to 49°C), package
of 30, \$32.



Shown larger than
actual size for detail.

Price
pkg of 10 pkg of 30
\$12 \$32

Model No. (Pkg 10)	Temperature Ratings			
ML4C-40	°C 40	43	46	49
ML4C-54	°C 54	60	66	71
ML4C-77	°C 77	82	88	93
ML4C-99	°C 99	104	110	116
ML4C-121	°C 121	127	132	138
ML4C-143	°C 143	149	154	160
ML4C-166	°C 166	171	177	182
ML4C-188	°C 188	193	199	204
ML4C-210	°C 210	216	224	232
ML4C-241	°C 241	249	254	260



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters