

1/16 DIN Temperature/Process Limit Controllers

CN7400
Starts at
\$255



- ✓ Dual Display
- ✓ FM-Approved Limit
- ✓ Universal Inputs
- ✓ Illuminated Keys
- ✓ Remote Reset Capability

Panel Punches Available, Visit omega.com/panelpunches



CN7430, \$255, shown actual size.

The CN7400 Series temperature/process FM-approved limit controllers set a new standard in 1/16 DIN limit controls. They have universal inputs (10 thermocouple and 4 RTD types, voltage, and current). Standard features include remote reset capability. Outputs include normally open (form "A") and normally closed (form "B") relays. Form "A" and form "B" relays can be set up for each setpoint output and logically linked to emulate a form "C" output.

Inputs

Input Types	Range
K Thermocouple	-200 to 2500°F (-129 to 1371°C)
J Thermocouple	-100 to 1600°F (-73 to 871°C)
T Thermocouple	-350 to 750°F (-212 to 398°C)
E Thermocouple	-100 to 1800°F (-73 to 982°C)
N Thermocouple	-100 to 2372°F (-73 to 1300°C)
R Thermocouple	0 to 3200°F (-17 to 1760°C)
S Thermocouple	0 to 3200°F (-17 to 1760°C)
B Thermocouple	75 to 3308°F (24 to 1820°C)
L (J DIN) Thermocouple	-100 to 1600°F (-73 to 871°C)
C Thermocouple	0 to 4208°F (-17 to 2320°C)
Pt100 RTD (0.00385)	-200 to 875°C (-328 to 1607°F)
Pt100 RTD (0.00392)	-200 to 875°C (-328 to 1607°F)
RTD, 120 Ω Nickel (0.00628)	-80 to 320°C (-112 to 608°F)
RTD, Pt1000 (0.00385)	-200 to 875°C (-328 to 1607°F)
0 to 20 mA*, 4 to 20 mA*	-1999 to 9999
0 to 10Vdc*, -10 to 10 Vdc*, -10 to 10 mVdc*	-1999 to 9999

Note: All thermocouple and RTD inputs can be set for 0.1° display. If temperature goes above 999.9° or below -199.9°, the display will return to whole-degree resolution.

*** Process Input Types:** The 0 to 20 mAdc, 4 to 20 mAdc, 0 to 10 Vdc, 2 to 10 Vdc, and -10 to 10 mVdc inputs are fully scalable from a minimum of 100 counts span placed anywhere within the range of -1999 to 9999. Decimal point position is adjustable from the zero place (9999), tenths (999.9), hundredths (99.99) or thousandths (9.999).

Specifications

Selectable Input: 10 thermocouple, 4 RTD, DC voltage or DC current

Display: Two 4-digit, 7-segment, 7.62 mm H (0.3") LEDs

Accuracy: ±0.25% of span, ±1 least significant digit

Supply Voltage: 100 to 240 Vac, nominal, 10 to 15%, 50 to 400 Hz; single phase; 132 to 240 Vdc, nominal, 10 to 20%

- Power Consumption:** 5 VA max
- Operating Temperature:** -10 to 55°C (14 to 131°F)
- Memory Backup:** Non-volatile memory
- Relay Control Output Ratings:**
 - Resistive:** SPST, 3 A @ 240 Vac
 - Inductive:** 1.5 A @ 240 Vac
- Weight:** 227 g (8 oz)
- Panel Cut-Out:** 45 mm² (1.77 in²)
- Bezel:** 48 mm² (1.9 in²)
- Maximum Panel Thickness:** 6.35 mm (0.25")
- Panel Depth:** 133 mm (5.24")



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
CN7430	\$255	Single output, NO relay
CN7434	290	Dual output, NO relay, NC relay

Comes complete with operator's manual.

Ordering Examples: CN7430, single output controller with NO relay, \$255.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$63), \$255 + 63 = \$318.

CN7434-PV1, dual output controller, NO relay/NC relay, 0 to 20 mA isolated retransmission output, \$290 + 70 = \$360.

Option

Ordering Suffix	Add'l Price	Description
-PV1	\$70	0 to 20 mA isolated retransmission output

Accessory (Field Installable)

Model Number	Price	Description
CNQUENCHARC	\$10	Noise suppression RC snubber (2 leads), 110 to 230 Vac

Recommended Reference Book: Controller Tuning, PID, GE-2117, \$25. Visit omega.com/bobi for Additional Books



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters