

RTD Simulators

CL510 Series
Starts at
\$499



- ✓ Simulate RTD Temperature Outputs
- ✓ High Accuracy
- ✓ Works with All Pulsed Instruments and a Wide Variety of Transmitters
- ✓ Easy Dial Knob Adjusts Output by 0.1°C/°F for CL510-7 Only, Others 1°C/°F
- ✓ Easy Check Switch: User Settable for 0% and 100% Span Adjustments

The OMEGA® CL510 and CL510-7 RTD simulators simulate standard RTD curves over the entire industrial temperature range. Choose between 7 standard RTD curves.

The CL510 Series will simulate RTD resistances into all types of instruments such as transmitters, recorders, controllers, alarms, data acquisition and computer systems. Calibrators are easy to reset and are compatible with pulsed systems and transmitters.

The easy check function allows the user to store 3 output temperatures for real convenience. All settings are saved with the power off.

Specifications

[Unless otherwise indicated, all specifications are rated from a nominal 23°C (73°F), 70% RH for 1 year from calibration]

Range: Pt100, -200 to 850°C; Cu10, -200 to 260°C; Ni110, -100 to 300°C; Ni120, -80 to 260°C

CL510 Single RTD curve simulator with 1° resolution and selectable units in °C or °F

Pt 100 - α Codes	
Code	Value
-1	0.003850
-2	0.003902
-3	0.003916
-4	0.003926

CL510-7 multi-type RTD simulator includes 7 RTD curves with 1° resolution and selectable units in °C or °F. Curves included with the CL510-7 are Pt100 α = 1.3850, 1.3902, 1.3916, 1.3926 and Cu10, Ni110, Ni120, Ω .

Accuracy: $\pm(0.015\%$ of setting in $\Omega + 0.05 \Omega$)

Typical Accuracies for RTD Curves are:

$\alpha = 1.3850, 1.3902, 1.3916, 1.3926: \pm 0.25^\circ\text{C} (\pm 0.5^\circ\text{F})$
Cu10 $\Omega: \pm 1.5^\circ\text{C} (\pm 3^\circ\text{F})$

Ni110 $\Omega, \text{Ni120 } \Omega: \pm 0.25^\circ\text{C} (\pm 0.5^\circ\text{F})$

Allowable Excitation Current:

100 μA to 10.2 mA, steady or pulsed/intermittent/smart
For Accuracies Below 100 μA Add:
 $\pm 10 \mu\text{V/excitation current}$ (units are in Ω)

Pulsed Excitation Current Compatibility: DC to 0.01 second pulse widths

Connections: 4 leads (2 red, 2 black), 70 cm (28") with spade lugs

Output Dial Adjustment

Resolution: 0.1°C or 0.1°F adjustment resolution for CL510-7; 1°C or 1°F adjustment resolution for CL510

Temperature Coefficient:

$\pm 0.05 \Omega/^\circ\text{C}$ ambient

Operating Temperature Range:

-25 to 60°C (-10 to 140°F)

Storage Temperature Range:

-25 to 60°C (-10 to 140°F)

Relative Humidity Range:

10% $\leq \text{RH} \leq 90\%$ [0 to 35°C (32 to 95°F)], non-condensing;

10% $\leq \text{RH} \leq 70\%$ [35 to 60°C (95 to 140°F)], non-condensing

Battery: 9V alkaline (included) provides 45 hours of continuous use, with low battery indication

Display: High-contrast graphic liquid crystal 5-digit display with 9.07 mm H (0.357") digits

Dimensions: 125.5 H x 46.2 W x 80 mm L (4.9 x 1.82 x 3.15")

Weight: 255 g (9 oz)



CL510, \$499, shown smaller than actual size.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
CL510-7	\$599	Multi-type RTD simulator (7 RTD curves)
CL510-(*)	499	Single RTD curve
SC-800	10	Soft carrying case

* Insert one RTD code from chart at left.

Comes complete with NIST certification (without test point), operator's manual and 9V battery.

Ordering Example: CL510-7, multi-type RTD simulator with 7 RTD curves, \$599.

OCW-2, OMEGACARESM extends standard 3-year warranty to a total of 5 years (\$107), \$599 + 107 = \$706.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters