



1/32 DIN Ramp/Soak Controllers with Fuzzy Logic

CN74000 Series Starts at **\$250**

Panel punches available, visit omega.com/panelpunches



- ✓ Large Dual Display
- ✓ Autotune
- ✓ Fuzzy Logic
- ✓ Universal Inputs
- ✓ Peak/Valley Indication
- ✓ Percent Output Indication
- ✓ 16-Segment Ramp/Soak Function
- ✓ Illuminated Keypad
- ✓ Free Software

The CN74000 Series controllers set a new standard in 1/32 DIN power, flexibility, and value. Despite their small size, these controllers are loaded with features, including multiple universal inputs, fuzzy logic, autotune, auto/manual capability, and 16-segment ramp and soak with adjustable time base. RS485 serial communication is optional.

Inputs

Input Types	Range
K Thermocouple	-200 to 2500°F (-129 to 1371°C)
J Thermocouple	-100 to 1600°F (-73 to 871°C)
T Thermocouple	-350 to 750°F (-212 to 398°C)
E Thermocouple	-100 to 1800°F (-73 to 982°C)
N Thermocouple	-100 to 2372°F (-73 to 1300°C)
R Thermocouple	0 to 3200°F (-17 to 1760°C)
S Thermocouple	0 to 3200°F (-17 to 1760°C)
B Thermocouple	75 to 3308°F (24 to 1820°C)
L (J DIN) Thermocouple	-100 to 1600°F (-73 to 871°C)
C Thermocouple	0 to 4208°F (-17 to 2320°C)
Pt100 RTD (0.00385)	-200 to 875°C (-328 to 1607°F)
Pt100 RTD (0.00392)	-200 to 875°C (-328 to 1607°F)
RTD, 120 Ω Nickel (0.00628)	-80 to 320°C (-112 to 608°F)
RTD, Pt1000 (0.00385)	-200 to 875°C (-328 to 1607°F)
0 to 20 mA*, 4 to 20 mA*	-1999 to 9999
0 to 10 Vdc*, -10 to 10 Vdc*, -10 to 10 mVdc*	-1999 to 9999

Note: All thermocouple and RTD inputs can be set for 0.1° display. If temperature goes above 999.9° or less than -199.9° the display will return to whole degree resolution.

* **Process Input Types:** The 0 to 20 mAdc, 4 to 20 mAdc, 0 to 10 Vdc, and 2 to 10 Vdc, inputs are fully scalable from a minimum of 100 counts span placed anywhere within the within the range of -1999 to 9999. Decimal point position is adjustable from the zero place (9999), tenths (999.9), hundredths (99.99), or thousandths (9.999).



CN74020, \$250, shown actual size.

Specifications

Selectable Inputs: Thermocouple, RTD, DC voltage or DC current

Display: Two 4-digit, 7-segment, 6.35 mm H (0.25") LEDs

Accuracy: ±0.25% of span, ±1 least significant digit

Supply Voltage: 100 to 240 Vac, nominal, 10 to 15%, 50 to 400 Hz

Single Phase: 132 to 240 Vdc, nominal, 10 to 20%

Power Consumption: 5 VA max

Operating Temperature: -10 to 55°C (14 to 131°F)

Memory Backup: Non-volatile memory, no batteries required

Control Output Ratings:

Relay: SPST, 3 A @ 240 Vac resistive; 1.5 A @ 240 Vac inductive; Pilot Duty Rating: 250 VA, 2 A @ 120 Vac or 1 A @ 240 Vac

Switched Voltage (Non-Isolated): 5 Vdc @ 20 mA

Weight: 114 g (4 oz)

Front-Panel Rating: NEMA 4X (IP66)

Panel Cut-Out: 45 x 22 mm (1.772 x 0.874")

Maximum Panel Thickness: 6.35 mm (0.25")

Panel Depth: 111.60 mm (4.395")

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CN74020	\$250	Single output, DC pulse
CN74030	250	Single output, relay
CN74033	275	Dual output, relay/relay
CN74053	315	Dual output, 4 to 20 mA/relay
CN74123	275	Dual output, DC pulse/relay and alarm
CN74133	275	Dual output, relay/relay and alarm

Options

Ordering Suffix	Add'l Price	Description
-C4*	\$80	RS485 communications
-LV	47	12 to 24 Vdc/Vac power

Accessories (Field Installable)

Model Number	Price	Description
CNQUENCHARC	\$10	Noise suppression kit, 110 to 230 Vac
CN7-485-USB-1	99	RS485 to USB mini-node converter

* Free CN7-A software download available at omega.com/cn74000

Comes complete with operator's manual.

Ordering Examples: CN74123-C4, dual-output controller, DC pulse and a mechanical relay output, alarm, RS485 communications, \$275 + 80 = \$355. CN74030, single output controller, relay, \$250.

Recommended Reference Book: Controller Tuning, PID, GE-2117, \$25. Visit omega.com/bobi for Additional Books.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters