



1/8 DIN Vertical Ramp/ Soak Temperature/ Process Controllers

CN7600 Series

\$147

All Models



- ✓ Dual 4-Digit LED Display
- ✓ 8 Ramp/Soak Programs, 8 Segments Each
- ✓ Universal Inputs
- ✓ Dual Controls
- ✓ RS485 Communications

The CN7600 Series Controller offers versatility and reliability for temperature and process monitoring applications. The CN7600 features dual outputs, universal input, and up to three additional alarm outputs. The second output can be configured as a third alarm output. Control methods include ON/OFF, PID, auto-tune or manual tune. PID control is supported with 64 ramp/soak control actions. RS485 communication is standard.

Specifications

Inputs: Thermocouple, RTD, DC voltage or DC current

Display: Two 4-digit, 7 segment 9.35 mm H (0.38") LEDs

PV: Red, **SV:** Green

Accuracy: ±0.25% span, ±1 least significant digit

Supply Voltage: 100 to 240 Vac, 50/60 Hz

Power Consumption: 5 VA max

Inputs

Input Types	Range
K Thermocouple	-200 to 1300°C (-328 to 2372°F)
J Thermocouple	-100 to 1200°C (-148 to 2192°F)
T Thermocouple	-200 to 400°C (-328 to 752°F)
E Thermocouple	0 to 600°C (32 to 1112°F)
N Thermocouple	-200 to 1300°C (-328 to 2372°F)
R Thermocouple	0 to 1700°C (32 to 3092°F)
S Thermocouple	0 to 1700°C (32 to 3092°F)
B Thermocouple	100 to 1800°C (212 to 3272°F)
L Thermocouple	-200 to 850°C (-328 to 1562°F)
U Thermocouple	-200 to 500°C (-328 to 932°F)
Pt100 RTD	-200 to 600°C (-328 to 1112°F)
0 to 50 mV	-999 to 9999
0 to 5 V	-999 to 9999
0 to 10 V	-999 to 9999
0 to 20 mA*	-999 to 9999
4 to 20 mA*	-999 to 9999

* Requires external 250 Ω precision shunt resistor, **OMX-R250** (sold separately). Available at omega.com/cn7800

CN7623, \$147, shown smaller than actual size.



Operating Temperature:
0 to 50°C
(32 to 122°F)

Memory Backup:
Nonvolatile memory

Control Output Ratings:

Relay: SPST, 5 A
@ 250 Vac resistive
Voltage Pulse: 14V,
10 to -20% (max 40 mA)

Current: 4 to 20 mA

Communication: RS485 MODBUS® communication protocol

Panel Cut-Out: 92 x 46 mm (3.60 x 1.8")

Maximum Panel Thickness: 9.50 mm (0.375")

Panel Depth: 79.2 mm (3.125")

Weight: 425 g (15 oz)

Front Panel Rating: IP66

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CN7623	\$147	Dual output, DC pulse/relay with RS485*
CN7633	147	Dual output, relay/relay with RS485*
CN7653	147	Dual output, 4 to 20 mA/relay with RS485*
CN7663	147	Dual output, 0 to 5 or 0 to 10 Vdc/relay with RS485*

Accessories (Field Installable)

Model No.	Price	Description
CNQUENCHARC	\$8	Noise suppression kit, 110 to 230 Vac
CN7-485-USB-1	99	RS485 to USB mini-node converter
OMX-R250	1	250 Ω precision resistor

* Free CN7-A software download available at omega.com/cn7600. Comes complete with operator's manual.

Ordering Examples: **CN7623**, dual-output controller, DC pulse, mechanical relay output, and RS485 communications, **\$147**.

CN7663, dual output controller, 0 to 5 or 0 to 10 Vdc, mechanical relay output, RS485 communications, **\$147**.

Recommended Reference Book: Controller Tuning/PID, **GE-2117, \$25.**

See Section Y For Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters