

# 1/8 DIN 4- and 7-Zone Process Controllers

Panel punches available, visit [omega.com/panelpunches](http://omega.com/panelpunches)

CN1504 Starts at **\$497** 4-Zone



CN1504-TC, \$497, shown actual size.

- ✓ 1/8 DIN Cutout
- ✓ On/Off and Full PID Controls
- ✓ Wide Range of Input Signals: Thermocouples, RTD's, Thermistors, 4 to 20 mA, 0 to 10 Vdc, Millivolts
- ✓ Input Type Selectable from Front Keys
- ✓ Scaling for Voltage, Current and Millivolt Signals
- ✓ Independent 7-Segment Ramp/Soak Profile for Each Zone
- ✓ 3 Display Modes: Setpoint Only, Process Only or Both Process and Setpoint
- ✓ Programmable Heating or Cooling Outputs
- ✓ Setpoint Deviation Display
- ✓ Captures Min/Max Readings for Each Zone

The CN1500 Series is a compact unit that offers the features of up to 7 controllers in a single 1/8 DIN enclosure. Careful design, high-functionality and compactness allow it to offer the best cost/performance ratio of any controller in its class. The input type for each zone is selected independently. Scaling and offset allow current and voltage signals to be converted and


displayed in engineering units. Temperature can be displayed in Centigrade or Fahrenheit. Additionally, each zone has its own ramp/soak profile with up to 7 segments. On/off, as well as PID control, is offered for optimum process stability. Processes that do not require tight control through complex tuning of PID parameters can be run under simple on/off control. Each zone has its own set of on/off and PID parameters and each zone can be programmed for heating or cooling. Setpoint deviation, positive as well as negative, can be viewed. Additional functions include min/max reading for each zone, indefinite program hold, automatic scanning and displaying of different zones and three display modes (setpoint only, process only or both setpoint and process). Power, control, and process signal connections are conveniently made with Euro-style plug-in connectors. Each zone has a 3-digit long engineering label that can be programmed to indicate the type of process being controlled, e.g., °C or °F for temperature, PSI for pressure, etc. Every controller's run status is indicated by LED's. Channel-to-channel scan time is also programmable.

**Specifications**  
**Input Types:** J, K, T, E, R, S, B, thermistor, RTD, 4 to 20 mA loop current, 0 to 10 Vdc, and 0 to 100 mV  
**CJC Error:** ±0.5°C (10 to 45°C)/ ±0.9°F (50 to 113°F)  
**Open Thermocouple Indication:** "HELP" displayed  
**Accuracy:**  
**Temperature Resolution:** 1°C/1°F  
**Voltage:** 0.05% FS  
**Current:** 0.05% FS  
**Resolution:**  
**Thermocouple and RTD:** 1°C/°F  
**Thermistor:** 0.1°C/°F  
**Display:** Red 7-segment LED display, 10 mm (0.39")  
**Display Test:** "8.8.8.8.8.8." on power-up  
**Scan Rate:** 2 channels/s (non-adjustable)  
**Channel Display Time:** Programmable, 1 to 999 seconds  
**Power Option:** 120 Vac 50/60 Hz, ±10%, (optional) 220 Vac 50/60 Hz, 12 Vdc @ 900 mA, ±20%  
**Scale:** Programmable, 1 to 30,000  
**Offset:**  
**Current:** 0 to 20.00  
**Voltage Input:** 0 to 10.000  
**Millivolt:** 0 to 100.00  
**Decimal Point:** Programmable, none, 10th, 100th, 1000th  
**Rate:** (PID) 0 to 500 seconds  
**Proportional Band:** 0 to 100% of span

**Reset:** 0.00 to 50.00 repeats/minute  
**On/Off Deadband:** Programmable, 0 to FS  
**Control Output:**  
 5 Vdc drive @ 50 mA open collector  
**Bezel Dimensions:**  
 65 H x 117 W x 178 D mm (2.5 x 4.6 x 7")  
**Panel Cutout:**  
 45 x 92 mm (1.77 x 3.66"); ½ DIN  
**Weight:** 992 g (2 lb 3 oz)  
**Ramp and Soak:** 7-segment programmable for each channel



DPS3104 companion scanners, \$468, also available.  
 Visit: [omega.com/dps3100\\_3200](http://omega.com/dps3100_3200)



KQSS-18G-12, quick disconnect thermocouple probes, \$23. See page A-56.



OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.

Recommended Reference Book:  
 Multisensor Instrumentation Design  
**GE-2539, \$85.**  
 See Section Y For Additional Books



## Input Types and Ranges

Thermocouple	Maximum Range	Accuracy (% of reading)
<b>J</b> Iron-Constantan	-200 to 1190°C -328 to 2174°F	±1°C ±1 count ±2°F ±1 count
<b>K</b> CHROME <sup>®</sup> GA-ALOME <sup>®</sup> GA	-170 to 1365°C -274 to 2489°F	±1°C ±1 count ±2°F ±1 count
<b>T</b> Copper-Constantan	-155 to 400°C -247 to 752°F	±1°C ±1 count ±2°F ±1 count
<b>E</b> CHROME <sup>®</sup> GA-Constantan	-185 to 915°C -300 to 1675°F	±1°C ±1 count ±2°F ±1 count
<b>R</b> Pt-13%Rh/Pt	0 to 1600°C 32 to 2900°F	±3°C ±1 count ±6°F ±1 count
<b>S</b> Pt-10%Rh/Pt	0 to 1600°C 32 to 2900°F	±3°C ±1 count ±6°F ±1 count
<b>B</b> Pt-30%Rh/Pt-6%Rh	470 to 1800°C 900 to 3300°F	±3°C ±1 count ±6°F ±1 count

RTD	Maximum Range	Accuracy (% of reading)
RTD 0.00385 (2-wire)	-200 to 800°C -328 to 1472°C	±1°C ±1 count ±2°F ±1 count
RTD 0.00392 (2-wire)	-100 to 450°C -148 to 842°F	±1°C ±1 count ±2°F ±1 count

Thermistor	Scaling Range	Accuracy (% of reading)
400 Series 2252 Ω @ 25°C	-8.0 to 100.0°C 17.2 to 212.0°F	±0.5°C ±1 count ±1.0°F ±1 count

Linear Input	Scaling Range	Accuracy (% of reading)
Current (4 to 20 mA)	1 to 30000	0.05% ±1 count
Millivolt (0 to 100 mV)	1 to 30000	0.05% ±1 count
Voltage (0 to 10 V)	1 to 30000	0.05% ±1 count

Input Code	Programmable Inputs
<b>TC</b>	J, K, T, E thermocouples, 4 to 20 mA, 0 to 10 Vdc
<b>RTD</b>	100 Ω RTD, 4 to 20 mA, 0 to 10 Vdc
<b>TH</b>	Thermistor (400 Series), 4 to 20 mA, 0 to 10 Vdc
<b>R</b>	R thermocouple, 4 to 20 mA, 0 to 10 Vdc
<b>S</b>	S thermocouple, 4 to 20 mA, 0 to 10 Vdc
<b>B</b>	B thermocouple, 4 to 20 mA, 0 to 10 Vdc
<b>MV</b>	100 mV, 4 to 20 mA, 0 to 10 Vdc

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model Number	Price	Description
<b>CN1504(*)</b>	<b>\$497</b>	4-zone controller
<b>CN1507(*)</b>	<b>767</b>	7-zone controller

\* Add input code from table above.

## Power Options

Ordering Suffix	Price	Description
<b>-1</b>	<b>NC</b>	240 Vac power
<b>-2</b>	<b>\$27</b>	12 Vdc power

## Accessory

Model No.	Price	Description
<b>CNQUENCHARC</b>	<b>\$8</b>	Noise suppression RC snubber (2 leads), 110 to 230 Vac

Comes complete with operator's manual.

\* Add input code from table above.

**Ordering Examples:** CN1504TC, 4-zone controller for thermocouple input, \$497.

OCW-3, OMEGACARE<sup>SM</sup> extends standard 2-year warranty to a total of 5 years (\$124), \$497 + 124 = \$621.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters