

1/32 DIN Dual-Zone Controllers with Fuzzy Logic

Panel Punches Available, Visit omega.com/panelpunches

CN79000 Series Starts at **\$316**



- ✓ Thermocouple Inputs Only
- ✓ Large Dual Display
- ✓ Illuminated Keypad
- ✓ Free Software

The CN79000 controller set a new standard in 1/32 DIN power, flexibility, and value. The CN79000 is a dual zone controller in the 1/32 DIN size. The CN79000 Series offers 5 thermocouple input types and each zone offers a single setpoint. Standard features include independent fuzzy logic, autotune, and peak/valley indication for each zone. RS485 Serial communication is optional.

Specifications

Display: Two 4-digit, 7 segment, 6.35 mm H (0.25") LEDs

Accuracy: ±0.25% of span, ±1 least significant digit

Supply Voltage: 100 to 240 Vac, nominal, 10 to 15%, 50 to 400 Hz

Single Phase: 132 to 240 Vdc, nominal, 10 to 20%

Power Consumption: 5 VA maximum

Operating Temperature: -10 to 55°C (14 to 131°F)

Memory Backup: Nonvolatile memory, no batteries required

Control Output Ratings:

Relay (Resistive): SPST, 3 A @ 240 Vac

Relay (Inductive): 1.5 A @ 240 Vac

Pilot Duty Rating: 250 VA, 2 A @ 120 Vac or 1 A @ 240 Vac

DC Pulse: 5 Vdc @ 20 mA (non-isolated)

Current: 4 to 20 mA

Weight: 114 g (4 oz)

Panel Cut-Out: 45 x 22 mm (1.772 x 0.874")

Front Bezel: 52.8 x 30.1 mm (2.080 x 1.184")

Maximum Panel Thickness: 6.35 mm (0.25")

Panel Depth: 111.60 mm (4.395")

Inputs

Input Types	Range
K Thermocouple	-129 to 1371°C (-200 to 2500°F)
J Thermocouple	-73 to 871°C (-100 to 1600°F)
E Thermocouple	-73 to 982°C (-100 to 1800°F)
N Thermocouple	-73 to 1300°C (-100 to 2372°F)
L (J DIN) Thermocouple	-73 to 871°C (-100 to 1600°F)

Note: All thermocouple inputs can be set for 0.1° display. If temperature goes above 999.9° or less than -199.9° the display will return to whole degree resolution.

Inputs are not isolated, must use ungrounded thermocouples.



CN79033, \$316.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
CN79022	\$316	Dual-zone, DC pulse/DC pulse
CN79033	316	Dual-zone, relay/relay
CN79053	350	Dual-zone, 4 to 20 mA/relay

Options

Ordering Suffix	Add'l Price	Description
-C4	\$80	RS485 communications*
-LV	47	12 to 24 Vdc/Vac

* Free CN7-A software download available at omega.com/cn79000

Comes complete with operator's manual.

Ordering Examples: CN79033, dual-zone, dual-mechanical relay outputs, \$316.

OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$77), \$316 + 77 = \$393.

CN79053, dual zone 4 to 20 mA relay, \$350.

Accessories (Field Installable)

Model Number	Price	Description
CNQUENCHARC	\$10	Noise suppression RC snubber (2 leads), 110 to 230 Vac
CN7-485-USB-1	99	RS485 to USB mini-node converter

Recommended Reference Book: Controller Tuning, PID, GE-2117, \$25. Visit omega.com/bobi for Additional Books



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters