

iSeries 1/32 DIN Temperature, Process and Strain PID Controllers

MONOGRAM

Panel Punches Available, Visit omega.com/panelpunches

CNi32 Series Starts at **\$205**



CNi3233, \$205, smaller than actual size.

- ✓ High Accuracy: $\pm 0.03\%$ Reading, 0.5°C ($\pm 0.9^{\circ}\text{F}$)
- ✓ First 1/32 DIN Instrument with Totally Programmable Color Displays Standard
- ✓ User-Friendly, Simple to Configure
- ✓ Free Software, ActiveX Controls
- ✓ Full Autotune PID Control
- ✓ Universal Inputs: Thermocouple RTD, Process Voltage/Current, Strain
- ✓ First 1/32 DIN Instrument Offering Both RS232 and RS485 Serial Communications in 1 Instrument (Optional)
- ✓ First 1/32 DIN Instrument with Built-in Excitation, 24 Vdc Standard
- ✓ Temperature Stability $\pm 0.04^{\circ}\text{C}/^{\circ}\text{C}$ RTD and $\pm 0.05^{\circ}\text{C}/^{\circ}\text{C}$ TC @ 25°C (77°F)
- ✓ NEMA 4 (IP65) Front Bezel
- ✓ First 1/32 DIN Instrument with Analog Output Selectable as a Control Output or as Retransmission of Process Variable
- ✓ 2 Control or Alarm Outputs Optional: DC Pulse, Solid State Relays, Mechanical Relays, Analog Voltage and Current
- ✓ Front Removable and Plug Connectors

The OMEGA® CNi32 is the iSeries controller in the extremely compact and increasingly popular 1/32 DIN size (22.5 x 45 mm cutout). The CNi32 is the most sophisticated and accurate instrument available in the small 1/32 DIN package, yet is still easy to configure.

The CNi32 handles more thermocouple, RTD, process voltage and current inputs than any other 1/32 DIN controller.

The CNi32 is the first 1/32 DIN controller with built-in excitation for transmitters or other devices, 24 Vdc @ 25 mA.

The CNi32 has built-in excitation for bridge transducers, 5 Vdc @ 40 mA or 10 Vdc @ 60 mA. When communications options are installed, external excitation may be used and ratiometric operation maintained by connecting the external excitation to the sense leads. Both 4- or 6-wire bridge configurations are supported for internal or external excitation. Non-ratiometric operation is supported

for voltage and current transducers and is also valuable in measuring offset and millivolt output of bridge devices during manufacturing and calibration. This model also features 10-point linearization which allows the user to linearize the signal input from extremely nonlinear transducers of all kinds.

The CNi32 introduces a number of unique features not yet found on any other 1/32 DIN instrument. The CNi32 is the first 1/32 DIN controller with a totally programmable display that can change color between **GREEN**, **AMBER**, and **RED** at any setpoint or alarm point. The unique 9-segment LED characters greatly improves alphanumeric representations.

The CNi32 is the first 1/32 DIN controller offering 2 SPDT Form C relays, instead of the single throw relays on typical 1/32 DIN controllers.

The CNi32 is the first to offer both RS232 and RS422/485 serial communications in 1 instrument (C24 option). Both ASCII protocol and modbus protocol are selectable from the menu.

The iSeries displays feature unique 9-segment LED characters, which greatly improves alphanumeric representations. The 7-segment LED characters found on most instruments are adequate for presenting numbers, but not letters.


Words are easier to read with the unique 9-segment LED characters on the iSeries, which makes operating and programming simpler and easier.




9-segment LED



7-segment display



9-segment display



Options

Ordering Suffix	Add'l Price	Description
-AL	N/C	Limit alarm version (simplified menu, alarms only, no PID control) ²
-SM	N/C	Simplified menu (on/off control or alarms, no PID) ³
Network Options		
-C24	\$60	Isolated RS232 and RS485/422, 300 to 19.2 Kb ¹
-EIS-2B	195	Industrial iServer Microserver™, serves 32 devices
Power Supply		
-DC	\$25	12 to 36 Vac/dc, 24 Vac ¹
Factory Setup		
-FS	50	Factory setup and configuration
-FS(RTD-1N)	75	Factory scaled for MIL-T-7990B nickel RTD input, 0 to 200°C (32 to 392°F)
-FS(RTD-2N)	75	Factory scaled for MIL-T-7990B nickel RTD input, -40 to 300°C (-40 to 572°F)
Software (Requires Network Option)		
OPC-SERVER LICENSE	\$295	OPC server/driver software license

¹ Excitation not available with "-DC", "-C24" or "-C4E" options.

² "-AL" option not available on models with analog (0 to 10V/0 to 20 mA) output.

³ "-SM" option not available on CNIS strain/process input models.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)			
Model No.	Price	Output 1	Output 2
Temperature/Pressure Input			
CNI3222	\$205	0.5 A SSR	0.5 A SSR
CNI3223	205	0.5 A SSR	Relay
CNI3224	205	0.5 A SSR	DC pulse
CNI3233	205	Relay	Relay
CNI3242	205	DC pulse	0.5 A SSR
CNI3243	205	DC pulse	Relay
CNI3244	205	DC pulse	DC pulse
CNI3252	205	Analog	0.5 A SSR
CNI3253	205	Analog	Relay
CNI3254	205	Analog	DC pulse
Strain/Process Input			
CNI3222	\$240	0.5 A SSR	0.5 A SSR
CNI3223	240	0.5 A SSR	Relay
CNI3224	240	0.5 A SSR	DC pulse
CNI3233	240	Relay	Relay
CNI3234	240	Relay	DC pulse
CNI3242	240	DC pulse	0.5 A SSR
CNI3243	240	DC pulse	Relay
CNI3244	240	DC pulse	DC pulse
CNI3252	240	Analog	0.5 A SSR
CNI3253	240	Analog	Relay
CNI3254	240	Analog	DC pulse

Comes complete with DPI32-B-COVER and operator's manual.

Ordering Examples: CNI3222-C24, 1/32 DIN PID controller with 2 solid-state relays for PID control and serial communications, both RS232 and RS485, \$205 + 60 = **\$265**.

CNI322-AL, 1/32 DIN strain/process controller, limit alarm version with SSR output, **\$240**.

Accessory

Model No.	Price	Description
DPP-1	\$400	1/32 DIN panel punch



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters