



1/16 DIN High/Low Limit Controller

CN63500 Series
Starts at
\$228

Panel Punches
Available Visit
[omega.com/
panelpunches](http://omega.com/panelpunches)



CN63500-R1, \$228, shown smaller than actual size.

- ✓ Dual 4-Digit LED Display
- ✓ Thermocouple or RTD Sensor Input
- ✓ Remote Reset Input
- ✓ Main Limit Output: 5 A Relay, Selectable for High or Low Trip Activation
- ✓ 5 A Relay Alarms (Optional)
- ✓ Optional NEMA 4X (IP65) Sealed Front Bezel
- ✓ Parameters Security Via Programmable Lockouts
- ✓ Dual Display



The CN63500 Series are temperature limit controllers, intended to provide an independent shutdown for thermal processes. The CN63500 accepts signals from a variety of temperature sensors (thermocouple or RTD elements), and its comprehensive programming allows it to meet a wide variety of application requirements. Dual 4-digit displays allow viewing of the process temperature and limit setpoint simultaneously. Front panel indicators inform the operator of the process and output status. The main limit output and alarm outputs are field-replaceable. The limit output is selectable for high or low trip activation. If the process temperature goes above the limit setpoint for a high trip, or below the limit setpoint for a low trip, the limit relay will de-energize to initiate a process shutdown. The limit output cannot be reset until the process temperature returns to the proper operating range; manual reset is required (local or remote). Sensor failure will initiate a process shutdown. Relay alarm(s) can be configured to activate according to a variety of actions (absolute high or low, deviation high or low and band in or out) with adjustable hysteresis. A standby feature suppresses the alarm during power-up until the process stabilizes outside the alarm region. The unit is constructed of lightweight, high-impact plastic case with a tinted front panel. The front panel meets NEMA 4X (IP65) specifications when properly installed. Multiple units can be stacked horizontally or vertically. Modern surface-mount technology, extensive testing, plus high-immunity to noise interference makes the CN63500 extremely reliable in industrial environments.

Specifications

Display: 2-line by 4-digit LED

Upper (Main) Display: 10.2 mm H (0.4") red LED

Lower (Secondary) Display:

7.6 mm H (0.3") green LED

Power:

Line Voltage Models: 85 to 250 Vac,
50/60 Hz, 8 VA

Low-Voltage Models:

DC Power: 18 to 36 Vdc, 7 W

AC Power: 24 Vac ±10%,
50/60 Hz, 9 VA

Memory: Non-volatile EEPROM

retains all programmable parameters and values

Environmental Conditions

Operating Range: FM rated @ 0 to 65°C,

UL rated @ 0 to 55°C

Storage Range: -40 to 80°C (-40 to 176°F)

Operating and Storage Humidity: 85% max relative
humidity (non-condensing) from 0 to 65°C (32 to 149°F)

Altitude: Up to 2000 m (6562')

Isolation Breakdown Ratings

AC Line With Respect to All Inputs and Outputs:

2300V for 1 minute (250V working)

Relay Contacts to All Other Inputs and Outputs:

2300 Vac

DC Power With Respect to Sensor Input: 50V working

(500V for 1 minute)

Connection: Wire clamping screw terminals

Weight: 0.17 kg (0.38 lb)

Input Specifications

Sensor Input


Sample Period: 100 ms

Step Response Time: Less than 300 ms typical,
400 ms max (to within 99% of final value)

Normal Mode Rejection: >40 dB @ 50/60 Hz

Common Mode Rejection: >120 dB, DC to 60 Hz

Overvoltage Protection: Input overload 120 Vac for 15 s max



Thermocouple Inputs

Types: T, E, J, K, R, S, B, N, linear mV, software selectable
Input Impedance: 20 MΩ, all types
Lead Resistance Effect: 0.25 μV/Ω
Cold-Junction Compensation: $\pm 1^\circ\text{C}$ typical, ($\pm 1.5^\circ\text{C}$ max), error over 0 to 65°C (32 to 149°F) max ambient temperature range; defeated for linear mV indication mode
Resolution: 1° for all types, or 0.1° for T, E, J, K, and N only

Thermocouple Type	Display Range	Wire Color	
		ANSI	BS1843
T	-200 to 400°C -328 to 752°F	(+) Blue (-) Red	(+) White (-) Blue
E	-200 to 750°C -328 to 1382°F	(+) Violet (-) Red	(+) Brown (-) Blue
J	-200 to 760°C -328 to 1400°F	(+) White (-) Red	(+) Yellow (-) Blue
K	-200 to 1250°C -328 to 2282°F	(+) Yellow (-) Red	(+) Brown (-) Blue
R	0 to 1768°C 32 to 3214°F	(+) Black (-) Red	(+) White (-) Blue
S	0 to 1768°C 32 to 3214°F	(+) Black (-) Red	(+) White (-) Blue
B	149 to 1820°C 300 to 3308°F	(+) Grey (-) Red	No standard
N	-200 to 1300°C -328 to 2372°F	(+) Orange (-) Red	(+) Orange (-) Blue
mV	-5.00 to 56.00mV	No standard	No standard

Failed Sensor Response:

Main Output: Sensor failure will initiate a process shutdown
Display: "OPEN"
Alarms: Upscale
Indication Accuracy: $\pm(0.3\%$ of span $+1^\circ\text{C})$ @ 23°C ambient after 20 minute warm-up (includes NIST conformity, cold-junction effect, A/D conversion errors and linearization conformity)
Span Drift (Maximum): 130 PPM/°C
Rtd Input: 2- or 3-wire, 100 Ω platinum, alpha = 0.00385 (DIN43760), alpha = 0.0039162
Excitation: 150 μA typical
Lead Resistance: 15 Ω max per input lead
Remote Resent Input: Internally pulled up to 5 Vdc 1 mΩ
 V_{IL} : 0.85V max
 V_{IH} : 3.65V min
 V_{IN} Max: 5.25 Vdc
 I_{OFF} : 1 μA max

Output Specifications

Limit and Alarm Output Relays
Contact Rating: 5 A @ 250 Vac or 30 Vdc (resistive load)
 $\frac{1}{10}$ HP @ 120 Vac (inductive load)
Life Expectancy: 100,000 cycles at max load rating (decreasing load increases life expectancy)
Limit Output:
CN63500-R1-AL1: Form "C" relay
CN63500-R1-AL2: Form "A" relay
 Selectable for high or low trip activation, if the process temperature goes above the limit setpoint for a high trip, or below the limit setpoint for a low trip, the limit relay will de-energize to initiate a process shutdown; the limit output cannot be reset until the process temperature returns to the proper operating range; manual reset is required (local or remote)
Alarm Outputs: 1 or 2 form "A" relays
Modes: Absolute high-acting, absolute low-acting, deviation high-acting, deviation low-acting, inside band-acting, outside band-acting
Reset Action: Programmable, automatic or latched; latched alarms can be reset regardless of limit exceed condition
Standby Mode: Programmable, enable or disable
Hysteresis: Programmable

RTD Type	Range
385	-200 to 600°C (-328 to 1100°F)
392	-200 to 600°C (-328 to 1100°F)
Ω	2.0 to 320.0 Ω

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
Standard Power Models (85 to 250 Vac, 50 to 60 Hz)		
CN63500-R1-AL1	\$228	Single output, form "C" relay, 1 alarm
CN63500-R1-AL2	238	Single output, form "A" relay, 2 alarms
Low-Voltage Models (18 to 36 Vdc)		
CN63500-R1-AL1-LV	\$244	Single output, form "C", 1 alarm
CN63500-R1-AL2-LV	255	Single output form "A" relay, 2 alarms

Comes complete with operator's manual.
Ordering Examples: **CN63500-R1 AL2**, 85 to 250 Vac power, single-output relay, 2 alarms, **\$238**.
CN63500-R1-AL1-LV, 18 to 36 Vdc power single-output relay, 1 alarm, **\$244**.

Accessories (Field Installable)

Model No.	Price	Description
CN6-RBDLA210	\$63	Output module, single-output, form "C" relay, 1 alarm
CN6-48111	63	Output module, single-output, form "A" relay, 2 alarms
DPP-4	475	$\frac{1}{16}$ DIN panel punch
PE-1318	90	Reference Book: Practical Process Control





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters