

1/16 DIN Ramp/Soak Controllers

CN7800 Series

\$108

All Models



Panel Punches Available, Visit omega.com/panelpunches



CN7833, \$108.

- ✓ Dual Display
- ✓ Autotune
- ✓ Universal Input
- ✓ 8 Ramp/Soak Programs, 8 Segments Each
- ✓ Programmable Repeat and Linking Features
- ✓ RS485 Communications
- ✓ Free Software
- ✓ 2 Alarm Standard

Monitor and control temperature or process applications with precision using the CN7800 Series controllers. The CN7800 Series provides dual LED displays for local indication of process value and setpoint value. Control methods include on/off, PID, auto-tune and manual-tune. PID control is supported with 64 ramp/soak control actions. Two additional alarm outputs are standard on the CN7800 Series. The alarm outputs can be quickly configured by using the 13 built-in alarm functions. The controller communicates easily with the built-in RS485 interface.

Inputs

Input Types	Range
K Thermocouple	-200 to 1300°C (-328 to 2372°F)
J Thermocouple	-100 to 1200°C (-148 to 2192°F)
T Thermocouple	-200 to 400°C (-328 to 752°F)
E Thermocouple	0 to 600°C (32 to 1112°F)
N Thermocouple	-200 to 1300°C (-328 to 2372°F)
R Thermocouple	0 to 1700°C (32 to 3092°F)
S Thermocouple	0 to 1700°C (32 to 3092°F)
B Thermocouple	100 to 1800°C (212 to 3272°F)
L Thermocouple	-200 to 850°C (-328 to 1562°F)
U Thermocouple	-200 to 500°C (-328 to 932°F)
Pt100 RTD	-200 to 600°C (-328 to 1112°F)
0 to 50 mV	-999 to 9999
0 to 5 V	-999 to 9999
0 to 10 V	-999 to 9999
0 to 20 mA*	-999 to 9999
4 to 20 mA*	-999 to 9999

* Requires external 250 Ω precision shunt resistor, OMX-R250 (sold separately). Available at omega.com/cn7800

Specifications

Inputs: Thermocouple, RTD, DC voltage or DC current
Display: Two 4-digit, 7 segment 6.35 mm H (0.25") LEDs (PV: red, SV: green)
Resolution: 1.0, 0.1 for thermocouples (except Types R, S and B)
Accuracy: ±0.25% span, ±1 least significant digit
Supply Voltage: 100 to 240 Vac, 50/60 Hz
Power Consumption: 5 VA max
Operating Temperature: 0 to 50°C (32 to 122°F)
Memory Backup: Non-volatile memory
Control Output Ratings:
Relay: SPST, 5 A @ 250 Vac resistive
Voltage Pulse: 14V, 10 to -20% (max 40 mA)
Current: 4 to 20 mA
Alarms: SPST, 3 A @ 250 Vac resistive
Communication: RS485 MODBUS® A-5-11/RTU communication protocol
Weight: 114 g (4 oz)
Front Bezel: 48 mm² (1.89 in²)
Panel Cut-Out: 45 mm² (1.77 in²)
Maximum Panel Thickness: 9.50 mm (0.375")
Panel Depth: 80 mm (3.15")

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
CN7833	\$108	Dual output, relay/relay, 2 alarms, RS485*
CN7823	108	Dual output, DC pulse/relay, 2 alarms, RS485*
CN7853	108	Dual output, 4 to 20 mA/relay, 2 alarms, RS485*

* Free CN7-A software download available at omega.com/cn7800

Accessories (Field Installable)

Model No.	Price	Description
CNQUENCHARC	\$8	Noise suppression RC snubber (2 leads), 110 to 230 Vac
OMX-R250	1	250 Ω precision resistor
CN7-485-USB-1	99	RS485 to USB mini-node converter

Comes complete with operator's manual.

Ordering Examples: CN7823, dual-output controller, DC pulse, mechanical relay output, and RS485 communications, \$108.

CN7853, dual output 4 to 20 mA relay two alarms, \$108.

Recommended Reference Book: Controller Tuning/PID, GE-2117, \$25.

See Section Y For Additional Books





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters