

iSeries

MONOGRAM

1/8 DIN Temperature, Process and Strain PID Controllers

Embedded Internet Connectivity!

- ✓ High Quality
- ✓ 5-Year Warranty
- ✓ High Accuracy: $\pm 0.5^{\circ}\text{C}$ ($\pm 0.9^{\circ}\text{F}$), 0.03% Reading
- ✓ User-Friendly, Simple to Configure
- ✓ Free Software
- ✓ Full Autotune PID Control
- ✓ Universal Inputs: RTD, Thermocouple, Process Voltage/Current, Strain
- ✓ Totally Programmable Color Displays Standard
- ✓ Built-In Excitation Standard
- ✓ 2 Control or Alarm Outputs: DC Pulse, Mechanical Relays, Analog Voltage and Current
- ✓ Embedded Internet Connectivity Available



CNi8 Series Starts at **\$325**



The universal temperature and process instrument (CNi models) handles 10 common types of thermocouples, multiple RTDs, and several process (DC) voltage and current ranges. This model also features built-in excitation, 24 Vdc @ 25 mA. With its wide choice of signal inputs, this model is an excellent choice for measuring or controlling temperature with a thermocouple, RTD, or 4 to 20 mA transmitter.

The strain and process instruments (CNiS models) measure inputs from load cells, pressure transducers, and most any strain gage sensor as well

as process voltage and current ranges. The CNiS has built-in 5 or 10 Vdc excitation for bridge transducers, 5 Vdc @ 40 mA or 10 Vdc @ 60 mA. (Any excitation voltage between 5 and 24 Vdc is available by special order). This CNiS model supports 4- and 6-wire bridge configurations, ratiometric and non-ratiometric measurements. The CNiS features fast and easy "in process" calibration/scaling of the signal inputs to any engineering units. This model also features 10-point linearization which allows the user to linearize the signal input from extremely nonlinear transducers of all kinds.

The OMEGA® CNi8 is a 1/8 DIN size [96 x 48 mm (3.7 x 1.9")] digital panel meter featuring the big iSeries color-changing display. The digits are twice the size of typical 1/8 DIN panel meters. The iSeries meters feature the only LED displays that can be programmed to change color between **GREEN, AMBER,** and **RED** at any setpoint or alarm point. The "CNi8" model is available as an extremely accurate programmable digital panel meter with no outputs or with dual outputs for controlling or alarming functions. Other options include isolated programmable analog output, serial communications, MODBUS and Ethernet. The user can easily program the CNi8 for any control or alarming requirement from simple on/off to full autotune PID with a choice of form C SPDT relays, solid state relays, DC pulse, and analog (voltage and current) outputs.

Fully isolated analog output for retransmission of the process value is available in addition to the control and alarm relays (specify model CNi8A33).

The CNi8 covers a broad selection of transducer and transmitter inputs with 2 input models:

Input Type	Range	Accuracy
Universal Process		
Process Voltage	0 to 100 mV, 0 to 1 V, 0 to 10 Vdc	0.03% rdg
Process Current	0 to 20 mA (4 to 20 mA)	0.03% rdg
Excitation	24 V @ 25 mA	—
Universal Strain/Process		
Process Voltage	0 to 100 mV, -100 to 1 V, 0 to 10 Vdc	0.03% rdg
Process Current	0 to 20 mA (4 to 20 mA)	0.03% rdg
Excitation	5 V @ 40 mA, 10 V @ 60 mA	—
Nickel RTD Input (FS Required)		
RTD-1N (Nickel MIL-T-7990B)	0 to 200°C (32 to 392°F)	0.1°C (0.2°F)
RTD-2N (Nickel MIL-T-7990B)	-40 to 300°C (-40 to 572°F)	0.3°C (0.5°F)
Temperature		
J Iron-Constantan	-210 to 760°C (-346 to 1400°F)	0.4°C (0.7°F)
K CHROMEGA™-ALOMEGA™	-270 to -160°C/-160 to 1372°C (-454 to -256°F/-256 to 2502°F)	1.0°C/0.4°C (1.8°F/0.7°F)
T Copper-Constantan	-270 to -190°C/-190 to 400°C (-454 to -310°F/-310 to 752°F)	1.0°C/0.4°C (1.8°F/0.7°F)
E CHROMEGA™-Constantan	-270 to -220°C/-220 to 1000°C (-454 to -364°F/-364 to 1832°F)	1.0°C/0.4°C (1.8°F/0.7°F)
R Pt/13%Rh-Pt	-50 to 40°C/40 to 1768°C (-58 to 104°F/104 to 3214°F)	1.0°C/0.5°C (1.8°F/0.9°F)
S Pt/10%Rh-Pt	-50 to 100°C/100 to 1768°C (-58 to 212°F/212 to 3214°F)	1.0°C/0.5°C (1.8°F/0.9°F)
B 30%Rh-Pt/6%Rh-Pt	100 to 640°C/640 to 1820°C (212 to 1184°F/1184 to 3308°F)	1.0°C/0.5°C (1.8°F/0.9°F)
C 5%Re-W/26%Re-W	0 to 2320°C (32 to 4208°F)	0.4°C (0.7°F)
N Nicrosil-nisil	-250 to -100°C/-100 to 1300°C (-418 to -148°F/-148 to 2372°F)	1.0°C/0.4°C (1.8°F/0.7°F)
L J DIN	-200 to 900°C (-328 to 1652°F)	0.4°C (0.7°F)
RTD Pt, 0.00385, 100, 500, 1000	-200 to 900°C (-328 to 1652°F)	0.4°C (0.7°F)
RTD Pt, 0.00392, 100, 500, 1000	-200 to 850°C (-328 to 1652°F)	0.4°C (0.7°F)

iSeries change color

PATENTED




Totally Programmable Color Displays


The OMEGA® i/8, i/16, and i/32 are the first complete series of 1/8, 1/16 and 1/32 DIN process control instruments with totally programmable color displays. The display can be programmed to change color at any setpoint or alarm point.



Dimensions: mm (in)



TOP VIEW



MOST POPULAR MODELS HIGHLIGHTED!

Options

Ordering Suffix	Add'l Price	Description
-AL	N/C	Limit alarm version (simplified menu, alarms only, no PID control)*3*4
-SM	N/C	Simplified menu (on/off control or alarms, no PID)*6
Network Options		
-EI	\$55	Ethernet with embedded Web server
-C24	60	Isolated RS232 and RS485/422, 300 to 19.2 Kb*2
-C4EI	115	Ethernet with embedded Web server + isolated RS485/422 hub for up to 31 devices*1
Power Supply		
-DC	\$25	12 to 36 Vac/dc, 24 Vac*2*5
Factory Setup		
-FS	\$50	Factory setup and configuration
-FS(RTD-1N)	75	Factory scaled for MIL-T-7990B nickel RTD input, 0 to 200°C (32 to 392°F)
-FS(RTD-2N)	75	Factory scaled for MIL-T-7990B nickel RTD input, -40 to 300°C (-40 to 572°F)
Software (Requires Network Option)		
OPC-SERVER LICENSE	\$295	OPC server/driver software license

*1 Ethernet options are not available for the i8A controller.

*2 "-DC", "-C24", and "-C4EI" not available with excitation.

*3 Analog output is not available with "-AL" units.

*4 CNi8A-AL contains 1 alarm and 1 analog retransmission

*5 20 to 36 Vdc for CNi8A.

*6 "-SM" option not available on CNiS strain models.

To Order (Specify Model Number)

Model No.	Price	Output 1	Output 2
2 Control Outputs			
CNi833	\$325	Relay	Relay
CNi844	325	DC pulse	DC pulse
CNi843	325	DC pulse	Relay
CNi842	325	DC pulse	0.5 A SSR
CNi822	325	0.5 A SSR	0.5 A SSR
CNi823	325	0.5 A SSR	Relay
CNi824	325	0.5 A SSR	DC pulse
CNi853	325	Analog	Relay
CNi854	325	Analog	DC pulse
CNi852	325	Analog	0.5 A SSR
2 Control Outputs with Isolated Analog Output			
CNi8A33	\$385	Relay	Relay
CNi8A44	385	DC pulse	DC pulse
CNi8A43	385	DC pulse	Relay
CNi8A42	385	DC pulse	0.5 A SSR
CNi8A22	385	0.5 A SSR	0.5 A SSR
CNi8A23	385	0.5 A SSR	Relay
CNi8A24	385	0.5 A SSR	DC pulse
Strain/Process Input with 2 Control Outputs			
CNiS833	\$370	Relay	Relay
CNiS834	370	Relay	DC pulse
CNiS844	370	DC pulse	DC pulse
CNiS843	370	DC pulse	Relay
CNiS842	370	DC pulse	0.5 A SSR
CNiS822	370	0.5 A SSR	0.5 A SSR
CNiS823	370	0.5 A SSR	Relay
CNiS824	370	0.5 A SSR	DC pulse
CNiS853	370	Analog	Relay
CNiS854	370	Analog	DC pulse
CNiS852	370	Analog	0.5 A SSR

Comes complete with operator's manual.

Ordering Examples: CNi8A22, 1/8 DIN temp/process controller with isolated analog output and 2 SSR outputs, \$385. CNiS833, 1/8 DIN strain/process controller with 2-relay outputs, \$370.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters