

¼ DIN Digital Temperature and Limit Controllers

Panel punches available, visit omega.com/panelpunches

CN8100 Series Starts at **\$315**



- ✓ Large, Easy-to-Read LED, Selectable for Either Setpoint or Process Temperature
- ✓ Type J or K Thermocouple Input
- ✓ Adjustable Output Hysteresis to Prevent Rapid Cycling Around Setpoint Temperature
- ✓ Adjustable Deviation Alarm Flashes When Measured Temperature Exceeds or Falls Below Setpoint Temperature
- ✓ NEMA 4X (IP65) Front Bezel, Splash-Proof and Resistant to Dust
- ✓ Discrete Status Indicators Illuminate When Temperature Display, Setpoint Display or Heat/Cool Output Is Active
- ✓ Auto Tuning (CN8101 and CN8102)

The CN8100 Series controller is a low-cost, general purpose ¼ DIN temperature controller, ideal for OEM or replacement applications. Microprocessor-based and accurate to $\pm 0.3\%$ FS, it may be ordered as either a PID controller, on/off controller or limit safety device.

As a separate safety feature to your control application, the CN8121-R1 limit controller provides reliable high/low temperature limit shut-off control for most machine and process control applications including environmental chambers,



CN8102-R1-R2, dual output PID controller, \$342, shown smaller than actual size.

furnaces, ovens and packaging machinery. As a high-limit device, these controllers have a normally energized SPST latching output relay which becomes de-energized whenever the process variable (PV) exceeds a selected setpoint value. Reset of the latching output relay is done by holding the parameter button for 3 seconds on the front panel of the controller, or by cycling power to the controller.

Specifications

General

Line Voltage: 85 to 250 Vac, 50/60 Hz, 120 to 300 Vdc (auto polarity)

Display: 3-digit, 14 mm (0.56") orange LED

Discrete Indicators:

Setpoint: Amber

Actual: Amber

Heat: Orange

Cool: Orange

Power Consumption:

Less than 6 VA (instrument)

Front Panel Rating: NEMA 4X (IP65)

Operating Temperature:

0 to 60°C (32 to 140°F)

Humidity Tolerance: 90% RH maximum, non-condensing

Memory Protection:

Solid-state, non-volatile memory

Connections: Fast-on style (0.250" wide)

Panel Cutout: ¼ DIN, 92 mm² (3.622 in²)

Dimensions: 96 x 96 x 6.35 mm bezel (3.78 x 3.78 x 0.25")

Panel Depth: 88.9 mm (3.5")

Weight: 737 g (1 lb. 10 oz)

Performance

Accuracy: $\pm 0.3\%$ of FS, ± 1 digit

Setpoint Resolution: 1 count

Repeatability: ± 1.0 count

Temperature Stability: 5 μ V/°C maximum

TC Cold End Tracking: $\pm 0.05^\circ\text{C}/^\circ\text{C}$ ambient

Noise Rejection: Common mode
>100 dB, Series mode >70 dB
Process Sampling: 3.7 Hz (270 ms)

Available Inputs:

Thermocouple:

CN8110: Type J

CN8120: Type J

CN8100: Type J or K

Maximum lead resistance,
100 Ω for rated accuracy

Control Characteristics:

Control Hysteresis: 1 to 140°C
(2 to 252°F)

Display Offset: -70 to 70°C
(-126 to 126°F)

Deviation Alarm: Off, 1 to 140°C
(Off, 1 to 252°F)

Outputs: Electromechanical relay,
5 A @ 250 Vac, 5 A @ 30 Vdc,
solid-state relay, 120/240 Vac,
0 voltage switched, 2 A continuous
(output 1), 0.5 A continuous (output 2)
10 A surge @ 25°C (77°F), pulsed DC
5V for external SSR

CN8121-R1,
\$363.

CN8111-R1, \$317.

CN8102-R1-R2,
\$342.

Controllers shown
smaller than actual size.

Output Options

Output Type	First Output Suffix- Heat Only (Reverse)	Second Output Suffix- Alarm (CN8112) or Cool Only (Direct—CN8102)
5 A Relay	-R1	-R2
AC SSR	-T1	-T2
DC Pulse	-D1	-D2

Note: “-T1” = 2A ac SSR, “-T2” = 1A ac SSR.



OMEGACARESM extended warranty program
is available for models shown on this page.
Ask your sales representative for full details
when placing an order. OMEGACARESM
covers parts, labor and equivalent loaners.

Input Types, Ranges and Setpoint Limits, °C/°F Switchable

Input Types for PID Control	Range
J Iron–Constantan	0 to 485°C (32 to 905°F)
K CHROME [®] –ALOMEGA [®]	-17 to 537°C (0 to 999°F)
Input Type for On/Off and Limit	Range
J Iron–Constantan	0 to 485°C (32 to 905°F)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CN8101-(*)	\$315	PID controller, single output with Type J and K thermocouple input
CN8102-(*)-(*)	342	PID controller, dual output with Type J and K thermocouple input
CN8111-(*)	317	On/off controller, single output with Type J thermocouple input
CN8112-(*)-(*)	335	On/off controller, single control output and alarm output with Type J thermocouple input
CN8121-R1	363	High-limit controller, single relay output with Type J thermocouple input, FM approved
DPP-6	575	¼ DIN panel punch
PE-1318	120	Reference Book: Practical Process Control

Comes complete with operator's manual.

* Specify output type from Output Options table.

Ordering Examples: CN8102-R1-R2, ¼ DIN dual mechanical relay output PID controller, \$342.

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$86), \$342 + 86 = \$428.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters