

Microprocessor-Based Temperature/Relative Humidity Recorder

CT485B Series

\$642

Basic Unit includes
120 double sided charts



Shown smaller
than actual size

For additional
features and
models, please
consult sales or
visit omega.com

The CT485B is NO LONGER AVAILABLE, Please
review our LATEST [CTXL SUPERRECORDER\(tm\)](#)



- ✓ Available in Computer Room White or Charcoal Gray
- ✓ Versatile Remote Mounting Sensor
- ✓ Convenient Front Panel Programming
- ✓ 200 mm (8") Chart for 1, 7, or 32-Day Recording
- ✓ Fully Electronic Microprocessor Control
- ✓ Benchtop or Wall Mounted
- ✓ Alarm Contact Standard
- ✓ 1,2,3 Year Extended Warranty Comes with Extra Pens, Paper, Batteries
- ✓ Sensors Not Recommended for Use in a Corrosive Environment
- ✓ Companion Pressure and pH Recorder Available

Complete with 120 Assorted Double-Sided Charts, 2 Sets of Pens, 1.8 m (6') Remote Sensor Cable, Wall Mounting Kit, Cal-Lock Kit, Batteries, and ac Adaptor

All 220 Vac Models
are CE Labeled

Covered by U.S. and international patents and pending applications

The new Model CT485B completely self-contained temperature/relative humidity recorder is microprocessor based to accurately measure, indicate and record temperature and relative humidity.

This rugged unit comes standard with alarms. They contain a single, integral relay contact which closes in response to an alarm condition. Simultaneous high and low alarm points for temperature and relative humidity are user selectable. When the current conditions exceed any of the preset values, the 2 Amp relay contact closes and an audible alarm sounds.

Flipping open a hinged front panel door permits access to the power switch and controlling functions of the recorder. The

door comes with a locking mechanism. The user may select 1, 7 or 32 day operation, program the instrument to recording °C or °F, and access alarm and calibration controls or max/min functions.

A separate 3-position switch next to the digital display selects a °C, °F or %RH readout. The chart drive is stepper controlled for precision, and a unique magnetic retaining knob eliminates the possibility of paper tear.

Calibration of alarm models is digital, and a user may make calibration adjustments in the field using the convenient panel pushbuttons. An optional calibration lockout cover prevents unauthorized changing of calibration codes. A stabilizing arm provides added stability for benchtop

use. The arm conveniently rotates under the unit for wall mounting. Recessed rear mounting slots and a wall template enable easy wall mounting. A decorative cover for the stabilizing arm is supplied for wall mount use. A standard 110 or 220 Vac (depending on model ordered) power adaptor is supplied for continuous long-term operation, along with four D-cell batteries for backup power or field use. Each unit includes 1.8 m (6') of cable for remotely mounting the sensor. A sensor holder clip is provided.

Units come standard with two chart light bulbs. When using the ac power adaptor, these bulbs provide easy viewing of the chart in dimly lit conditions. A switch is provided to allow the chart lights to be turned on or off.

OMEGACARESM extended warranty program is available for this model. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equipment loaners.

Specifications

Measurement Inputs: Temperature and humidity, with plug-in external sensor, removable for remote location, 2 m (6') extension cable included; 0.02 to 1.20 Vdc signal with voltage input adaptor

TEMPERATURE

Range: -17 to 49°C (2 to 120°F)

Accuracy: ±1°C

Sensor: Solid state

Response Time: 5 minutes for 63% step change

Display Resolution: 1°C/1°F, backlit LCD

HUMIDITY

Range: 2 to 98% RH

Accuracy: ±3% @25°C, between 20 and 90% of range (±5% below 20% and above 90% @25°C)

Sensor: Resistive polymer.

Not recommended for use in corrosive air environments

Response Time: 5 minutes for a 30 to 80% step change

Display Resolution:

1% RH 2½ digit LCD, backlit, 12.7 mm (0.5") high; low battery

Display Modes: Front panel switchable between °C, °F and %RH for continuous digital display; max/min storage for both temperature and humidity or flashing to indicate alarm condition

ELECTRONICS

Type: Microprocessor-controlled and linearized high and low peak hold for both temperature and humidity, re-initializes position at every chart change

CHART

Type: 203 mm (8") circular, linear radial divisions, double sided; 1, 7 and 32 days, °C and °F scales

CHART DRIVE

Type: Stepper motor

Ranges: 1, 7 and 32 day, selectable

Accuracy: 1% of rotation

Chart Hold Down: magnetic hub lock

RECORDING PENS

Type: Disposable fiber tip, red for temperature, blue for humidity

PEN DRIVES

Type: Motorized linear screw drive

Deadband: 1°F, 1% RH

Zero: Automatic zero during chart change or power interruption


Penlift: Automatic on door opening; pens are door mounted and swing clear of the chart when door opens

Pen Arms: Clear plastic to allow full chart viewing

NEW BACKLIT DISPLAY FEATURE ON AC POWER!

Benchtop and/or Wall Mounted!

The CT485B is NO LONGER AVAILABLE, Please review our LATEST [CTXL SUPERRECORDER\(™\)](#)




Available in computer room white or charcoal gray.

CE labeled 220 Vac model shown with included ferrite core noise suppressor (included on CE models)

Specialty Charts for Museum/Art Gallery, Hospitals, Labs/Clean Rooms and Computer Room/Office Applications

Custom Charts Available



Convenient blue and red circles tell you at a glance if an out-of-range condition occurs

OPERATING CONDITIONS (RECORDER)

Temperature: 0 to 49°C (32 to 120°F)
Humidity: 0 to 90% RH, non-condensing

OPERATING CONDITIONS (SENSOR REMOTE)

Sensors not recommended for use in a corrosive environment
Temperature: -17 to 49°C (2 to 120°F)
Humidity: 0 to 98% RH

ALARMS

Alarms: User-selectable for high or low temperature and humidity

Audible Alarm: Integral piezoelectric beeper

Alarm Relay Contacts:

1 Amp, 30 Vdc normally open, single pole, single throw (SPST)

Power (Recorder): Four D cells batteries (included) and 9 Vdc/110, 50/60 Hz power adaptor (supplied); 220 Vac power adaptor supplied where applicable

Battery Life: more than 1 month continuous operation in 32-day mode (average conditions)

Power Requirements: 300 mA "normal" during pen movement for battery (dc) power; 500 mA "normal" during pen movement for ac power using ac adaptor with chart lights on

Note: the light bulbs drain 200 mA of current

DC Power Jack Voltage:

8.3 to 12.4 Vdc (nominal 9 Vdc), 1 Amp max.

MECHANICAL

Dimensions: 33.5 H x 27.1 W x 6.7 cm D (13 3/16 x 10 1/16 x 2 5/8")

Weight: Approx. 3.2 kg (7 lb) including batteries

Mounting: "Keyhole" slots for wall mounting; foot cover for benchtop use

Case: Rugged ABS plastic

ANALOG VOLTAGE

INPUT ADAPTOR

Input: 20 mVdc to 1200 mVdc records as -17 to 49°C, (2 to 120°F) input protection up to 20 Vdc or 10 Vac RMS

Input Impedance: 330 Kohms min.

Input Connections: Banana jacks, 19 mm (0.75") spacing


Cable Length: 305 mm (12")

For Companion Recorders, Please see Section S

New!
Backlit Display
feature on ALL
benchtop and/or wall
mounted models!



The CT485B is NO LONGER AVAILABLE, Please review our LATEST [CTXL SUPERRECORDER\(tm\)](#)



pH Model



Model CTPH

\$970

Basic Unit



Pressure/Temp Model

Model CT585

\$700

Basic Unit

ALL MODELS AVAILABLE FOR FAST DELIVERY!

The CT485B is NO LONGER AVAILABLE, Please review our LATEST [CTXL SUPERRECORDER\(tm\)](#)


To Order (Specify Model Number)

Model Number	Price	Description
CT485B-110V-G-AL	\$642	Gray, 110 Vac, with alarms and relay contacts
CT485B-110V-W-AL	650	White, 110 Vac, with alarms and relay contacts
CT485B-220V-G-AL	662	Gray, 220 Vac, with alarms and relay contacts
CT485B-220V-W-AL	670	White, 220 Vac, with alarms and relay contacts


Comes with complete operator's manual, batteries, ac adaptor, assorted charts, pen set, remote sensor cable, and wall mounting kit.

Ordering Example: CT485B-220V-W-AL, CE labeled white recorder with alarms and relay contacts, 220 V, with 120 double sided charts (\$670), and CT485-CWC, package of 100, 7 day, °C (celsius) temperature measurement charts (\$19), \$670 + 19 = **\$689.**

OCW-3 OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$167), \$670 + 167 = **\$837.**



Shown smaller than actual size



**Charts—Each Unit Includes:
120 Double-Sided Charts FREE!**
(20 each of 1-day, °F; 1-day, °C; 7-day, °F; 7-day, °C; 32-day, °F; 32-day °C).
Additional charts can be ordered below as 1 pack of 100 or 6 packs of 100

Model No.	Price	Description
CT485-CDF	\$19	100 Charts, 1 day am/pm, °F
CT485-CDC	19	100 Charts, 1 day am/pm, °C
CT485-C24F	10	20 Charts, 24 hour clock, °F
CT485-C24C	10	20 Charts, 24 hour clock, °C
CT485-CWF	19	100 Charts, 7 day, °F
CT485-CWC	19	100 Charts, 7 day, °C
CT485-CMF	19	100 Charts, 32 day, °F
CT485-CMC	19	100 Charts, 32 day, °C
CT485-CSP	19	120 Charts, 20 of each style
CT485-CDF-6	87.50	600 Charts, 1 day, °F
CT485-CDC-6	87.50	600 Charts, 1 day, °C
CT485-CWF-6	87.50	600 Charts, 7 day, °F
CT485-CWC-6	87.50	600 Charts, 7 day, °C
CT485-CMF-6	87.50	600 Charts, 32 day, °F
CT485-CMC-6	87.50	600 Charts, 32 day, °C

Note: all charts are double sided.
Ordering Example: CT485-CWC-6 package of 600 double sided charts, 7 days, with °C (celsius) temperature measurements, **\$87.50.**

Specialty Paper
(All double-sided, packages of 20 charts)

Model Number	Price	Description
CT485-MW(*)	\$20	Museums/art galleries, 7 days (in °C or °F) 18.3 to 22.2 (65 to 72°F), 40 to 50% RH
CT485-MM(*)	20	Museums/art galleries, 32 days (in °C or °F) 18.3 to 22.2°C (65 to 72°F), 40 to 50% RH
CT485-HW(*)	20	Hospitals, 7 days (in °C or °F) 20 to 23.3°C (68 to 74°F), 40 to 50% RH
CT485-HM(*)	20	Hospitals, 32 days (in °C or °F) 20 to 23.3°C (68 to 74°F), 40 to 50% RH
CT485-LW(*)	20	Lab, clean rooms, 7 days (in °C or °F) 20 to 23.9°C (68 to 75°F), 40 to 55% RH
CT485-LM(*)	20	Lab, clean rooms, 32 days (in °C or °F) 20 to 23.9°C (68 to 75°F), 40 to 55% RH
CT485-PW(*)	20	Computer rooms/offices, 7 days (in °C or °F) 18.3 to 23.9°C (65 to 75°F), 45 to 60% RH
CT485-PM(*)	20	Computer rooms/offices, 32 days (in °C or °F) 18.3 to 23.9°C (65 to 75°F), 45 to 60% RH
CT485-WMC	20	Wine storage 32 days, 10 to 15.6°C, 60 to 70% RH
CT485-WMF	20	Wine storage 32 days, 50 to 60°F, 60 to 70% RH

*Insert C (for °C) or F (for °F)
Ordering Example: CT485-MWC specialty paper for museums and art galleries, 7 days, with °C (celsius) temperature measurements, **\$20.**

Accessories

Model Number	Price	Description
CT485-CABLE-6W	\$23.75	2 m (6') remote sensor cable, white
CT485-CABLE-6G	23.75	2 m (6') remote sensor cable, gray
CT485B-CAL-LABEL	5	Calibration lockout cover labels (sheet of 10)
CT485B-CLIP-KIT	5	Sensor clip kit
CT485-AMV-W	22.50	Analog voltage input adaptor (cable), white
CT485-AMV-G	22.50	Analog voltage input adaptor (cable), gray
CT485-PS	10	Pen set, red and blue, package of 1 each
CT485-PS-6	52	Pen set, red and blue, package of 6 each
CT485B-CAL-KIT	75	Calibration kit
CAL-3-HU	125	NIST Traceable Calibration
CT485B-RP-W	80	White replacement probe
CT485B-RP-G	80	Gray replacement probe



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters