

Cryogenic Autotune Temperature Controllers



CYC324-03, \$2300, shown smaller than actual size.

CYC320 Series
Starts at

\$2300



- ✓ Autotune PID
- ✓ For Temperature Control from 1.4 to 800 K
- ✓ Electronic Accuracy and Control Stability to $\pm 0.1^{\circ}\text{C}$
- ✓ Autotuning PID Parameters Automatically Determined
- ✓ Manual Tuning of PID Parameters via Front Panel
- ✓ Silicon Diode, 100 Ω Pt RTD, or Thermocouple Input
- ✓ Ability to Store One User Defined Calibration Curve
- ✓ RS232C Communications Standard
- ✓ 25 Watt DC Heater Output
- ✓ Small Rack Mount Package
- ✓ Isolated Current Source Allows True 4-Wire Sensor Readings For High Instrument Accuracy

The CYC320 Series cryogenic temperature controllers offer a simple, low cost answer to basic low temperature control needs. They incorporate a scroll type entry so that setup can easily be accomplished from the front keypad. Three models are available to accommodate either silicone diode, RTD or thermocouple input. The operator can also enter a user-defined curve, for a custom sensor. This curve can have up to 97 points plus two end points. The curve values are entered over the standard RS232 interface.

A cryogenic system is a complex arrangement of thermal resistances and heat capacities which are represented by thermal mass and time constants.

The CYC320 Series analyzes this system's operating parameters on-line. The autotune feature increases the user's efficiency by automatically calculating the correct proportional (gain), integral (reset) and derivative (rate) control parameters within minutes. Once set, the PID values are only modified when the system characteristics change. Time spent adjusting or fine-tuning the controller is eliminated, leaving the user with more time to experiment with something other than controller settings! Heater output of the CYC230 Series is a variable dc current for quiet, stable control.



CYC321-01 rear panel.

CYC320-HTR cartridge heater, \$70.

Specifications

CYC321: Silicon diode, 1.4 K to 475 K

CYC322: 100 Ω platinum RTD, 30 K to 800 K

CYC324: Ch-AuFe (0.07%) thermocouple, 4 K to 325 K;

Type E: 40 K to 425 K

Type K: 90 K to 325 K

Type T: 90 K to 485 K

Curve Storage: Memory space for one 99 point user defined curve

Display: 8 digit alphanumeric LED display

Resolution: 0.1 (K or °C)

Instrument Accuracy (When Used With):

Silicon Diode: ±0.2 mV ±0.02% rdg

100 Ω RTD: ±20 mV ±0.05% rdg

Thermocouple: ±2 μV ±0.05% rdg

System Accuracy: Instrument accuracy plus sensor accuracy; ranges from 0.1 K at 4.2 K to 0.6 K at 800 K

Repeatability: ±0.1 (K or °C) or better (dependent on sensor sensitivity)

TEMPERATURE CONTROL CHARACTERISTICS

Setpoint Resolution: 0.1 (K or °C)

Control Stability: Better than ±0.1 K in a properly designed system

Automatic Control Modes: P, PI, or PID control user selectable

Manual Control Modes: Proportional (Gain) 0 to 999; Integral (Reset) 1 to 999 sec; Derivative (Rate) 0 to 50% of Integral Time

Heater Output: 25 Watts/1 A at 25 V compliance

Heater Load: 25 Ω or greater. automatic shutoff if load < 20 Ω

GENERAL

Communications: RS232C 3-wire, half-duplex, asynchronous transmission at 300 or 1200 baud; RJ-11 modular socket; user may input setpoint, heater on/off, curve data; output data includes temperature, setpoint, heater %, external curve

Response Time: 1 sec. electronic data update rate (typical)

Power: 110 or 220 Vac selectable, 65 VA

Dimensions: 217 L x 90 W x 317 mm D (8.5 x 3.5 x 12.5")

Weight: 2.7 kg (6 lb)

CYC320-HTR

Cartridge Heater: Nickel-Chromium resistance wire with MgO insulation, 2 solid pins



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Input Type
CYC324-03	\$2300	Thermocouple controller

Comes complete with sensor input connector power cord, double banana plug for heater output and operator's manual.

Note: Units are calibrated at no additional cost.

Ordering Example: CYC324-03, silicone diode controller, CYC320-SHC, heater cable assembly, CY7-SD7, silicon sensor, \$2300 + 175 + 140 = **\$2615.**

OCW-3, OMEGACARESM extends the standard 1-year warranty to a total of 4 years (\$350), \$2615 + 350 = **\$2965.**

Accessories

Model No.	Price	Description
CYC320-SHC	\$175	Cable assembly for CYC321 and CYC322
CYC320-HTR	70	Cartridge heater, 25 W
CYD200-C	30	RJ11 jack and 3 m (10') of cable, RS232 adaptor
CYD200-D	51	RJ11 to DB25 adaptor, connects RJ11 to 25-pin RS232 serial port
CYD200-DB9	51	RJ11 to DB9 adaptor, connects RJ11 to 9-pin RS232 serial port

For information on precision calibration option yielding highest readout accuracy, please contact our Cryogenic Applications Engineers at 1-800-TC-OMEGA.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters