

# Miniature Benchtop Controllers



## iSeries

CSi32 Series  
Starts at  
**\$345**



CSi32, \$345, shown actual size.


- ✓ Rugged Metal Benchtop Enclosure
- ✓ 4-Digit Display, 1 or 0.1° Resolution
- ✓ Built Around OMEGA's Award-Winning Patented iSeries Controllers
- ✓ 5-Year Warranty
- ✓ Simple to Configure and Use
- ✓ Full Autotune PID Heat-Cool Control
- ✓ Single Ramp and Soak Capability
- ✓ High Accuracy  $\pm 0.5^{\circ}\text{C}$  ( $\pm 0.9^{\circ}\text{F}$ )
- ✓ Models with Dedicated Thermocouple, RTD, Process Voltage or Current Input
- ✓ Two 5 Amp 120 Vac SSR Outputs Standard
- ✓ Second Output May be Used for Control or as an Alarm
- ✓ Optional Serial Communications
- ✓ Serial to USB Accessory Cable Included

The CSi32 Series is the newest in Omega's line of benchtop controllers. They feature a  $\frac{1}{2}$  DIN size (96 x 48 mm) digital panel controller in a rugged benchtop metal enclosure. The controller used is Omega's award winning and patented iSeries with color-changing display. The iSeries meters feature the only LED displays that can be programmed to change color between **GREEN**, **AMBER**, and **RED** at any setpoint or alarm point. Other options include, serial communications. These controllers can be purchased factory configured for one of 10 common types of thermocouples, multiple RTD types, or process (DC) voltage and current. They are ideal for laboratory use and applications

requiring portable temperature and process control. Pre-wired input and output receptacles in the rear of the case enable quick and easy connections to power, input, power output and digital communications.

The iSeries are full PID controllers with Autotune and can also be programmed for On/Off control via the front panel or through the use of a PC and the free configuration software. The iSeries configuration software is designed to interface with any of the iSeries controllers and the CSi32 Series benchtop controllers with optional communication hardware.

CSi32 Benchtop Controller shown with LHM Series Heating Mantle, \$139, (Flask not included), and KMTXL-125G-12 Thermocouple Probe, \$27.95. Visit [omega.com/kmtxl\\_nmtxl](http://omega.com/kmtxl_nmtxl) for more information. Shown smaller than actual size.



P-X



# iSeries

## Specifications

**Accuracy:** See table on next page

**Resolution:** 1%/0.1°; 10 μV process

**Temperature Stability:**

RTD: 0.04°C/°C

**Thermocouple:** 25°C (77°F); cold-junction compensation of 0.05°C/°C

**Process:** 50 ppm/°C

**NMRR:** 60 dB

**CMRR:** 120 dB

**A/D Conversion:** Dual-slope

**Reading Rate:** 3 samples per second

**Digital Filter:** Programmable


**Display:** 4-digit, 9-segment LED; 10.2 mm (0.40"); **RED, GREEN, and AMBER**, programmable colors for process variable, setpoint and temperature units

**Input Types:** Thermocouple, RTD, analog voltage, analog current


**Thermocouple Lead Resistance:** 100 Ω max

**Thermocouple Type (ITS 90):** J, K, T, E, R, S, B, C, N, L

**RTD Input (ITS 68):** 100/500/1000 Ω Pt sensor; 2-, 3- or 4-wire; 0.00385 or 0.00392 curve



Model CSI32 Front View



Model CSI32 Rear View

**PATENTED**  
Covered by U.S. and International patents and pending applications

## iSeries

### change color

At Any Setpoint

**Totally Programmable Color Displays**

The OMEGA® i/8, i/16, and i/32 are the first complete series of 1/8, 1/6, and 1/2 DIN process control instruments with totally programmable color displays. The display can be programmed to change color at any setpoint or alarm point.

**Voltage Input:** 0 to 100 mV, 0 to 1 Vdc, 0 to 10 Vdc

**Input Impedance:** 10 MΩ for 100 mV, 1 MΩ for 1 or 10 Vdc

**Current Input:** 0 to 20 mA (5 Ω load)

**Configuration:** Single-ended

**Polarity:** Unipolar

**Step Response:** 0.7 s for 99.9%

**Decimal Selection:** None or 0.1 for temperature; None, 0.1, 0.01 or 0.001 for process

**Control Output:** Dual 5 A SSR (internal)

**Setpoint Adjustment:** -1999 to 9999 counts

**Span Adjustment:** 0.001 to 9999 counts

**Offset Adjustment:** -1999 to 9999

**Control Modes:** PID autotune, on/off, direct/reverse,

**Alarm Modes:** Absolute or deviation; high, low, hi/low and band



9-segment LED

The iSeries displays feature unique 9-segment LED characters, which greatly improve alphanumeric representations. The 7-segment LED characters found on most instruments are adequate for presenting numbers, but not letters.

Words are easier to read with the unique 9-segment LED characters

on the iSeries, which makes operating and programming easier.



7-segment display



9-segment display

## Input Connection:

**Thermocouple:** Accepts both miniature and standard male thermocouple connectors

**Note:** A miniature and standard size male mating connector is included with each benchtop controller

**RTD, mA or mV:** Five position terminal strip

## Operating Ambient Range:

0 to 50°C (32 to 130°F)

**Benchtop Case Material:** Aluminum

**Power Connection:** Standard 3-prong power cord (provided)

**Output Connections:** Two standard 120 Vac outlets

**Weight:** 0.9 kg (2 lbs)

## Optional Communications

**RS232/RS485:** Selectable from menu; both ASCII and MODBUS® protocol selectable from menu; programmable 300 to 19.2K baud; complete programmable setup capability; program to transmit current display, alarm status, min/max, actual measured input value and status

**RS485:** Addressable from 0 to 199

**Connection:** RJ12 connector on rear panel

**Power:** 115 Vac, ± 10% 50 to 60 Hz



Input Type	Range	Accuracy	
V	Process Voltage	0 to 100 mV, 0 to 1 V, 0 to 10 Vdc	0.03% rdg
MA	Process Current	0 to 20 mA	0.03% rdg
J	Iron-Constantan	-210 to 760°C/-346 to 1400°F	0.4°C/0.7°F
K	CHROMEKA®-ALOMEGA®	-270 to -160°C/-160 to 1372°C -454 to -256°F/-256 to 2502°F	1.0°C/0.4°C 1.8°F/0.7°F
T	Copper-Constantan	-270 to -190°C/-190 to 400°C -454 to -310°F/-310 to 752°F	1.0°C/0.4°C 1.8°F/0.7°F
E	CHROMEKA®-Constantan	-270 to -220°C/-220 to 1000°C -454 to -364°F/-364 to 1832°F	1.0°C/0.4°C 1.8°F/0.7°F
R	Pt/13%Rh-Pt	-50 to 40°C/40 to 1768°C -58 to 104°F/104 to 3214°F	1.0°C/0.5°C 1.8°F/0.9°F
S	Pt/10%Rh-Pt	-50 to 100°C/100 to 1768°C -58 to 212°F/212 to 3214°F	1.0°C/0.5°C 1.8°F/0.9°F
B	30%Rh-Pt/6%Rh-Pt	100 to 640°C/640 to 1820°C 212 to 1184°F/1184 to 3308°F	1.0°C/0.5°C 1.8°F/0.9°F
C	5%Re-W/26%Re-W	0 to 2320°C/32 to 4208°F	0.4°C/0.7°F
N	Nicrosil-Nisil	-250 to -100°C/-100 to 1300°C -418 to -148°F/-148 to 2372°F	1.0°C/0.4°C 1.8°F/0.7°F
L	J DIN	-200 to 900°C/-328 to 1652°F	0.4°C/0.7°F
RTD	Pt, 0.00385, 100 Ω, 500 Ω, 1000 Ω	-200 to 900°C/-328 to 1652°F	0.4°C/0.7°F
RTD	Pt, 0.00392, 100 Ω, 500 Ω, 1000 Ω	-200 to 850°C/-328 to 1562°F	0.4°C/0.7°F

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
CSi32(*)	\$345	Benchtop controller

\* Insert Input Code: J, K, T, E, R, S, N, RTD, V, MA from Input and Range Table above.

Comes complete with operator's manual, configuration software, 120 Vac power cord and input connector.

## Options

Suffix	Price	Description
-C24	\$95	Isolated RS232 and RS485/422

## Accessories

Suffix	Price	Description
OM-CONV-USB	\$15	USB to RS232 converter

**Ordering Example:** CSi32K-C24, benchtop controller, Type K input and RS232/485 communications option, \$345 + 95 = \$440.

Models with communications option(s) include a standard RS232 cable for connection to a PC and RS232 to USB converter cable.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters