



Thermocouple/Process DIN Digital Indicator



Shown Actual Size

DP1610 Series
\$205
Basic Unit

- ✓ Large Four-Digit Red or Green LED Display
- ✓ Universal Sensor Input: Thermocouple, 3-Wire RTD, DC Voltage or Current
- ✓ One Latching or Non-Latching Relay
- ✓ Max Hold, Min Hold and Time Elapse
- ✓ Universal Power Supply
- ✓ IP65/NEMA-4 Front Panel
- ✓ Engineering Unit Labels Supplied for Faceplate

Optional Features

- ✓ 2nd and 3rd Alarm Relays
- ✓ Remote Reset for Alarms
- ✓ Analog Output
- ✓ Transmitter Power Supply
- ✓ RS-485 Communications
- ✓ Low Voltage Power
- ✓ Fully Configurable with Laptop or PC

The DP1610 digital indicator is an easy-to-operate microprocessor-based instrument, incorporating the latest in surface mount and CMOS technology.

The instrument is a high visibility, full range digital indicator with the flexibility to accommodate thermocouple, RTD and dc inputs. These inputs can be scaled and ranged from the front panel without calibration. Excellent accuracy combined with small size and useful output options make the DP1610 a highly attractive, low cost solution to industrial measurement and indication.

Using the maximum and minimum hold feature, the DP1610 allows maximum and minimum measured variables to be stored and subsequently viewed, even after power down.

The units are supplied with a face plate that has a clear window to display the engineering units being measured. Engineering unit labels are supplied for: %, °F, °C, mV, V, mA, A, kW, W, lb, rpm, atmos, ppm, ft., %RH, inHg, psi, GAL, GPS, GPM, GPH, GPD, and MGD.

Specifications Input

Thermocouple: R, S, J, T, K, L, B and N
RTD: 100 Ω (.00385 ohm/ohm/°C)
Volts: 0 to 5 Vdc, 1 to 5 Vdc, 0 to 10 Vdc and 2 to 10 Vdc
Millivolts: 0 to 50 mV dc and 10 to 50 mV dc

Milliamps:

0 to 20 mA dc and 4 to 20 mA dc

Sensor Fault Detection:

Displays "LL" or "HH" for thermocouple or RTD inputs and sensor break

SnSr. Alarms operate as if the process variable has gone over-range (TC & RTD) and under-range (V, mV, mA)

Remote Reset:

Voltage free or TTL compatible

Alarm Outputs

Output 1 Relay Only:

SPDT, 2 A resistive @ 120/240 Vac

Output 2 Relay:

SPDT 2 A, resistive @ 120/240 Vac

Analog Outputs

Current Output

(retransmission only):

0 to 20 mA dc into 500 ohm max
4 to 20 mA dc into 500 ohm max.

Volts DC Output:

(retransmission only):

0 to 10 Vdc 500 ohm minimum
0 to 5 Vdc 500 ohm minimum

Output 3 Relay:

SPDT, 2 A resistive @ 120/240 Vac

Transmitter Power Supply:

20 to 28 Vdc (24 Vdc nominal)
910 ohm (22 mA @ 20 Vdc)

Display

Digital Display:

Four 7-segment LED's, 9.9 mm (.39") high

Alarm Adjustment

Process Alarm: ± Input Span

Performance

Measurement Accuracy (T/C & RTD):

±0.25% of span,
±1 LSD @ 20°C (68°F)

Note: Reduced performance with Type "B" thermocouple from 100 to 600°C (212 to 1112°F)

Measurement Accuracy (dc linear):
±0.05% of span, ±1 digit
Ambient Temperature Error:
0.01% of span/°C
change in ambient
Linearization Accuracy (TC and RTD):
Better than: ±0.2°C any point, any 0.1°C range (±0.05°C typical).
Better than: ±0.5°C any point, any 1°C range
Cold Junction Compensation:
Better than ±0.7°C
Noise Rejection
Common Mode: >120 dB at 50/60 Hz, giving negligible effect at up to 264 V, 50/60 Hz
Series Mode: >500% of span (at 50/60 Hz) causes negligible effect
Line Voltage: 90-264 Vac, 50/60 Hz (standard) 20-50 Vac 50/60 Hz or 22-65 Vdc (optional)
Operating Temperature: 0 to 55°C (32 to 131°F)
Storage Temperature: -20 to 80°C (-4 to 176°F)
Humidity: 20 to 95% non-condensing
Source Resistance: 1000 Ω max. (thermocouple)
Lead Resistance: 50 Ω per lead max balanced (Pt100)
EMI Susceptibility: Meets EN50082 Part 2 and EN50081 Part 2

Dimensions
Front panel: 48 x 96 x 100 mm deep (1.89 x 3.78 x 3.94")
Weight: .48 kg (1.06 lb) max
Front Panel Sealing: IP65

1/2 DIN DP1610
 Shown Actual Size
 1/2 DIN DP1632



Input Types and Ranges

Input Type	Range	
J Iron-Constantan	0 to 450°C 0 to 761°C 0.0 to 205.4°C	32 to 1471°F 32 to 571°F 32.0 to 401.7°F
K CHROMEGA®-ALOMEGA®	-200 to 760°C -200 to 1399°C	-328 to 1399°F -328 to 2503°F
T Copper Constantan	-200 to 262°C 0.0 to 260.6°C	-328 to 503°F 32.0 to 501.0°F
L Iron-Constantan (J DIN)	0 to 450°C 0 to 762°C 0.0 to 205.7°C	32 to 841°F 32 to 1403°F 32.0 to 402.2°F
N OMEGALLOY®	0 to 1399°C	32 to 2550°F
R Pt/13% Rh-Pt	0 to 1650°C	32 to 3002°F
S Pt/10% Rh-Pt	0 to 1649°C	32 to 3000°F
B Pt/30%Rh-Pt6%Rh	100 to 1824°C	211 to 3315°F
RTD Pt, 385 100 Ω	-101.0 to 300.5°C	-149.8 to 572.9°F
Process Voltage	0 to 50 mV dc, 10 to 50 mV dc, 0 to 5 Vdc, 1 to 5 Vdc, 0 to 10 Vdc, 1 to 10 Vdc, 2 to 10 Vdc	
Process Current	0 to 20 mA, 4 to 20 mA	

IN STOCK FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
DP1610-R1	\$205	1/2 DIN digital indicator with red display
DP1610-GN-R1	205	1/2 DIN digital indicator with green display

Note: Basic unit comes with 1 relay output built-in. Up to 2 more outputs and 1 add' option can be added.

OMEGACARESM extended warranty program is available for models shown on this page.

Ask your sales representative for full details when placing an order.

Ordering Example: DP1610-R1-R2-C4-24LV, 1/2 DIN meter with dual relay outputs,

RS-485 communications and 24V power supply, \$205 + 26 + 62 + 15 = \$308

OCW-1 OMEGACARESM extends standard 3-year warranty to a total of 4 years (\$30),

\$308+ 30 = \$338

Output Options:

Output 2 Suffix	Price	Description
-R2	\$26	Alarm Relay
-F2	47	Analog Retransmission
Output 3 Suffix	Price	Description
-R3	\$26	Alarm Relay
-TPS3	60	20-28 Vdc Trans. Power Supply

Note: only 1 option can be selected from each output ordering box above.

Optional Power Supply

Ordering Suffix	Add'l Price	Description
-24LV	\$15	20 to 50 Vac or 22 to 65 Vdc

Optional Plug-in Boards

Model No.	Price	Description
BD1600-R	\$26	2 A relay
BD1600-F	47	Analog
BD1600-TPS	60	Trans. power supply
BD1600-C4	62	RS-485 comm.

Option "R" above is for output slots 2 & 3 only.

Option "F" above is for output slot 2 only.

Option "TPS" above is for output slot 3 only.

Additional Options:

Ordering Suffix	Add'l Price	Description
-C4	\$62	RS-485 communications
-RR	26	Remote reset

Companion Products:

PTC1632 series 1/32 DIN
 Timer/Controllers also available.
 See page M-129



Shown actual size



CN1632 and DP1632 controllers and meters available. See pages P-19 and M-43
 Shown actual size





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters