




# Dual Channel Autotune Temperature Controllers



CYC325-T1, \$3560, shown smaller than actual size.

CYC325 Series Starts at

**\$3440**



- ✓ Operates Down to 1.2 K with Appropriate Sensors
- ✓ 2 Sensor Inputs
- ✓ Supports Diode, RTD, and Thermocouple Sensors
- ✓ Sensor Excitation (Current Reversal Eliminates Thermal EMF Errors for Resistance Sensors)
- ✓ 2 Autotuning Control Loops: 25 and 2 W Max
- ✓ Control Loop 2: Variable Vdc source from 0 to 10 V Max
- ✓ IEEE-488 and RS232C Interfaces

The CY325 Series dual-channel temperature controller is capable of supporting nearly any diode, RTD, or thermocouple temperature sensor. Two independent PID control loops with heater outputs of 25 and 2 W are configured to drive either a 50 or 25  $\Omega$  load for optimal control flexibility. Designed with ease of use, functionality, and value in mind, the CYC325 Series is ideal for general-purpose laboratory and industrial temperature measurement and control applications.

## Specifications Thermometry

**Number of Inputs:** 2

**Input Configuration:** Each input is factory configured for either diode/RTD or thermocouple

**Isolation:** Sensor inputs optically isolated from other circuits but not each other

**A/D Resolution:** 24-bit

**Input Accuracy:** Sensor dependent, refer to input specifications table

**Measurement Resolution:** Sensor dependent, refer to input specifications table

**Max Update Rate:** 10 rdg/s on each input (except 5 rdg/s on input A when configured as thermocouple)

**Filter:** Averages 2 to 64 input readings

### Sensor Input Configuration Diode/RTD:

**Measurement Type:** 4-lead differential

**Excitation:** Constant current with current reversal for RTDs

**Supported Sensors:** Diodes, silicon, GaAlAs; RTDs, 100  $\Omega$  Platinum, 1000  $\Omega$  Platinum, germanium, carbon-glass, Cernox™, and Rox™

**Standard Curves:** CY7 and CY670, PT-100, PT-1000, RX-102A, RX-202A

**Input Connector:** 6-pin DIN

### Thermocouple:

**Measurement:** 2-lead, room temperature, compensated

**Excitation:** N/A

**Supported Sensors:** Most thermocouple types

**Standard Curves:** Type E, Type K, Type T, AuFe 0.07% vs Cr, AuFe 0.03% vs Cr

**Input Connector:** Ceramic isothermal block



## Control

**Control Loops:** 2

**Control Type:** Closed loop digital PID with manual heater output or open loop

**Tuning:** Autotune (1 loop at a time), PID, PID zones

**Control Stability:** Sensor dependent, see input specification table

### PID Control Settings:

**Proportional (Gain):** 0 to 1000 with 0.1 setting resolution

**Integral (Reset):** 1 to 1000 (1000/s) with 0.1 setting resolution

**Derivative (Rate):** 1 to 200% with 1% resolution

**Manual Output:** 0 to 100% with 0.01% setting resolution

**Zone Control:** 10 temperature zones with P, I, D, manual heater out, and heater range

**Setpoint Ramping:** 0.1 K/min to 100 K/min

**Safety Limits:** Curve temperature, power up heater off, short circuit protection

### Front Panel:

**Display:** 2-line, 20-character, liquid crystal display with 5.5 mm (0.216") character height

**Number of Reading Displays:** 1 to 4

**Display Units:** K, °C, V, mV,

**Reading Source:** Temperature, sensor units

**Display Update Rate:** 2 rdg/s

**Temp Display Resolution:** 0.001° from

0 to 99.999°, 0.01° from 100 to 999.99°, 0.1° above 1000°

**Sensor Units Display Resolution:** Sensor dependent; to 5 digits

**Other Displays:** Setpoint, heater range, and heater output; user selected

**Setpoint Setting Resolution:** Same as display resolution (actual resolution is sensor dependent)

### Heater Output Display:

Numeric display in percent of full scale for power or current

**Heater Output Resolution:** 1%

**Display Annunciators:** Control input, remote, autotune

**Keypad:** 20-key membrane, numeric and specific functions

**Front Panel Features:** Front panel curve entry, keypad lock-out

### Interface

**IEEE-488 Interface Features:** SH1, AH1, T5, L4, SR1, RL1, PP0, DC1, DT0, C0, E1

**Reading Rate:** To 10 rdg/s on each input

**Software Support:** LabVIEW™ driver; consult factory for availability

### Serial Interface:

**Electrical Format:** RS232C

**Baud Rates:** 9600, 19200, 38400, 57600

**Connector:** 9-pin D-style, DTE configuration

**Reading Rate:** To 10 rdg/s, each input

### General

**Ambient Temperature:** 15 to 35°C (59 to 95°F) at rated accuracy, 5 to 40°C (41 to 104°F) at reduced accuracy

**Power Requirement:** Standard 120 Vac, optional 240 Vac, 6%, -10%, 50 or 60 Hz, 85 VA

**Dimensions:** 89 H x 216 W x 368 mm D (3.5 x 8.5 x 14.5"), half rack

**Weight:** 4.00 kg (8.82 lb)

**Approval:** CE mark

OMEGACARE<sup>SM</sup> extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE<sup>SM</sup> covers parts, labor and equivalent loaners.



## Input Specifications

	Sensor Temp Coefficient	Input Range	Excitation Current	Display Resolution	Measurement Resolution	Electronic Accuracy (at 25°C)	Electronic Control Stability <sup>1</sup>
Diode	Negative	0 to 2.5 V	10 μA ±0.05% <sup>2,3</sup>	100 μV	0.4 μV	±80 μV ±0.005% of rdg	±20 μV
Diode	Negative	0 to 7.5 V	10 μA ±0.05% <sup>2,3</sup>	100 μV	10 μV	±80 μV ±0.001% of rdg	±40 μV
PTC RTD	Positive	0 to 500ø	1 mA <sup>4</sup>	10 mø	2 mø	±0.004ø ±0.01% of rdg	±4 mø
PTC RTD	Positive	0 to 5000ø	1 mA <sup>4</sup>	100 mø	20 mø	±0.004ø ±0.02% of rdg	±40 mø
NTC RTD	Negative	0 to 7500ø	10 μA ±0.05%	100 mø	40 mø	±0.1ø ±0.04% of rdg	±80 mø
Thermocouple	Positive	±25 mV	N/A	1 μV	0.4 μV	±1 μV ±0.05% of rdg <sup>5</sup>	±0.8 μV
Thermocouple	Positive	±50 mV	NA	1 μV	20 μV	±1 μV ±0.05% of rdg <sup>5</sup>	±0.8 μV

<sup>1</sup> Control stability of the electronics only, in ideal thermal system

<sup>2</sup> Current source error has negligible effect on measurement accuracy

<sup>3</sup> Diode input excitation can be set to 1 mA


<sup>4</sup> Current source error is removed during calibration

<sup>5</sup> Accuracy specification does not include errors from room temperature compensation

ø = diameter



CYC325-T1 rear view, \$3560, shown smaller than actual size.



- 1 Loop 1 heater output
- 2 Serial (RS232C) I/O (DTE)
- 3 Line input assembly
- 4 Loop 2 heater output
- 5 Sensor input connectors
- 6 IEEE-488 interface



**AVAILABLE FOR FAST DELIVERY!**

**To Order (Specify Model Number)**

Model No.	Price	Description
CYC325	\$3440	2 diode/RTD inputs
CYC325-T1	3560	1 diode/RTD, 1 thermocouple input
CYC325-T2	3675	2 thermocouple inputs

**Accessories**

Model No.	Price	Description
CYC-6201	\$168	1 m (3.3' long) IEEE-488 (GPIB) computer interface cable assembly
CYC-CAL-325-CERT	325	Instrument recalibration with certificate, no points
CYC-CAL-325-DATA	488	Instrument recalibration with certificate and data
CYC-RM-1/2	168	Rack mount kit for mounting one ½ rack temperature controller in 482.60 mm (19") rack, 90 mm (3.5") high
CYC-RM-2	168	Rack mount kit for mounting two ½ rack temperature controllers in 482.60 mm (19") rack, 135 mm (5.25") high
CYC-106-009	10	Heater output connector, dual banana jack
CYC-106-233	13	6-pin male input connector
CYC-106-735	17	Terminal block, 2-pin
MA-2001	65	Reference Book: Semiconductor-Laser Physics

Comes complete with heater output connector (dual banana jack), sensor input mating connector (6-pin DIN plugs), terminal block (2-pin), power cord and operator's manual.

Add suffix "-240" for 240 Vac power supply, no additional cost.

Ordering Example: CYC325, 2 inputs silicon diode/RTD controller, \$3440.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters