

# Temperature/Humidity Handheld Meter

Available in USB or RS232 Interfaces

HH311

\$219



**OMEGAETTE™**

Choice of USB or RS232 Interface.

- ✓ Triple Display
- ✓ Temperature/Humidity Probe
- ✓ Second Temperature Input
- ✓ Choice of RS232 or USB Interfaces
- ✓ Timer and REL Functions
- ✓ MIN/MAX/HOLD Functions
- ✓ Resolution 0.1
- ✓ Auto Power-Off
- ✓ Mini-Tripod Included

The HH311 is a low cost, high performance handheld meter. It offers a triple display to show the temperature and humidity from a handheld probe and can display data from a separate K type thermocouple connected via a standard SMP type miniature connector to the T2 input. The temperature/humidity probe uses a semiconductor and polymer capacitive sensor. Optional software packages are offered to allow data to be read by a PC through either RS232 or USB cables.

## Specifications

**Range:** 0 to 100% RH, -20 to 60°C (-4 to 140°F)

**T2 Range:** -200 to 1370°C (-328 to 2498°F)

**Resolution:** 0.1 (except T2 for -200 > T2 > 200)

**Accuracy:** ±2.5% RH at 25°C, ±0.7°C (±1.4°F)

**T2 Accuracy:** ±[0.5% rdg ±1°C (2°F)]

**Humidity Response Time:** 75 sec in slowly moving air

**T1 Response Time:** 40 sec in slowly moving air

**Meter Dimensions:**

186 H x 64 W x 30 mm D (7.3 x 2.5 x 1.2")

**Probe Dimensions:** 190 x 15 mm (7.5 x 0.6"), cable stretches to 1.5 m (5')

**Operating Environment:**

0 to 50°C (32 to 122°F), 0 to 90% non-condensing

**Storage Environment:**

-10 to 60°C (14 to 140°F), 0 to 80% non-condensing

**Power Requirements:**

One 9V battery (included), AC adapter 9 Vdc 10 mA min

**Plug Diameter:** 3.5 x 1.35 mm

**RS232:** 9600 bps, N, 8, 1 serial interface

**Battery Life:** Approx 100 hours with alkaline battery

**Weight:** Approx 320 g (11.3 oz)



HH311, \$219.


**AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

Model No.	Price	Description
HH311	\$219	Temperature/humidity handheld meter
HH310-SW	50	Software and RS232 interface cable
HH310-SW-USB	50	Software and USB interface cable
KTSS-HH	29	Type K immersion probe (not shown)
HH300-ADAPTER	18	Power adaptor (115V)
HH300-CABLE	18	RS232 interface cable (spare)
HH300-CABLE-USB	18	USB interface cable (spare)
MINI-TRIPOD	12	Spare mini-tripod expands 142 to 279 mm (5.6 to 11")

Comes complete with hard carrying case, mini-tripod, 9V battery, beaded thermocouple (for T2 input), calibration certificate, and operator's manual.

**Ordering Example:** HH311, temperature/humidity handheld meter, \$219.



### Free Thermocouple Included!

This model includes a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy. **Order a Spare!** Model No. SC-GG-K-30-36, \$15.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters