

Economical Handheld Thermometers

OMEGATEMP®

- ✓ Lightweight Design
- ✓ Pocket Hook and Magnet Hanger
- ✓ MAX/DATA HOLD Function



HH67
\$55



HH67, \$55, shown smaller than actual size.

HH67 Semiconductor Thermometer with Probe Attached

Specifications

Temperature:

Range: -50 to 150°C (-58 to 302°F)

Resolution: 0.1°C (1°F)

Accuracy:

- ±3.0°C from -50 to 0°C
- ±1.5°C from 0 to 100°C
- ±3.0°C from 100 to 150°C;
- ±6.0°F from -58 to 32°F
- ±3.0°F from 32 to 212°F
- ±6.0°F from 212 to 302°F

Sensor: Semiconductor, silicon diode type

Dimensions: 160 H x 48 W x 24 mm D (6.3 x 1.9 x .94")

Weight: Approx 78 g (2.7 oz.) including battery

Probe: Brass with conformal coating

Probe Diameter: 3.2 mm (1/8") with pointed tip

Probe Length: 130 mm (5.1")

Display: 3½ digit liquid crystal display (LCD)

Low Battery Indication: The "E" is displayed when the battery voltage drops below the operating level

Measurement Rate: 2.5 times/second

Operating Environment: 0 to 50°C (32 to 122°F) <70% R.H.

Storage Environment: -20°C to 60°C (-4 to 140°F), 0 to 80% R.H. with battery removed from meter

Accuracy: Stated accuracy at 23°C ± 5°C (73°F ± 9°F), <75% R.H.

Battery: Three 1.5 V "AAA" size (included)

Battery Life: 300 hours, typical use

Applications

- ✓ Greenhouses
- ✓ Office Environment
- ✓ Department Stores
- ✓ Labs
- ✓ Weather Monitoring
- ✓ Art Galleries
- ✓ Museums
- ✓ Workshops
- ✓ Environmental Studies

- ✓ Auto Power-Off Function Can Be Disabled
- ✓ Battery Life 300 Hours Typical Use
- ✓ °C/°F Switchable



HH68K
\$65



No points

HH68K, \$65, shown smaller than actual size.

HH68K Type K Thermometer with Probe Attached

Specifications

Temperature:

Range: -100 to 850°C (-148 to 1562°F)

Type K (CHROMEGA®-ALOMEGA®)

Resolution: 1°C or 1°F, 0.1°C or 0.1°F

Accuracy (does not include probe): 18 to 28°C (64 to 82°F) ambient ±(0.3% rdg + 1°C) on °C ranges ±(0.3% rdg + 2°F) on °F ranges

Resolution

Resolution	Range
0.1°C	-59.9 to 199.9°C
1°C	-100 to -60°C; 200 to 850°C
0.1°F	-59.9 to 199.9°F
1°F	-148 to -60°F; 200 to 1562°F

Dimensions: 160 H x 48 W x 24 mm D (6.3 x 1.9 x .94")

Weight: Approx 80 g (2.8 oz.) including battery

Probe: Stainless steel

Probe Diameter: 3.2 mm (1/8") with pointed tip

Probe Length: 132 (5.2")

Display: 3½ digit liquid crystal display (LCD)

Low Battery Indication: The "E" is displayed when the battery voltage drops below the operating level

Measurement Rate: 2.5 times/second

Operating Environment: 0 to 50°C (32 to 122°F) <70% R.H.

Storage Environment: -20 to 60°C (-4 to 140°F), 0 to 80% R.H. with battery removed from meter

Accuracy: Stated accuracy at 23°C ± 5°C (73°F ± 9°F), <75% R.H.

Battery: Three 1.5 V "AAA" size (included)

Battery Life: 300 hours, typical use

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HH67	\$55	Semiconductor thermometer with probe attached
HH68K	65	Type K thermometer with probe attached
SC67	10	Soft carrying case

Comes with complete operator's manual, magnet hanger, and batteries.

Ordering Example: HH68K, Type K thermometer with probe attached, \$65.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters