

KX**Extension Grade
CHROME[®]
ALOMEGA[®]
Duplex ANSI Type KX**ANSI Color Code: Positive Wire,
Yellow; Negative Wire,
Red; Overall, Yellow**MOST POPULAR MODELS HIGHLIGHTED!**

Insulation	AWG No.	Model Number	Price/1000'	SLE/1000' ^{††}	Type Wire	Insulation		Max. Temp [*]		Nominal Size mm (in)	Wt. [†] kg/300 m (lb/1000')
						Conductor	Overall	°C	°F		
Glass	16	EXGG-K-16	\$1095	\$1265	Solid	Glass Braid	Glass Braid	200	392	2.2 x 3.3 (0.085 x 0.130)	9 (17)
Neoflon PFA	16	EXTT-K-16	1575	1815	Solid	PFA	PFA	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXTT-K-20	625	715	Solid	PFA	PFA	200	392	1.7 x 3.0 (0.068 x 0.116)	4 (9)
	24	EXTT-K-24	430	520	Solid	PFA	PFA	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)
Polyvinyl	14	EXPP-K-14	1360	1570	Solid	Polyvinyl	Polyvinyl	105	221	3.4 x 7.3 (0.134 x 0.288)	13 (28)
	16	EXPP-K-16	785	905	Solid	Polyvinyl	Polyvinyl	105	221	3.1 x 5.3 (0.123 x 0.207)	10 (22)
	16	EXPP-K-16S	1190	1430	7 x 24	Polyvinyl	Polyvinyl	105	221	5.5 x 5.7 (0.139 x 0.226)	10 (22)
	18	EXPP-K-18S	1080	1295	7 x 26	Polyvinyl	Polyvinyl	105	221	3.5 x 5.2 (0.138 x 0.205)	8 (16)
	20	EXPP-K-20	440	505	Solid	Polyvinyl	Polyvinyl	105	221	2.4 x 3.8 (0.095 x 0.151)	6 (12)
	20	EXPP-K-20S	565	675	7 x 28	Polyvinyl	Polyvinyl	105	221	3.1 x 4.4 (0.123 x 0.175)	6 (12)
	24	EXPP-K-24	355	425	Solid	Polyvinyl	Polyvinyl	105	221	1.9 x 3.0 (0.075 x 0.120)	2 (4)
24	EXPP-K-24S	445	535	7 x 32	Polyvinyl	Polyvinyl	105	221	2.1 x 3.4 (0.082 x 0.134)	4 (9)	
Neoflon FEP	16	EXFF-K-16	1415	1630	Solid	FEP	FEP	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXFF-K-20	605	695	Solid	FEP	FEP	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXFF-K-24	390	450	Solid	FEP	FEP	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)

* Maximum temperature is for extension grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb. (does not include packing material).

†† To order special limits of error wire, add "-SLE" to model number before spool length

Ordering Example: EXTT-K-20-25, 25' spool of extension grade thermocouple wire, Type KX, 20 gage, stranded, Neoflon PFA insulation, \$625 x 0.0625 = \$39.

EX**Extension Grade
CHROME[®]/Constantan
Duplex ANSI Type EX**

ANSI Color Code: Positive Wire, Purple; Negative Wire, Red; Overall, Purple

Insulation	AWG No.	Model Number	Price/1000'	SLE/1000' ^{††}	Type Wire	Insulation		Max. Temp [*]		Nominal Size mm (in)	Wt. [†] kg/300 m (lb/1000')
						Conductor	Overall	°C	°F		
Neoflon PFA	16	EXTT-E-16	\$1575	\$1815	Solid	PFA	PFA	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXTT-E-20	715	825	Solid	PFA	PFA	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXTT-E-24	520	600	Solid	PFA	PFA	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)
Polyvinyl	16	EXPP-E-16	1105	1270	Solid	Polyvinyl	Polyvinyl	105	221	3.1 x 5.3 (0.123 x 0.207)	10 (22)
	18	EXPP-E-18S	845	1015	7 x 26	Polyvinyl	Polyvinyl	105	221	3.5 x 5.2 (0.138 x 0.205)	8 (16)
	20	EXPP-E-20	340	390	Solid	Polyvinyl	Polyvinyl	105	221	2.4 x 3.8 (0.095 x 0.151)	6 (14)
	24	EXPP-E-24S	420	505	7 x 32	Polyvinyl	Polyvinyl	105	221	2.1 x 3.4 (0.82 x 0.134)	4 (9)
Neoflon FEP	16	EXFF-E-16	1415	1630	Solid	FEP	FEP	200	392	2.2 x 3.9 (0.086 x 0.152)	8 (16)
	20	EXFF-E-20	700	850	Solid	FEP	FEP	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXFF-E-24	455	520	Solid	FEP	FEP	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)

* Maximum temperature is for extension grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb. (does not include packing material).

†† To order special limits of error wire, add "-SLE" to model number before spool length

Ordering Example: EXPP-E-20-50, 50' spool of extension grade thermocouple wire, Type EX, 20 gage, Polyvinyl over Polyvinyl insulation, \$340 x 0.1 = \$34.

RX/SX**Extension Grade
Copper/Alloy#11
Duplex ANSI
Type RX and SX**Compensating Extension Wires for Platinum (-) /
Platinum-Rhodium (+) Thermocouples.

ANSI Color Code: Positive Wire, Black; Negative Wire, Red; Overall, Green

Insulation	AWG No.	Model Number	Price/1000'	Type Wire	Insulation		Max. Temp [*]		Nominal Size mm (in)	Wt. [†] kg/300 m (lb/1000')
					Conductor	Overall	°C	°F		
Glass	20	EXGG-RS-20	\$480	Solid	Glass Braid	Glass Braid	200	392	1.5 x 2.4 (0.060 x 0.095)	3 (6)
	24	EXGG-RS-24	430	Solid	Glass Braid	Glass Braid	200	392	1.3 x 2.0 (0.050 x 0.080)	1.8 (1.4)
Neoflon PFA	20	EXTT-RS-20	610	Solid	PFA	PFA	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXTT-RS-24	530	Solid	PFA	PFA	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)
Polyvinyl	16	EXPP-RS-16	555	Solid	Polyvinyl	Polyvinyl	105	221	3.0 x 5.0 (0.118 x 0.195)	10 (22)
Neoflon FEP	20	EXFF-RS-20	530	Solid	FEP	FEP	200	392	1.7 x 2.9 (0.068 x 0.116)	4 (9)
	24	EXFF-RS-24	430	Solid	FEP	FEP	200	392	1.4 x 2.3 (0.056 x 0.092)	3 (6)

* Maximum temperature is for extension grade wire or insulation, whichever is lower.

† Weight of spool and wire, rounded to next highest kg/lb. (does not include packing material).

Ordering Example: EXTT-RS-20-500, 500' spool of extension grade thermocouple wire, Type RX, 24 gage, Neoflon PFA insulation, \$610 x 0.5 = \$305.

Note: Published prices are based on market value at time of printing and are subject to change due to Nickel surcharges, Chromium and precious-metal market fluctuations.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters