

Fine Diameter 1/16" and 1.5 mm RTD Probes

Standard and Metric Dimensions



Also Available with PFA Coating. See Page C-92

PR-13 and PR-17 Series, include mating connector.




PR-11 Series Transition junction probe with 1 m (40") PFA insulated leads, strip end termination standard, \$97.


- ✓ 100 Ω DIN Platinum Class "A" Per IEC 60751
- ✓ OMEGA's Platinum RTD Probes Are Available in 1.5 mm and 1/16" Diameters for Faster Response Times

Note: Because of their smaller physical size, these probes are more fragile and should be handled with greater care than our larger diameter versions of the same probes. Avoid subjecting probes to bending, flexing or vibration.

Add a connector! Add suffix "-MTP" for miniature or "OTP" for standard size connector, \$7 add'l.



PR-13 Series quick disconnect probe with standard size connector, \$115.



PR-17 Series quick disconnect probe with miniature size connector, \$115.

PR-16 Series utility handle probe, \$119.



Standard Dimensions

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)						
Model Number	Lead Style†	Ω @ 0°C	**Sheath Length			
			6"	12"	18"	24"
PR-11-2-100-1/16-(*)-E	2	100	\$97	\$97	\$100	\$103
PR-13-2-100-1/16-(*)-E	2	100	115	115	118	121
PR-16-2-100-1/16-(*)-E	2	100	119	119	122	125
PR-17-2-100-1/16-(*)-E	2	100	115	115	118	121

† Available in lead type 2 (3-wire) and lead type 1 (2-wire). Please contact Custom Engineering for 4-wire, type 3.
 * Specify sheath length. Minimum sheath length for any style probe is 4". 1/16" dia RTD probes cannot be bent. For intermediate lengths, use next longer probe price. Over 24", consult Custom Engineering. Actual diameter of sheath is 0.064" ± 0.003". Consult Sales Department for lead wire with stainless steel overbraid.
 To order additional lead length on the PR-11 style probes, consult Sales Department. European curve α = 0.00385.
 ** Intermediate probe lengths are available at the price of next longer standard probe. Longer probes are available through Custom Engineering.
Ordering Example: PR-17-2-100-1/16-6-E, quick disconnect probe 6" long, lead type 2 (3-wire configuration), 1/16" dia., 304 SS sheath, \$115.

Metric Dimensions

To Order (Specify Model Number)						
Model Number	Lead Style†	Ohms @ 0°C	**Sheath Length			
			150 mm	300 mm	450 mm	600 mm
PR-11-2-100-M15-(*)-E	2	100	\$97	\$97	\$100	\$103
PR-13-2-100-M15-(*)-E	2	100	115	115	118	121
PR-16-2-100-M15-(*)-E	2	100	119	119	122	125
PR-17-2-100-M15-(*)-E	2	100	115	115	118	121

† Available in lead type 2 (3-wire) and lead type 1 (2-wire). Please contact Custom Engineering for 4-wire, type 3.
 * Specify sheath length. Minimum sheath length for any style probe is 100 mm. 1.5 mm dia RTD probes cannot be bent. For intermediate lengths, use next longer probe price. Over 600 mm, consult Custom Engineering. Actual diameter of sheath is 1.5 mm ± 0.075 mm. To order additional lead length on the PR-11 style probes, consult Sales Department. European curve α = 0.00385.
 ** Intermediate probe lengths are available at the price of next longer standard probe. Longer probes are available through Custom Engineering.
Ordering Example: PR-17-2-100-M15-150-E, quick disconnect probe 150 mm long, lead type 2 (3-wire configuration), 1.5 mm dia., 304 SS sheath, \$115.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters