

# Economical Handheld Thermometers

**OMEGATEMP®**

- ✓ Lightweight Design
- ✓ Pocket Hook and Magnet Hanger
- ✓ MAX/DATA HOLD Function



HH67  
**\$59**



HH67 shown smaller than actual size.

## HH67 Semiconductor Thermometer with Probe Attached

### Specifications

#### Temperature:

**Range:** -50 to 150°C (-58 to 302°F)

**Resolution:** 0.1°C (1°F)

#### Accuracy:

- ±3.0°C from -50 to 0°C
- ±1.5°C from 0 to 100°C
- ±3.0°C from 100 to 150°C
- ±6.0°F from -58 to 32°F
- ±3.0°F from 32 to 212°F
- ±6.0°F from 212 to 302°F

**Sensor:** Semiconductor, silicon diode type

**Dimensions:** 160 H x 48 W x 24 mm D (6.3 x 1.9 x .94")

**Weight:** Approx 78 g (2.7 oz) including battery

**Probe:** Brass with conformal coating

**Probe Diameter:** 3.2 mm (1/8") with pointed tip

**Probe Length:** 130 mm (5.1")

**Display:** 3½ digit liquid crystal display (LCD)

**Low Battery Indication:** The "⊖" is displayed when the battery voltage drops below the operating level

**Measurement Rate:** 2.5 times/second

**Operating Environment:** 0 to 50°C (32 to 122°F) <70% RH

**Storage Environment:** -20°C to 60°C (-4 to 140°F),

0 to 80% RH with battery removed from meter

**Accuracy:** Stated accuracy at 23°C ±5°C (73°F ±9°F), <75% RH

**Battery:** 1.5V x 3 pcs "AAA" size (included)

**Battery Life:** 300 hours, typical use

### Applications

- ✓ Greenhouses
- ✓ Office Environment
- ✓ Department Stores
- ✓ Labs
- ✓ Weather Monitoring
- ✓ Art Galleries
- ✓ Museums
- ✓ Workshops
- ✓ Environmental Studies

- ✓ Auto Power Off Function Can Be Disabled
- ✓ Battery Life 300 Hours Typical Use
- ✓ °C/°F Switchable

HH68K  
**\$69**



No points

HH68K shown smaller than actual size.

## HH68K Type K Thermometer with Probe Attached

### Specifications

#### Temperature:

**Range:** -100 to 850°C (-148 to 1562°F)

type K (CHROMEALOMEGA®-ALOMEGA®)

**Resolution:** 1°C or 1°F, 0.1°C or 0.1°F

**Accuracy (does not include probe):** 18 to 28°C (64 to 82°F) ambient ±(0.3% rdg + 1°C) on °C ranges ±(0.3% rdg + 2°F) on °F ranges

#### Resolution

Resolution	Range
0.1°C	-59.9 to 199.9°C
1°C	-100 to -60°C; 200 to 850°C
0.1°F	-59.9 to 199.9°F
1°F	-148 to -60°F; 200 to 1562°F

**Dimensions:** 160 H x 48 W x 24 mm D (6.3 x 1.9 x .94")

**Weight:** Approx 80 g (2.8 oz) including battery

**Probe:** Stainless steel

**Probe Diameter:** 3.2 mm (1/8") with pointed tip

**Probe Length:** 132 (5.2")

**Display:** 3½ digit LCD

**Low Battery Indication:** The "⊖" is displayed when the battery voltage drops below the operating level

**Measurement Rate:** 2.5 times/second

**Operating Environment:** 0 to 50°C (32 to 122°F) <70% RH

**Storage Environment:** -20 to 60°C (-4 to 140°F),

0 to 80% RH with battery removed from meter

**Accuracy:** Stated accuracy at 23°C ±5°C (73°F ±9°F), <75% RH

**Battery:** 1.5V x 3 pcs "AAA" size (included)

**Battery Life:** 300 hours, typical use

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
HH67	\$59	Semiconductor thermometer with probe attached
HH68K	69	Type K thermometer with probe attached
SC-50	13	Soft carrying case

Comes complete with operator's manual, magnet hanger, and batteries.

**Ordering Example:** HH68K, Type K thermometer with probe attached, \$69.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters