



# Portable Fiber Optic Data Logger Thermometer

HHTFO-101  
**\$2695**



- ✓ Battery Operated (Included)
- ✓ Data Logging on SD Cards (SD Card Sold Separately)
- ✓ -200 to 300°C Range
- ✓ RS232 Com Link
- ✓ Optional Windows Software
- ✓ Large LCD Display
- ✓ No Gage Factor or Calibration
- ✓ Accuracy of  $\pm 0.5^{\circ}\text{C}$

## Applications

- ✓ High Voltage Environments
- ✓ EMI, RFI and Microwave Environments
- ✓ Microwave and Food Processing
- ✓ Hazardous Environments
- ✓ Civil Engineering and Geotechnical Applications

The HHTFO-101 offers impressive versatility. Battery operated for maximum user freedom, this single-channel instrument allows you to freely move from one area to another to measure temperatures at various critical sensing points.

The HHTFO-101 runs on standard "AA" type alkaline or rechargeable batteries, providing power for at least 5 hours of continuous use. It also comes with a universal power supply.

The HHTFO-101 comes with a built-in flash card data logging feature allowing user to save collected data directly onto a high capacity SD flash card. SD cards of up to 1 GB capacity are supported. The data can be accessed through any PC equipped with a flash card reader. The HHTFO-101 also features the SnapLog feature which



allows recording of 1 temperature point with time stamp every time the SnapLog key is pressed.

The HHTFO-101 features a 160 x 160 pixel LCD display with a LED backlight. It provides celsius or fahrenheit temperature readings that are well contrasted in any condition.

The HHTFO-101 icon-driven user interface is built around a 6-button ruggedized keypad. All functions are accessible through the display menu, including data logging on SD card, instrument setup and configuration, and expert mode. Datalogging sessions can also be viewed directly on the display.

This multi-purpose instrument comes with a built-in RS232 port for remote interfacing. The instrument is a perfect match with the optional FOB100-SOFT software. Software features include min/max alarm, full datalogging functions, and bar-graph, trend-line, or statistics display. Moreover, all system features are accessible through ASCII commands, facilitating the development of custom routines or proprietary drivers by users.

The HHTFO-101 is a valuable monitoring tool for a wide range of applications in energy, industrial and research activities, such as hot spot monitoring inside power transformers during manufacturing and heat runs. It can also be used in various high voltage applications and MW/RF heating applications.

Its accuracy and high degree of sensitivity to temperature changes makes it a natural choice for a wide variety of applications. The field-proven sensors are interchangeable and no calibration or inconvenient gage factors are required when changing sensors. The HHTFO-101 comes with a complete 1-year warranty.

## Specifications

### Number of Channels:

Single-channel instrument

**Resolution:** 0.1°C (0.1°F)

**Accuracy:** ±0.5°C (0.9°F) or 1% FS

**Sampling Rate:** 5 Hz

### Upgradeability—Firmware:

Flash ROM upgradeable through serial communication

**Display:** 53 x 53 mm (3" diagonal) graphic matrix display, 160 x 160 pixels, transfective display, yellow-green LED backlight

**Units:** User selectable, metric or imperial

### Data Logging Memory:

Temperature plus time and date stamp in ASCII format on removable SD flash card

**Data Logging Rate:** Logging sessions with user selectable rate from 1 sec to 1-hr

**SnapLog™ Feature:** Save 1 data point logging and time stamp when SnapLog key is pressed

### Temperature Measurement

**Range:** -80 to 300°C (-112 to 572°F)

## Communication And I/O

**Operating Mode:** Front panel keypad, FOB100-50FT Windows software or RS232 ASCII commands

**Communication (Hardware):** RS232

**Communication protocols:** ASCII (over RS232)

## Mechanical and Environmental

### Operating Temperature:

-20 to 55°C (0 to 150°F)

**Storage Temperature:** -30 to 70°C (0 to 160°F), non-condensing

**Form Factor:** Handheld unit, anodized aluminum extrusion and heavy-duty die-cast top and bottom end caps painted with textured black powder paint (RAL 9005)

### Enclosure Protection:

IP54 standard

## Connectors:

**Optical:** 1 ST connector

**Serial:** DB-9

**Power-In:**

Power jack connector

**SD Card:** Push-to-eject card slot on top panel

**Batteries:** Battery access port on bottom side

## Dimensions:

180 H x 118 W x 37 mm D (7 x 4.6 x 1.4")

**Weight:** 550 g (1.2 lb), without batteries

## Power


**Power Requirements:** 6 Vdc power-in or 4 "AA" alkaline (included) or rechargeable batteries

**Power Consumption:** 1.25 W



HHTFO-101, \$2695, with HHTFO-101-EC protective end caps and shoulder strap, \$95, shown smaller than actual size.

**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
HHTFO-101	\$2695	Fiber optic thermometer
FOBS-2	249	Sensor with 2 m (6.6') cable
FOBS-10	377	Sensor with 10 m (33') cable
FOBS-20	537	Sensor with 20 m (66') cable
FOBS-30	697	Sensor with 30 m (98') cable
Accessories		
FOB100-SOFT	\$395	Windows software and RS232 cable
HHTFO-101-WM	275	Wall mount
HHTFO-101-EC	95	Protective end caps and shoulder strap
1GB-SD	29	SD memory card, 1 GB
OS-XL-FCR	39	USB flash card reader
EE-2470	111	Reference Book: Microwave Engineering, Second Edition 

Comes with universal charger, 4 "AA" NiMH batteries, and operator's manual.

**Ordering Example:** HHTFO-101, 1-channel handheld fiber optic thermometer, FOBS-2, 2 m (6.6') cable temperature sensor, 1GB-SD, 1 GB SD flash card, \$2695 + 249 + 29 = \$2973.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters