

Constant-Temperature Circulating Baths

HCTB-3000/RCTB-3000 Series

Starts at

\$1345

Complete System



A bridge to mount all circulating baths is included with all baths



HCTB-3030, \$1669, shown smaller than actual size with BATH-12, \$422.

- ✓ Temperature Stability to $\pm 0.005^{\circ}\text{C}$
- ✓ Temperature Range: -40 to 200°C (-40 to 392°F) Available
- ✓ 5 Bath Sizes from 8 to 48 Liters, or Use with Existing Baths or Containers
- ✓ High Pump Capacity with External Connections
- ✓ Adjustable Over-Temperature Cutoff
- ✓ 120V Power, 240V Optional
- ✓ Includes Mounting Bridge for Liter Baths

Applications

- ✓ Use as Calibration Standard
- ✓ Laboratory and Biological
- ✓ Stress and Shock Testing

A choice of 4 temperature controllers with either analog or digital temperature selectors offers temperature management over the range of -40 to 250°C (-40 to 392°F) with stability as good as $\pm 0.005^{\circ}\text{C}$. Each model has a rugged, splash-proof case with all submerged parts made of either stainless steel or high-temperature, self-extinguishing plastic. Powerful pressure circulating pumps with external circulation connections are standard on all models. However, the HCTB-3040 has dual suction and pressure pumps. With a choice of 4 different temperature controllers and 5 stainless steel baths with a capacity of 8 to 48 liters, a range of 20 different systems is available to suit most laboratory and industrial applications. Inlet

and outlet pipes at the rear of the controller can be used for external circulation to another apparatus or they can be sealed for circulation within the bath itself. The baths are also suitable for below ambient applications, and can be used at sub-ambient temperatures with a cooling coil (standard on HCTB-3040, optional on other models) or with RCTB-3000 Series dip and flow coolers.

Unheated Baths

Designed to be used with an HCTB-3000 Series thermoregulator, these new baths incorporate attractive carrying handles for added safety. The 4 smaller models have seam-free stainless steel interiors for easy cleaning. The largest bath, BATH-48, is of welded construction. All baths have stoved enamel steel outer cases.

Dip and Flow Coolers

The RCTB-3000 Series dip and flow coolers are designed for use at below-ambient temperatures down to -35°C (-31°F). The flow cooler works in conjunction with a thermoregulator and continually extracts heat from the bath fluid by means of the heat exchanger, which is built into the unit.

The cooling head of the dip cooler fits neatly and unobtrusively into the corner of the bath and can be secured with a specially designed mounting bracket (included). Even if cooling can be achieved by cold tap water, a dip cooler is recommended, since it conserves water and is easier and more convenient to use.





Thermoregulator Specifications

 MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)			
Model No. ^{††}	HCTB-3010	HCTB-3020	HCTB-3030
Price	\$818	\$1190	\$1669
Temperature Range °C (°F)*	-20 to 95 (-4 to 203)	-40 to 120 (-40 to 248)	-40 to 200 (-40 to 392)
Temperature Selection	Analog	Digital	Digital
Temperature Stability Using Water @ 40°C (°C)	±0.01	±0.01	±0.005
Pump Capacity (LPM)	10	10	10
Pump Capacity (mbar)	145	145	145
Method of Control	Proportional	PID	PID
Temperature Sensor	Thermistor	PRT	PRT
Adjustable Over-Temp Cutout	Yes	Yes	Yes
Low Liquid-Level Cutout	No	Yes	Yes
PC Interface	No	No	Yes, RS232
Cooling Coil**	No	No	No
Dimensions: mm (in) Extension Below Base	145 (5.7)	145 (5.7)	145 (5.7)
Size H x W x L, mm (in)	260 x 124 x 237 (10.2 x 4.9 x 9.3)	260 x 124 x 237 (10.2 x 4.9 x 9.3)	260 x 124 x 237 (10.2 x 4.9 x 9.3)

* Refrigeration required for below ambient cooling.

** Available as an option where not supplied as standard as HCTB-COIL.

†† For 240 Vac power, add suffix “-240V” to model number, no additional charge.

Note: For 4-point NIST calibration, points: -20°C, 60°C, 120°C, 180°C, add suffix “-NIST” to model number and \$280 to price.

Dip and Flow Cooler Specifications†

Model No. ^{††}	RCTB-3050	RCTB-3060	RCTB-3070	RCTB-3080
Price	\$2455	\$3184	\$2455	\$3184
Minimum Achievable Temperature °C (°F)	-20 (-4)	-35 (-31)	-20 (-4)	-35 (-31)
Cooling Capacity 0°C (W)	145	240	140	210
Cooling Capacity 20°C (W)	145	240	140	210
Cooling Capacity -10°C (W)	110	230	110	200
Internal Capacity (mL)	—	—	200	200
Dimensions H x W x L mm (in)	300 x 420 x 235 (11.8 x 16.5 x 9.3)	325 x 430 x 370 (12.8 x 16.9 x 14.6)	300 x 420 x 235 (11.8 x 16.5 x 9.3)	325 x 430 x 370 (12.8 x 16.9 x 14.6)
Coil Dimensions L x Dia. mm (in)	85 x 75 (3.3 x 3.0)	85 x 75 (3.3 x 3.0)	—	—
Hose Length to Coil mm (in)	1250 (49.2)	1250 (49.2)	—	—
Hose Connection mm (in)	—	—	16 (%)	16 (%)

† At ambient of 20°C, using a mixture of 40% water, 40% antifreeze, 20% alcohol to achieve -35°C, in a well-insulated 8 liter bath.

†† For 240 Vac power, add suffix “-240V” to model number, no additional charge.



BATH-8,
\$391.

BATH-18,
\$479.

BATH-26,
\$547.

All models shown smaller than actual size.

A bridge to mount all circulating baths is included with all baths. See picture on K-44.



Both models shown smaller than actual size.

RCTB-3050,
\$2455.

RCTB-3070,
\$2455.



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Unheated Bath Specifications

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)					
Model No.	BATH-8	BATH-12	BATH-18	BATH-26	BATH-48
Price	\$391	\$422	\$479	\$547	\$861
Overall Size H x W x L: mm (in)	172 x 325 x 265 (6.8 x 12.8 x 10.4)	172 x 325 x 354 (6.8 x 12.8 x 13.9)	172 x 325 x 530 (6.8 x 12.8 x 20.9)	222 x 325 x 530 (8.7 x 12.8 x 20.9)	298 x 365 x 594 (11.7 x 14.4 x 23.4)
Top of Bath to Liquid Level Max Depth: mm (in)	65 (2.6)	65 (2.6)	65 (2.6)	65 (2.6)	65 (2.6)
Internal Dimensions H x W x L: mm (in)	150 x 300 x 240 (5.9 x 11.8 x 9.4)	150 x 300 x 329 (5.9 x 11.8 x 13)	150 x 300 x 505 (5.9 x 11.8 x 19.9)	200 x 300 x 505 (7.9 x 11.8 x 19.9)	274 x 330 x 559 (10.8 x 13 x 22.8)
Working Length to Thermoregulator: mm (in)	115 (4.5)	205 (8.1)	380 (15.0)	380 (15.0)	430 (16.9)
Working Depth Max/Min: mm (in)	130/100 (5.1/3.9)	130/100 (5.1/3.9)	130/100 (5.1/3.9)	180/150 (7.1/5.9)	255/224 (10.0/8.8)
Working Capacity Max/Min: Liters (Gallons)	8.0/6.0 (2.1/1.6)	11.6/8.4 (3.1/2.2)	18.0/13.2 (4.8/3.5)	26.0/20.5 (6.9/5.4)	48.5/42.5 (12.8/11.2)

Accessories

Model No.	Price	Description
CAL-SOFT	\$136	Software (included with HCTB-3040)
HCTB-COIL	115	Water-cooling coil
LID-8	136	Flat lid for use with 8 liter bath and mounting bridge
LID-12	137	Flat lid for use 12 liter bath and mounting bridge
LID-18	144	Flat lid for use 18 liter bath and mounting bridge
LID-26	144	Flat lid for use 26 liter bath and mounting bridge
LID-48	191	Flat lid for use 48 liter bath and mounting bridge
PE-1411	80	Reference Book: Control System Design Guide: Using Your Computer to Understand and Diagnose Feedback Controllers

Comes complete with mounting bridge and operator's manual.

Ordering Examples: HCTB-3030, digital thermoregulator, BATH-18, 18 liter bath, LID-18, flat lid and CAL-SOFT, software, \$1669 + 479 + 144 + 136 = \$2428.

HCTB-3010, digital thermoregulator, BATH-8, 8 liter bath, \$818 + 391 = \$1209.





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters