



# Four-Channel, Handheld Data Logger Thermometer With USB Interface

HH147U

**\$299**



Standard No Points

Optional RS232

- ✓ 4 Backlit Displays
- ✓ Resolution 0.1°C/0.1°F, 1°C/1°F
- ✓ Functions: °C/°F/K, Max, Min, Avg, Hold, Rel, Limit, Hi/Lo, Type, Count, Time, Clock, Channel, T1-T2, T3-T4, Backlight, RS232, Rec, Call
- ✓ NIST-Traceable Certificate of Calibration (No Points)
- ✓ Auto Power-Off, Low Battery Indication
- ✓ USB Interface with Windows Software (Optional RS232 Cable Available)
- ✓ 10,000 Record Data Logger
- ✓ CALL-Fit to Quick-Read Memory Data (50 Pages/Second)
- ✓ Perpetual Calendar Function
- ✓ CE-Mark Approval (Conforms to ITS-90)
- ✓ Battery Life: 550 hr



HH147U, \$299.

SPHT-K-6, 6" Type K surface probe, \$45.

The OMEGA® HH147U is a rugged, easy-to-use thermometer with 4 standard miniature connector inputs. It accepts 7 different thermocouple types and displays all 4 inputs at the same time. It also provides differential temperature measurement readings of T3-T4, as well as individual readings of the 4 inputs. Other features are a low battery indicator, perpetual calendar, and auto power-off.

## Specifications

- Thermocouple Range:**  
**K Type:** -100 to 1300°C (-148 to 2372°F)  
**J Type:** -100 to 1000°C (-148 to 1832°F)  
**E Type:** -50 to 800°C (-58 to 1472°F)

- T Type:** -100 to 400°C (-148 to 752°F)  
**R/S Type:** 0 to 1700°C (32 to 3092°F)  
**N Type:** -100 to 1300°C (-148 to 2372°F)
- Accuracy (18 to 28°C Ambient):**  
**K/J/E/T Type:**  
 ±(0.1% rdg + 0.7°C) -100 to 1300°C  
 ±(0.1% rdg + 1.4°F) -148 to 2372°F  
**R/S Type:**  
 ±(0.1% rdg + 2°C) 0 to 1700°C  
 ±(0.1% rdg + 4°F) 32 to 3092°F  
**N Type:**  
 ±(0.1% rdg + 1.5°C) -100 to 1300°C  
 ±(0.1% rdg + 3°F) -148 to 2372°F
- Operating Temperature and Humidity:** 0 to 50°C (32 to 122°F) 0 to 80% RH  
**Storage Temperature and Humidity:** -20 to 60°C (-4 to 140°F) 0 to 80% RH

- Power Requirement:** 4 "AAA" batteries (included)  
**Input Protection at Thermocouple Input:** 4 Vac/dc maximum  
**Dimensions (Without Holster):** 164 H x 76 W x 32 mm D (6.4 x 3 x 1.25")  
**Weight:** Approx 270 g (9.5 oz)

## Free Thermocouple Included!

These models include a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy (1 per channel). **Order a Spare!** Model No. SC-GG-K-30-36, \$15.



**AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
HH147U	\$299	4-channel data logger thermometer
SPHT-K-6	45	150 mm (6") Type K surface probe
HH147U-RS232CABLE	24	Optional RS232 cable
HH147U-USB	35	Spare USB cable
SC-GG-K-30-36	15	1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy

Comes complete with 4 beaded wire Type K thermocouples (1 per channel), rubber boot, 4 "AAA" batteries, software, USB cable and NIST certificate (no points), and operator's manual.  
**Ordering Examples:** HH147U, data logger thermometer and SPHT-K-6, Type K general purpose surface probe, \$299 + 45 = \$344. OCW-3, OMEGACARE™ extends standard 1-year warranty to a total of 4 years (\$74), \$299 + 74 = \$373.



OMEGACARE™ extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARE™ covers parts, labor and equivalent loaners.



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters