

Thermocouple Wire Overbraiding 304 SS, Inconel® or Tinned Copper

OMEGA can overbraid any thermocouple wire with either Inconel 600, 304 SS or Tinned Copper overbraiding. Both Inconel and Stainless Steel overbraiding add durability, flexibility, and abrasion protection to your valuable thermocouples, thus lengthening the life of your thermocouple by protecting it from wear. Low cost Tinned Copper overbraiding provides electrical shielding with the added benefits of durability, flexibility, and abrasion protection.


ANSI color code shown To order IEC color code visit omega.com



For Longer Lengths Consult Sales for Price and Delivery!



Shown larger than actual size.



304 SS Overbraid, 760°C Max Continuous

MOST POPULAR MODELS HIGHLIGHTED!

| Wire dia. mm (Gauge) | Price/ft 7.5 m (25') | Price/ft 15 m (50') | Price/ft 30 m (100') | Price/ft 60 m (200') | Price/ft 150 m (500') & Over* |
|-------------------------|-------------------------|------------------------|-------------------------|-------------------------|----------------------------------|
| 1.6 (14) | \$1.10 | \$0.88 | \$0.77 | \$0.66 | \$0.44 |
| 1.3 (16) | 1.03 | 0.82 | 0.72 | 0.62 | 0.41 |
| 0.8 (20) | 0.70 | 0.56 | 0.49 | 0.42 | 0.28 |
| 0.5 (24) | 0.53 | 0.42 | 0.37 | 0.32 | 0.21 |
| 0.25 (30) | 0.53 | 0.42 | 0.37 | 0.32 | 0.21 |
| 0.13 (36) | 0.53 | 0.42 | 0.37 | 0.32 | 0.21 |

Add to price per foot of wire.

Inconel 600 Overbraid, 1000°C Max Continuous

| Wire dia. mm (Gauge) | Price/ft 7.5 m (25') | Price/ft 15 m (50') | Price/ft 30 m (100') | Price/ft 60 m (200') | Price/ft 150 m (500') & Over* |
|-------------------------|-------------------------|------------------------|-------------------------|-------------------------|----------------------------------|
| 1.6 (14) | \$1.73 | \$1.38 | \$1.21 | \$1.04 | \$0.69 |
| 1.3 (16) | 1.58 | 1.26 | 1.10 | 0.95 | 0.63 |
| 0.8 (20) | 1.15 | 0.92 | 0.81 | 0.69 | 0.46 |
| 0.5 (24) | 0.88 | 0.70 | 0.61 | 0.53 | 0.35 |
| 0.25 (30) | 0.88 | 0.70 | 0.61 | 0.53 | 0.35 |
| 0.13 (36) | 0.88 | 0.70 | 0.61 | 0.53 | 0.35 |

Add to price per foot of wire.

Tinned Copper Overbraid, 200°C Max Continuous

| Wire dia. mm (Gauge) | Price/ft 7.5 m (25') | Price/ft 15 m (50') | Price/ft 30 m (100') | Price/ft 60 m (200') | Price/ft 150 m (500') & Over* |
|-------------------------|-------------------------|------------------------|-------------------------|-------------------------|----------------------------------|
| 1.6 (14) | \$0.75 | \$0.60 | \$0.53 | \$0.45 | \$0.30 |
| 1.3 (16) | 0.73 | 0.58 | 0.51 | 0.44 | 0.29 |
| 0.8 (20) | 0.45 | 0.36 | 0.32 | 0.27 | 0.18 |
| 0.5 (24) | 0.33 | 0.26 | 0.23 | 0.20 | 0.13 |
| 0.25 (30) | 0.33 | 0.26 | 0.23 | 0.20 | 0.13 |
| 0.13 (36) | 0.33 | 0.26 | 0.23 | 0.20 | 0.13 |

Add to price per foot of wire.

* For quantities over 3000', please consult Sales Department for price. Minimum order for overbraided wire: 25'.

To Order:

For **Stainless Steel Overbraid**, add the suffix "SB" to the wire part number and specify Stainless Steel Overbraid on your order.

For **Inconel Overbraid**, add the suffix "IB" to the wire part number and specify Inconel Overbraid on your order.

For **Tinned Copper Overbraid**, add suffix "TCB" to the wire part number and specify Tinned Copper Overbraid on your order.

Pricing:

To compute the total cost, add the price of the overbraiding from the tables to the price of the thermocouple wire.

Ordering Example:

GG-K-20-TCB-200, glass braid insulated wire, type K, 20 AWG, 200' with tinned copper overbraid,

Wire: \$535 x 0.3 = \$160.50
Overbraid: + \$0.27 x 200 = \$54.00
Total: = \$214.50



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters