

Wireless and High Accuracy Data Logger/Thermometers

HH806 Series
Starts at
\$199



Standard
No Points

HH806AW
Comes with Windows software, USB cable, wireless receiver and AC adaptor, and 2 thermocouples

- ✓ Wireless Models HH806W, HH806AW
- ✓ Dual Inputs
- ✓ 7 Thermocouple Types
- ✓ Triple Display
- ✓ Data Logging
- ✓ Includes NIST-Traceable Calibration Certificate (No Points)
- ✓ High/Low Alarm (Audible)
- ✓ Auto Power-Off
- ✓ MAX/MIN/MAX/MIN/AVG/REL/HOLD
- ✓ Thermocouple Offset
- ✓ Optional USB Interface
- ✓ Optional AC Adaptor

HH806AU
Features built-in USB port for use with optional windows software (see page L-16)

Wireless Models Available! Monitors Up to 10 Different Meters With 1 Receiver

The HH806 represents the top of the line in the HH800 series of handheld thermometers. All of the HH806 versions feature exceptional 0.05% basic accuracy and include a triple display as well as data logging capabilities. At a push of a button the HH806W can store up to 128 samples on demand, and at a user specified logging interval up to 1024 in data logging mode. The HH806AU and HH806AW expand the data logging capabilities further and allow storage of up to 256 samples on demand and up to 16,000 in data logging mode. All versions of the HH806 feature three easy to read displays. Two 4½ digit displays are selectable for T1 or T2 and the third 6 digit display can be used for T1-T2 or to show the current date and time. Windows software is available for all models but is included with the HH806AW, as is the USB cable, wireless receiver, and AC adaptor (HH806AW only).



HH806AW, \$315, shown actual size.

Specifications

Measurement Range:

- Type K: -200 to 1372°C (-328 to 2501°F)
- Type J: -210 to 1200°C (-346 to 2192°F)
- Type T: -200 to 400°C (-328 to 752°F)
- Type E: -220 to 1000°C (-364 to 1832°F)
- Type R: 0 to 1767°C (32 to 3212°F)
- Type S: 0 to 1767°C (32 to 3212°F)
- Type N: -50 to 1300°C (-58 to 2372°F)


Accuracy: Stated accuracy at 23°C ±5°C, <75% RH



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

Free Thermocouple Included!

These models include a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy (1 per channel). **Order a Spare! Model No. SC-GG-K-30-36, \$15.**



Type K/J/T/E:

±(0.05% rdg + 0.3°C) -50 to 1372°C
 ±(0.05% rdg + 0.7°C) -50 to -210°C
 ±(0.05% rdg + 0.6°F) -58 to 2501°F
 ±(0.05% rdg + 1.4°F) -58 to -346°F

Type N:

±(0.05% rdg + 0.8°C) -50 to 0°C
 ±(0.05% rdg + 0.4°C) 0 to 1300°C
 ±(0.05% rdg + 1.6°F) -58 to 32°F
 ±(0.05% rdg + 0.8°F) 32 to 2372°F

Type R/S:

±(0.05% rdg + 2.0°C to 1767°C
 ±(0.05% rdg + 4.32°F to 3212°F

Operating Environment: 0 to 50°C
 (32 to 122°F) at <70% RH

Storage Temperature: -20 to 60°C
 (-4 to 140°F), 0 to 80% RH with
 battery removed

Battery: 4 x 1.5V "AAA" (included)

Dimensions: 160 H x 83 W x 38 mm D
 (6.3 x 3.3 x 1.5")

Wireless Features:

Frequency Range: USA 900 MHz
 European 868.0 to 868.6 MHz

Current Consumption: 5 to 20 mA

Approximate Range: 25 m (75')

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)			
Model No.	HH806W (Wireless)	HH806AU	HH806AW (Wireless)
Price	\$199	\$210	\$315
Units	°C/°F	°C/°F	°C/°F
Display	Triple Display	Triple Display	Triple Display
Input types	K/J/T/E/R/S/N	K/J/T/E/R/S/N	K/J/T/E/R/S/N
Data Storage	128 on demand + 1024 in logging mode	256 on demand + 16000 in logging mode	256 on demand + 16000 in logging mode
No. of Inputs	2	2	2
Wireless	Yes	No	Yes
USB Port	No	Yes	Yes
DC Power Jack	No	Yes	Yes
Resolution	0.1° to 1999°; 1° above (auto ranging)		

Note: All wireless units are USA, 900 Mhz frequency band versions. For European 868.0 Mhz-868.6 Mhz frequency band versions, add suffix "E", no additional charge.

Comes complete with NIST certificate (no points), 4 "AAA" batteries, Type K thermocouple (one per channel), rubber boot and operator's manual.
Ordering Examples: HH806AU, high accuracy data logger and HH800-SW, Windows software, \$210 + 20 = \$230. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$52), \$210 + 52 = \$262.

Accessories

Model No.	Price	Description
HH800-ADAPTOR	\$10	AC adaptor (USB models only)
SC-800	10	Soft case with belt loop for HH800 series, see pages L-59 and L-60

Software For HH800 Series with USB or Wireless Interface Software for Windows 2000 and Windows XP with Wireless Receiver

HH800-SW
 Starts at
\$22

HH800W-RSW Windows
 software and wireless
 receiver (wireless
 models only), \$40.

- ✓ Data Logging and Retrieval Software for USB
- ✓ Display Retrieved Data in Graphic Format
- ✓ Display MAX/MIN/AVG/REL
- ✓ High/Low Alarms
- ✓ Selectable Logging Interval
- ✓ Provided on 3.5" CD



Laptop not included.

The HH800-SW and the HH800W-RSW both allow real time data logging to a PC. For wireless enable meters HH800W-RSW comes with both the software and wireless receiver, while for meters with USB, HH800-SW comes with the software and a USB cable. Both versions of software are identical and can work interchangeably. For meters with built in data storage, the software allows users to download and analyze data on there PC. Users can also export data to Excel or text files for further manipulation.

To Order (Specify Model Number)		
Model No.	Price	Description
HH800-SW	\$22	Windows software and USB cable (USB models only)
HH800W-RSW	40	Windows software and wireless receiver (wireless models only) USA version
HH800WE-RSW	40	Windows software and wireless receiver (wireless models only) European version

Ordering Example: HH800-SW, data logging software for HH800 Series meters with built-in USB port, \$22.

Hardware Requirements: Pentium III, 700 Mhz or better, minimum of 150 MB free hard disk space is recommended, single USB port.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters