

Digital Stroboscope

HHT30 Series
Starts at
\$450



- ✓ NIST Calibration Certificate Included
- ✓ Internal Rechargeable Batteries or AC-Powered Models
- ✓ Electronic Switching Provides Continuous Cool Operation
- ✓ Tachometer Mode
- ✓ Internal Phase Shift
- ✓ Easy-to-Read Backlit Digital Display
- ✓ Latching Trigger and 1/4-20 UNC Tripod Mount Allow Hands-Free Operation
- ✓ TTL-Compatible Input/Output Jacks
- ✓ Splashproof Cover Available for Battery Models
- ✓ 6 User-Programmable Memory Locations

The HHT30 digital stroboscope provides reliable and accurate speed measurements as well as stop-motion diagnostic inspection. A rotary encoder enables quick, precise frequency setting from 30 to 14,000 flashes per minute. The crystal-controlled circuitry eliminates drift and allows readings accurate to 0.1 rpm. "Divide by 2" and "Multiply by 2" buttons let the user check actual rpm. With "Phase +" and "Phase -" buttons, the user can add or subtract internal phase delays to keep the reference viewing target in eyesight. An "Adder Mode" enables visual inspection for misalignment or bent odd-numbered fan blades, propellers, etc. In the "Tach" mode, the unit uses external sensors to measure up to 200,000 rpm directly without flashing the strobe. Up to 6 preset memory values can be recalled from memory, and the unit recalls the last value measured.

A "% Charge" indicator shows remaining battery life. The microprocessor-controlled charging circuit ensures long battery life.

Specifications

Flash Range: 30 to 14,000 fpm, 0.5 to 233.33 fps
Flash Accuracy: ±0.01% rdg or ±0.5 fpm
Flash Resolution: 0.1 fpm
Tach Range: 5 to 200,000 rpm
Tach Resolution: 0.1 rpm, up to 99,999.9 rpm; 1 rpm, 100,000 to 200,000 rpm
Tach Accuracy: ±0.01% rdg or ±0.2 rpm
Display: 6-digit backlit alphanumeric LCD, 12.7 mm (0.5")
Average Power:
 HHT31: 15 W
 HHT32: 10 W
Flash Energy: 180 mJ (typical)
Flash Duration: 20 to 50 µs
Flash Tube Life: 100 million flashes typical
Power Supply:
 HHT31: 115 or 230 Vac, 50 to 400 Hz
 HHT32: Internal rechargeable batteries, 6 Vdc @ 2.5 A max
Battery Life (HHT32): Greater than 60 minutes @ 6000 fpm
External Trigger Input: 1/8" phone plug, TTL compatible
Trigger to Flash Delay: 5 µs, typical
Synchronization Output: 1/8" phone plug, TTL compatible
Weight:
 HHT31: 0.7 kg (1.5 lb)
 HHT32: 1.1 kg (2.5 lb)
Dimensions
Body: 90.4 H x 93.0 W x 229 mm L (3.56 x 3.66 x 9")
Reflector Housing: 122 mm Dia. (4.8")
Handle: 108 mm L (4.25")
Tripod Mount: 1/4-20 UNC
Operating Temperature: 5 to 40°C (41 to 104°F)
Operating Humidity: Max RH 80% for temperatures up to 31°C (88°F), decreasing linearly to 50% RH @ 40°C (104°F)



HHT32, \$515, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
HHT31	\$450	Stroboscope, 115 Vac powered
HHT31-KIT	590	HHT31 with rugged case and spare lamp
HHT31-230	500	Stroboscope, 230 Vac powered
HHT31-230-KIT	655	HHT31-230 with rugged case and spare lamp
HHT32	515	Stroboscope with internal battery, 115 Vac, 3-hr recharger
HHT32-KIT	660	HHT32 with 3-hr recharger, case and spare lamp
HHT32-230	530	Stroboscope with internal battery, 230 Vac, 3-hr recharger
HHT32-230-KIT	670	HHT32-230 with 3-hr recharger case, spare lamp
HHT20-ROS	142	Remote sensor for tachometer mode
HHT32-SPC	25	Splashproof protective cover for HHT32 models only

Comes with operator's manual and NIST certificate. HHT32 also includes rechargeable battery and AC charger. "-KIT" models also include rugged carrying case and spare lamp.

Ordering Example: HHT32-KIT, stroboscope with rechargeable battery, 115 Vac fast charger, rugged case and spare lamp, HHT32-SPC, splashproof cover, \$660 + 25 = **\$685**. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (**\$168**), \$660 + 165 = **\$825**.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters